



Z-PACK 2mm HM Connectors (Continued)

Vertical Male Connectors, 8 Row, Types D, E and F

Vertical Male Connectors

Types D, E and F mate with respective right angle receptacle connectors shown on page 217.

8 row Versions

For use with unshielded female connectors. Type D has 176 signal pins with center guiding and keying facility, and Type E has 200 signal pins and Type F has 88 signal pins. They are stackable without change of contact pitch according to the chart on page 210.

8+2 Row Versions

For use with females with ground return shields and have contacts in rows z and i in addition to those above.

Short Tail Versions

Standard versions have contact option A in rows a-h with option C in rows z and i on 8-2 row versions.

Feedthrough Versions

For midplane connection, 8 row versions mate with standard 8 row female connectors and 8+2 row versions mate with female connectors having ground return shields. Standard versions use contact options K and T instead of A and C.

For versions other than those shown, refer to page 243 which gives access to other sizes and loading patterns.

Guide pin Part No. 532808-1 may be used with Type D male connectors to give early alignment.

Electrical Characteristics —
 page 208.

Materials and Finish



Glass filled polyester housing, gray, UL94 V-0 rated
 Phosphor-bronze signal contacts
 Contact area 0.8µm Au over 1.3µm Ni
 ACTION PIN contact 0.5µm Sn/Pb over 1.3 µm Ni

Coding keys for type D page 243.

Board layout page 258 for guidance only.

Protection Covers available, see page 228.

Tooling — page 354.



Part Numbers	Short Tail		Feedthrough	
	8 Row	8+2 Row	8 Row	8+2 Row
Type D	646346-1	646356-1	646372-1	646375-1
Type D (16 column, 128 position)	646362-1	—	—	—
Type E	646347-1	646357-1	646373-1	646376-1
Type F	646457-1	646515-1	646514-1	646515-1

Backplane Systems

Backplane Connectors