

1825256-1 Product Details

 [Live Product Chat](#)


1825256-1

TE Internal Number: 1825256-1

 [Active](#)

Slide Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Number of Positions = 2
- Single Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Side
- Actuator Color = Black
- MHS Series

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, MHS SERIES, SINGLE POLE, RIGHT ANGLE \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[onlinecomponents.com](#)
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS
[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 2
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Actuator Style = Side
- Mount Angle = Right Angle
- Grade = Instrumentation
- Termination Type = PC
- PCB Retention Feature = Yes

Electrical Characteristics:

- Contact Rating = 300mA @ 125 VAC

Body Related Features:

- Actuator Color = Black
- Series = MHS
- Mount Style = Through-Hole
- Switch Style = Low Profile
- PCB Tail Length (mm [in]) = 3.51 [0.136]
- PCB Retention Method = Guide Posts
- Actuator Material = POM
- Flammability Rating = UL 94-HB
- Actuator Travel = 2.00 [.079]

Contact Related Features:

- Contact Plating = Silver
- Contact Base Material = Copper Alloy

Configuration Related Features:

- Terminal Configuration = Standard
- Operating Function = On None On
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

 [Provide Website Feedback](#) | [Need Help?](#)