

MRJ3404 Product Details

Share | Print | Email



MRJ3404
(1825535-3)

TE Internal Number: 1825535-3

Active

Rotary Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 12 Positions
- Angle of Throw = 30.00 °
- Actuator Style = Long Thin Knob
- Code Type = 3 Poles
- Straight Mount Angle

[View all Features](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • MINIATURE ROTARY SWITCH 12 POS.,-30%%d DETENT (MRJ SE... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Angle of Throw (°) = 30.00 • Actuator Style = Long Thin Knob • Code Type = 3 Poles • Mount Angle = Straight • Product Series = MRJ <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Contact Rating = 0.4 VA max @ 20 VDC or peak AC <p>Termination Features:</p> <ul style="list-style-type: none"> • Solder Tail Contact Plating = Gold over Nickel <p>Body Features:</p> <ul style="list-style-type: none"> • Number of Positions = 12 	<p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Base Material = Brass <p>Housing Features:</p> <ul style="list-style-type: none"> • Housing Material = Epoxy <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Other:</p> <ul style="list-style-type: none"> • Brand = Alcoswitch • Comment = Adjustable

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

