


# 520 Series CMP Cat 5e UTP Cable Cut Sheet

57825-X



## Description

AMP NETCONNECT 520 Series Category 5e plenum cables feature the best in class AirES® technology. This patented design saves as much as 32% of the available space in cable runs and is a key component of the AMPNETCONNECT structured cabling system. The smaller diameter also saves space in the communications closet, reduces the amount of cable management accessories required and lowers the risk associated with fire and smoke in the plenum space.

AMP NETCONNECT Enhanced Category 5e (Cat5E) cables exceed ANSI/TIA-568-C.2 Enhanced Category 5 (Category 5e) and ISO/IEC 11801 Class D performance requirements by significant margins, providing extra headroom for a more robust cabling system. The AMP NETCONNECT Enhanced Category 5 System complies with all of the performance requirements for current and proposed applications such as Gigabit Ethernet (1000BASE-Tx), 10 and 100BASE-Tx, token ring, 155 Mbps ATM, 100 Mbps TP-PMD, ISDN, analog and digital video, and analog and digital voice (VoIP).

AMP NETCONNECT Category 5E cables are available in standard colors white, gray, blue and yellow. Packaging includes reel-in-a-box, pull boxes and reels. Additional jacket colors are also available.

## Specification

Horizontal cabling shall be 24 AWG, 4-pair UTP, NEC/NFPA CMP rated and be independently verified for compliance. Cable jacketing shall be white, gray, blue or yellow and shall be lead-free. Individual conductors shall be 100% FEP insulated. Cable shall be independently verified by ETL and shall exceed all ANSI/TIA and ISO Enhanced Category 5/Class D requirements as well as meet the performance requirements listed in the table shown on page 2.

Cable performance shall be independently verified and characterized to 350MHz. Cable shall be supplied on reels, in pull boxes or in a reel-in-a-box. Cable shall be independently verified for flammability by UL. Flammability shall comply to NEC article 800 and NFPA 262. Horizontal cable shall be AMP NETCONNECT part number 57825-X.

## ORDERING INFORMATION

Product Description	Packaging	Part Numbers			
		White	Gray	Blue	Yellow
Category 5E UTP Cable, 350MHz, 4-Pair, Plenum (CMP) Rated	RL	57825-1	57825-3	57825-5	57825-7
	RB	57825-2	57825-4	57825-6	57825-8
	PB	6-57825-2	6-57825-4	6-57825-6	6-57825-8

Packaging: RL = 1000ft Reel, RB = 1000ft Reel-in-a-Box, PB = 1000ft Pull Box



# 520 Series CMP Cat 5e UTP Cable Cut Sheet

57825-X

## PERFORMANCE DATA

FREQ MHZ	FITTED IMPEDANCE Ohms	INSERTION LOSS dB/100m		RETURN LOSS dB/100m		PAIR-PAIR NEXT dB/100m		PSNEXT dB/100m	
	Spec	Max	Spec	Min	Spec	Min	Spec	Min	Spec
1	100+/-5	1.9	2.0	33.1	20.0	79.8	65.3	78.1	62.3
4	100+/-3	3.7	4.1	30.1	22.9	72.4	56.3	67.9	53.3
8	100+/-3	5.3	5.8	32.7	24.5	64.4	51.8	63.5	48.8
10	100+/-3	6.0	6.5	31.4	25.0	63.7	50.3	62.4	47.3
16	100+/-3	7.6	8.2	37.0	25.0	61.4	47.2	59.7	44.2
20	100+/-3	8.6	9.3	37.5	25.0	59.7	45.8	58.0	42.8
25	100+/-3	9.6	10.4	35.1	24.3	58.7	44.3	56.9	41.3
31.25	100+/-3	10.8	11.7	34.4	23.6	58.7	42.9	54.9	39.9
62.5	100+/-3	15.5	17.0	33.2	21.5	52.4	38.4	50.3	35.4
100	100+/-3	19.8	22.0	29.8	20.1	49.3	35.3	47.2	32.3
155	100+/-3	25.1	-	29.3	-	51.3	-	47.9	-
200	100+/-3	28.9	-	22.9	-	47.5	-	45.5	-
250	100+/-3	32.5	-	25.0	-	42.6	-	41.1	-
300	100+/-3	35.9	-	22.5	-	43.6	-	41.1	-
350	100+/-3	39.3	-	22.4	-	41.1	-	39.6	-

## PERFORMANCE DATA

FREQ MHZ	PAIR-PAIR ACR dB/100m		PSACR dB/100m		PAIR-PAIR ACRF dB/100m		PSACRF dB/100m	
	Min	Spec	Min	Spec	Min	Spec	Min	Spec
1	78.0	63.3	76.4	60.3	70.2	63.8	70.0	60.8
4	68.7	52.0	64.3	49.2	58.9	51.8	58.7	48.8
8	59.1	46.0	58.2	43.0	52.8	45.7	52.5	42.7
10	57.9	43.8	56.4	40.8	51.1	43.8	50.8	40.8
16	54.0	39.0	52.2	36.0	47.4	39.7	47.1	36.7
20	51.2	36.5	49.5	33.5	45.0	37.8	44.9	34.8
25	49.2	33.9	47.5	30.9	43.0	35.8	42.6	32.8
31.25	48.2	31.2	44.3	28.2	41.4	33.9	41.1	30.9
62.5	37.0	32.4	34.9	18.4	35.2	27.9	35.2	24.9
100	29.9	13.3	27.9	10.3	32.0	23.8	31.7	20.8
155	26.7	-	23.6	-	28.7	-	28.6	-
200	19.6	-	16.9	-	27.4	-	27.3	-
250	10.9	-	9.4	-	25.8	-	25.4	-
300	8.6	-	6.1	-	24.4	-	23.8	-
350	2.5	-	0.8	-	22.8	-	22.1	-

# 520 Series CMP Cat 5e UTP Cable Cut Sheet

57825-X

## SPECIFICATIONS

<b>Mutual Capacitance:</b>	5.6 nF/100 m maximum
<b>Conductor DC Resistance:</b>	28.6 $\Omega$ /1000 ft (9.38 $\Omega$ /100 m) maximum
<b>Voltage:</b>	300 VDC
<b>Delay Skew:</b>	25ns/100m maximum
<b>Propagation Delay:</b>	538ns/100m maximum @ 100MHz
<b>Nominal Velocity of Propagation:</b>	76%
<b>Operating Temperature:</b>	-20°C - 60°C (-4°F - 140°F)
<b>Storage Temperature:</b>	-20°C - 80°C (-4°F - 176°F)
<b>Installation Temperature:</b>	5°C - 50°C (41°F - 122°F)
<b>Bend Radius:</b>	4 × cable diameter
<b>Packaging:</b>	1000ft (± 2%) Reel: 20 lbs/mft 1000ft (± 2%) Reel-in-a-Box: 23 lbs/mft 1000ft (± 2%) Pull Box: 20 lbs/mft
<b>Materials:</b>	Conductors: 24 AWG, Solid Copper, (Ø.0201 nominal) Insulation: 0.034 nominal, FEP (fluoropolymer) Jacket: 0.175 nominal, LSPVC
<b>Compliances:</b>	UL Subject 444 (UL)-C(UL) Type CMP ICEA S-90-661 ETL Verified TIA-568-C.2 Category 5e Horizontal Cable Requirements ISO/IEC 11801 Category 5e Horizontal Cable Requirements 2002/95/EC RoHS



## DATA SHEET

**Contact us:**  
Greensboro, NC  
USA 27409-8420  
Tel: 1-800-553-0938  
Fax: 1-717-986-7406

[www.te.com](http://www.te.com)  
[www.te.com/adc](http://www.te.com/adc)



TE Connectivity, TE connectivity (logo), Tyco Electronics, TE (logo), AMP, AMP NETCONNECT, and NETCONNECT are trademarks of the TE Connectivity Ltd. family of companies and its licensors.

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this document, TE Connectivity does not guarantee that it is error-free, nor does TE Connectivity make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE Connectivity reserves the right to make any adjustments to the information contained herein at any time without notice. TE Connectivity expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE Connectivity for the latest dimensions and design specifications.

Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

110257AE (57825-X.) 8/11 Revision © 2011, 2006