


1-1337445-0 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ **Active**
[View 3D PDF](#)

BNC RF Connectors

BNC Str PCB Skt 50Ohm Silver P

1-1337445-0 ✔

TE Internal Number: 1-1337445-0

Product Highlights [View All](#)

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Printed Circuit Board
- Body Style = Straight

- [Pricing & Availability](#) ➤
- [Request Sample](#) ➤
- [Add to My Part List](#) +
- [Buy Product through Distributor](#) ➤

[Feedback](#)

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type ?	Connector - RF
Gender	Jack
PCB Mounting Orientation ?	Vertical
Grade ?	Professional
PCB Mount Retention ?	With
PCB Mount Retention Type	Solder Tail (Pin)
Mounting Post Style	Straight
Sealed ?	No
Isolated ?	No
Dielectric Material ?	PTFE
Mechanical Attachment	
Surface Mountable	No
Hardware Included ?	No
Panel Mount Retention	Without
Electrical Characteristics	
Connector Impedance (Ω) ?	50
Frequency	DC - 4 GHz
Dimensions	
Mounting Post Length (mm [in])	4.50 [0.177]
PCB Thickness, Recommended (mm [in])	3.20 [0.126]
Body Features	
Body Style ?	Straight
Body Shape	Square
Body Material ?	Brass
Body Plating ?	Silver
Polarized ?	No

Contact Features	
Center Contact Material ?	Brass
Center Contact Plating ?	Silver
Housing Features	
Connector Style	Jack
Configuration Features	
Number of Ports	1
Solder Terminal	With
Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Converted to comply with RoHS directive
Environmental	
Operating Temperature (Max.) (°C)	165
Conditions for Usage	
Applies To ?	Printed Circuit Board
Packaging Features	
Packaging Method	Individual
Packaging Quantity	50
Other	
Brand	Greenpar

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)