



**DIP8-pin type  
featuring low on-resistance  
with 400V load voltage**

PhotoMOS®

**HE 2 Form A  
(AQW254)**



**RoHS compliant**

### FEATURES

**1. High sensitivity and low on-resistance**

Can control max. 0.16 A load current with 5 mA input current. Low on-resistance of Typ. 10.2Ω. (in case of using only 1 channel)

**2. Applicable for 2 Form A use as well as two independent 1 Form A use**

**3. Controls low-level analog signals**

PhotoMOS feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.

**4. Low-level off state leakage current of max. 1 µA**

### TYPICAL APPLICATIONS

- High-speed inspection machines
- Data communication equipment
- Telephone equipment

### TYPES

	Output rating*		Package	Part No.			Packing quantity		
				Through hole terminal		Surface-mount terminal			
	Load voltage	Load current		Tube packing style		Tape and reel packing style		Tube	
						Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side		
AC/DC dual use	400 V	120 mA	DIP8-pin	AQW254	AQW254A	AQW254AX	AQW254AZ	1 tube contains: 50 pcs. 1 batch contains: 500 pcs.	1,000 pcs

\*Indicate the peak AC and DC values.

Note: The surface mount terminal indicator "A" and the packing style indicator "X" or "Z" are not marked on the device.

### RATING

**1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)**


Item		Symbol	AQW254(A)	Remarks
Input	LED forward current	I <sub>F</sub>	50 mA	
	LED reverse voltage	V <sub>R</sub>	5 V	
	Peak forward current	I <sub>FP</sub>	1 A	f = 100 Hz, Duty factor = 0.1%
	Power dissipation	P <sub>in</sub>	75 mW	
Output	Load voltage (peak AC)	V <sub>L</sub>	400 V	
	Continuous load current	I <sub>L</sub>	0.12 A (0.16 A)	A connection: Peak AC, DC ( ): in case of using only 1 channel
	Peak load current	I <sub>peak</sub>	0.36 A	100 ms (1 shot), V <sub>L</sub> = DC
	Power dissipation	P <sub>out</sub>	800 mW	
Total power dissipation		P <sub>T</sub>	850 mW	
I/O isolation voltage		V <sub>iso</sub>	1,500 Vrms	
Ambient temperature	Operating	T <sub>opr</sub>	-40 to +85°C -40 to +185°F	(Non-icing at low temperatures)
	Storage	T <sub>stg</sub>	-40 to +100°C -40 to +212°F	

# HE 2 Form A (AQW254)

## 2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item		Symbol	AQW254(A)	Condition
Input	LED operate current	Typical I <sub>Fon</sub>	0.9 mA 3 mA	I <sub>L</sub> = Max.
		Maximum		
Input	LED turn off current	Minimum I <sub>Foff</sub>	0.4 mA 0.8 mA	I <sub>L</sub> = Max.
		Typical		
Input	LED dropout voltage	Typical V <sub>F</sub>	1.25 V (1.14 V at I <sub>F</sub> = 5 mA)	I <sub>F</sub> = 50 mA
		Maximum	1.5 V	
Output	On resistance	Typical R <sub>on</sub>	10.2 Ω	I <sub>F</sub> = 5 mA
		Maximum	16 Ω	I <sub>L</sub> = Max. Within 1 s
Output	Off state leakage current	Maximum I <sub>Leak</sub>	1 μA	I <sub>F</sub> = 0 mA V <sub>L</sub> = Max.
Transfer characteristics	Turn on time*	Typical T <sub>on</sub>	0.8 ms	I <sub>F</sub> = 5 mA
		Maximum	2 ms	I <sub>L</sub> = Max.
	Turn off time*	Typical T <sub>off</sub>	0.04 ms	I <sub>F</sub> = 5 mA
		Maximum	0.2 ms	I <sub>L</sub> = Max.
	I/O capacitance	Typical C <sub>iso</sub>	0.8 pF	f = 1 MHz
		Maximum	1.5 pF	V <sub>B</sub> = 0 V
	Initial I/O isolation resistance	Minimum R <sub>iso</sub>	1,000 MΩ	500 V DC

\*Turn on/Turn off time



## 3. Recommended operating conditions (Ambient temperature: 25°C 77°F)

Please use under recommended operating conditions to obtain expected characteristics.

Item	Symbol	Number of used channels	Min.	Max.	Unit
LED current	I <sub>F</sub>	Aqw254(A)	5	30	mA
Load voltage (Peak AC)	V <sub>L</sub>		—	320	V
Continuous load current	I <sub>L</sub>		1ch 2ch	0.16 0.12	A

■ These products are not designed for automotive use.


If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

## REFERENCE DATA

### 1. Load current vs. ambient temperature characteristics


Allowable ambient temperature: -40 to +85°C  
-40 to +185°F

When using 2 channels




### 2. On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: 400 V (DC); Continuous load current: 120 mA (DC)




### 3. Turn on time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: 400 V (DC); Continuous load current: 120 mA (DC)




4. Turn off time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: 400 V (DC); Continuous load current: 120 mA (DC)




5. LED operate current vs. ambient temperature characteristics

Load voltage: 400 V (DC); Continuous load current: 120 mA (DC)




6. LED turn off current vs. ambient temperature characteristics

Load voltage: 400 V (DC); Continuous load current: 120 mA (DC)




7. LED dropout voltage vs. ambient temperature characteristics

LED current: 5 to 50 mA




8. Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F




9. Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F




10. Turn on time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: 400 V (DC); Continuous load current: 120 mA (DC); Ambient temperature: 25°C 77°F




11. Turn off time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: 400 V (DC); Continuous load current: 120 mA (DC); Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Frequency: 1 MHz; Ambient temperature: 25°C 77°F



"PhotoMOS®", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation.

\*Recognized in Japan, the United States, all member states of European Union and other countries.

---

Please contact .....

**Panasonic Corporation**

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadomashi, Osaka 571-8506, Japan  
[industrial.panasonic.com/ac/e/](http://industrial.panasonic.com/ac/e/)

**Panasonic®**

©Panasonic Corporation 2017