



1-1337452-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

BNC RF Connectors

BNC Ins BHSkt 50Ohm Nickel Gol

1-1337452-0

TE Internal Number: 1-1337452-0

Product Highlights [View All](#)

- Connector - RF
- Jack
- Connector Style = Jack
- Body Style = Bulkhead
- Not Surface Mountable

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector - RF
Gender	Jack
Grade	Professional
Sealed	No
Isolated	No
Dielectric Material	ABS
Flats Dimension	12.7

Mechanical Attachment	
Surface Mountable	No
Hardware Included	No
Panel Mount Retention	With
Panel Mount Retention Type	Hex Nut
Panel Attachment Style	Front Mount
Panel Cutout	8.7mm x 9.6mm D-Shape
Flange Dimension [Dia.] (mm [in])	12.6 [0.496]

Electrical Characteristics	
Connector Impedance (Ω)	50
Frequency	DC - 4 GHz

Dimensions	
Panel Thickness (mm [in])	1.52 - 3.20 [0.062 - 0.126]

Body Features	
Body Style	Bulkhead
Body Material	Brass
Body Plating	Nickel
Polarized	No
Flange and Thread Material	ABS
Lockwasher Material	Mild Steel
Lockwasher Plating	Nickel

Contact Features	
Center Contact Material	Brass
Center Contact Plating	Gold

Housing Features	
Connector Style	Jack
Housing Material	ABS (Acrylonitrile-Butadiene-Styrene)

Configuration Features	
Number of Ports	1
Solder Terminal	With

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Converted to comply with RoHS directive

Environmental	
Operating Temperature (Max.) (°C)	85

Packaging Features	
Packaging Method	Individual
Packaging Quantity	50

Other	
Brand	Greenpar

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

