Compact / Cable type PM-45 SERIES



ORDER GUIDE

Туре		Appearance (mm in)	Sensing range	Model No.	Cable length	Output	Output operation
Compact / Cable type	K type	7 0.276 25.4 1.000 21.3 0.839	6 mm 0.236 in (fixed)	PM-K45	1 m 3.281 ft	NPN open-collector transistor	Incorporated with 2 outputs: Light-ON / Dark-ON
				PM-K45-C3	3 m 9.843 ft		
				PM-K45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-K45-P-C3	3 m 9.843 ft		
		13.7 0.539 18.1 1.024 1.024		PM-T45	1 m 3.281 ft	NPN open-collector transistor	
	T type			PM-T45-C3	3 m 9.843 ft		
				PM-T45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-T45-P-C3	3 m 9.843 ft		
	L type	26 1.024 7 0.276		PM-L45	1 m 3.281 ft	NPN open-collector transistor	
				PM-L45-C3	3 m 9.843 ft		
				PM-L45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-L45-P-C3	3 m 9.843 ft		
	Y type	13.4 0.528 13.4 0.811		PM-Y45	1 m 3.281 ft	NPN open-collector transistor	
				PM-Y45-C3	3 m 9.843 ft		
				PM-Y45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-Y45-P-C3	3 m 9.843 ft		
	F type	13 0.512 13.7 0.539 21.3 0.839		PM-F45	1 m 3.281 ft	NPN open-collector transistor	
				PM-F45-C3	3 m 9.843 ft		
				PM-F45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-F45-P-C3	3 m 9.843 ft		
	R type	13.7 21.3 0.539 21.3 0.839		PM-R45	1 m 3.281 ft	NPN open-collector transistor	
				PM-R45-C3	3 m 9.843 ft		
				PM-R45-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-R45-P-C3	3 m 9.843 ft		

Note: The suffix "-C3" in the model No. indicates a 3 m $9.843~{\rm ft}$ cable length type.

SPECIFICATIONS

		T	Compact / Cable type					
		Type		3 m 9.843 ft cable				
	S.	NPN output	PM- _□ 45	PM- _□ 45-C3				
Item	Node I	PNP output	PM- _□ 45-P	PM- _□ 45-P-C3				
Sensing range			6 mm 0.236 in (fixed)					
Minimum sensing object			0.8 × 1.2 mm 0.031 × 0.047 in opaque object					
Hysteresis			0.05 mm 0.002 in or less					
Repeatability			0.01 mm 0.0004 in or less					
Supply voltage			5 to 24 V DC ±10 % Ripple P-P 10 % or less					
Current consumption		nption	15 mA or less					
Output			<npn output="" type=""> NPN open-collector transistor • Maximum sink current: 50 mA • Applied voltage: 30 V DC or less (between output and 0 V) • Residual voltage: 2 V or less (at 50 mA sink current) 1 V or less (at 16 mA sink current)</npn>	<pnp output="" type=""> PNP open-collector transistor • Maximum source current: 50 mA • Applied voltage: 30 V DC or less (between output and + V) • Residual voltage: 2 V or less (at 50 mA source current) 1 V or less (at 16 mA source current)</pnp>				
	Output op	eration	Incorporated with 2 outp	outputs: Light-ON / Dark-ON				
	Short-circ	uit protection	Incorp	orated				
Response time			Under light received condition: 20 µs or less Under light interrupted condition: 80 µs or less (Maximum response frequency: 3 kHz) (Note 2)					
Operation indicator		ator	Orange LED (lights up under light received condition)					
Pollution degree		Э	3					
	Protection	l	IP64	IP64 (IEC)				
nce	Ambient te	emperature	-25 to +55 °C -13 to +131 °F (No dew condensation of	r icing allowed), Storage: –30 to +80 °C –22 to +176 °F				
Environmental resistance	Ambient h	umidity	5 to 85 % RH, Stor	rage: 5 to 95 % RH				
alre	Ambient il	luminance	Fluorescent light: 1,000 &	x at the light-receiving face				
ment	Voltage w	ithstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure					
iron	Insulation	resistance	20 MΩ, or more, with 250 V DC megger between all supply terminals connected together and enclosure					
En	Vibration r	resistance	10 to 2,000 Hz frequency, 1.5 mm 0.059 in double amplitude (maximu	um acceleration 196 m/s²) in X, Y and Z directions for two hours each				
	Shock resistance		15,000 m/s ² acceleration (1,500 G approx.) in X, Y and Z directions three times each					
Emitting element		nt	Infrared LED (Peak emission wavelength: 855 nm 0.034 mil, non-modulated)					
Material			Enclosure: PBT, Display section: Polycarbonate					
Cable			0.09-mm² 4-core cabtyre cable, PVC, 1 m 3.281 ft long	0.09-mm² 4-core cabtyre cable, PVC, 3 m 9.843 ft long				
Cable extension		า	Extension up to total 100 m 328.084 ft is possible with 0.3 mm ² , or more, cable. (Note 3)					
Weight			Net weight: 10 g approx., Gross weight: 15 g approx.	Net weight: 30 g approx., Gross weight: 35 g approx.				

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

2) The response frequency is the value when the disc, given in the figure below, is rotated.



3) If the cable is extended to 20 m 65.617 ft or longer, confirm that the supply voltage at the end of the cable attached to the sensor is 4.5 V or higher.