



CONNECTORS

SO DIMM



✓ Active

TE CONNECTIVITY (TE)

EMBOSS ASSY DDR2 SODIMM SOCKET 200P 5.2H

[DDR1 and DDR2 SODIMM](#) | [DDR2 SO DIMM](#) , [SO DIMM](#)

1717254-4

TE Internal Number: 1717254-4

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

DRAM Type Double Data Rate (DDR)

Stack Height 5.2 mm [.205 in]

Module Orientation Right Angle

PCB Mounting Style Surface Mount

Number of Positions 200

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

[DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS STANDARD PROFILE STANDARD TYPE](#)

PDF

English

CAD Files

[Customer View Model](#)

3D_STP.ZIP

English

[3D PDF](#)

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Product Specifications

Product Specification

DDR S.O.DIMM Socket 200 Positions

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_1717254-4_0526201722_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

DRAM Type Double Data Rate (DDR)

Profile Standard

Row-to-Row Spacing 6.2 mm [.244 in]

Connector & Contact Terminates To Printed Circuit Board

Product Type Socket

Configuration Features

Module Orientation Right Angle

Number of Positions 200

Number of Rows 2

Keying Standard

Number of Keys 1

Center Key None

Number of Bays 2

Electrical Characteristics

DRAM Voltage (V) 1.8

Signal Characteristics

SGRAM Voltage (V) 1.8

Body Features

Ejector Type Locking
Module Key Type SGRAM
Latch Plating Material Tin
Latch Material Stainless Steel
Ejector Location Both Ends

Contact Features

Solder Tail Contact Plating Material Gold Flash
Contact Mating Area Plating Material Gold Flash
Contact Base Material Copper Alloy
Socket Type Memory Card
Socket Style SO DIMM

Termination Features

Insertion Style Cam-In

Mechanical Attachment

PCB Mounting Style Surface Mount
PCB Mount Retention With
PCB Mount Retention Type Solder Peg

Housing Features

Centerline (Pitch) .6 mm [.024 in]
Housing Material High Temperature Thermoplastic
Housing Color Black

Dimensions

Stack Height 5.2 mm [.205 in]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Tape & Reel
Packaging Quantity 150

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
