


## 404806412009 Product Details

[Share](#) [Print](#) [Email](#)



**404806412009**  
(1623850-9)

TE Internal Number: 1623850-9

Active

[View 3D PDF](#)

### Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = K  $\Omega$
- Resistance = 5K  $\Omega$
- Power Rating = .50 W

[View all Features](#)

### Quick Links

- [▶ Check Pricing & Availability](#)
- [▶ Search for Tooling](#)
- [▶ Product Feature Selector](#)
- [▶ Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PROFESSIONAL TRIMMERS SERIES 4290X](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Professional Trimmers - Type 4290 Series - Tyco Elec...](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version BA)
- [3D Model](#) (IGES, Version BA)
- [3D Model](#) (STEP, Version BA)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Trimmer
- [Element](#) = Cermet
- [Series](#) = 4290
- [Sealed](#) = Yes
- [Mount Angle](#) = Vertical
- [Termination Type](#) = PCB Terminations

#### Electrical Characteristics:

- Resistance Selection ( $\Omega$ ) = K
- [Resistance \( \$\Omega\$ \)](#) = 5K
- [Power Rating \(W\)](#) = 0.50
- [Tolerance \(%\)](#) = 10

#### Termination Features:

- [Termination Post Orientation](#) = In Line

#### Body Features:

- [Package, Component Size](#) = 10

#### Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Side
- [Adjustment Style](#) = Screwdriver Slot
- [Operating Function](#) = Multi Turn

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = 100

#### Other:

- Brand = Citec

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

