



Product Specification

- Material
- Insulator: Glass-filled Thermoplastic PBT UL94V-0
- Contact: Brass
- Shell: Steel, 100u" Tin over 50u" min copper
- Clinch Nut: Brass, Nickel plated
- Boardlock: Brass, Tin plated
- Screwlock: Brass, Nickel plated

Electrical

- Contact Resistance: 20 milliohms
- Max at 1 AMP DC
- Insulation resistance: 1000 megaohms at 500 VDC
- Dielectric Withstanding Voltage: 1000 VAC/rms 60hz for 1 minute
- Current rating: 3 Amp
- Voltage rating: 250 VAC/rms 60hz



Scale	1:1							Name	Item No.
TOLERANCE								Drawn	10/18/12
X.X	±0.40							Miller	A-DS09LL-TL-B-R
X.XX	±0.25						Approved	10/18/12	
X.XXX	±0.15							Warner	Title
Angle	±3°								D-sub, Soldier Type, 9 pin male
									Drawing No.
									rev00
									Replace
									Sheet

