


8-53426 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



8-53426 -1

✓ [Active](#)

Radiation Resistant/Pre - Insulated Terminals & Splices

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- ? Terminal
- ? Wire Range = 3.00 - 6.00 ² [12 - 10] mm [AWG]
- ? Wire Range = 5180 - 13100 CMA
- ? Body Style = PIDG
- ? Wire Insulation Diameter = 5.84 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Terminal
- ? [Body Style](#) = PIDG
- ? [Wire Insulation Diameter \(mm \[in\]\)](#) = 5.84 [0.230]
- ? [Stud Size](#) = 1/4 [M6]
- ? [Finish](#) = Tin -Lead
- ? Tongue Material Thickness (mm [in]) = 1.04 [0.041]
- ? Color Code = Yellow
- ? Body Material = Copper
- ? Insulation = Yes
- ? Comment = Brazed Body

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 3.00 - 6.00 ² [12 - 10]
- ? [Wire Range \(CMA\)](#) = 5,180 - 13,100
- ? Insulation Sleeve Color = Natural
- ? Insulation Sleeve Material = PVF2
- ? Insulation Support Sleeve Material = Copper

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece
- ? Packaging Quantity = 100/Box

Other:

- ? Brand = AMP