



+ CABLE ASSEMBLIES

## PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**  
English

TE CONNECTIVITY (TE)

### CA MINI IO TYPE II PIGTAIL

2205130-3

TE Internal Number: 2205130-3

Always EU RoHS/ELV Compliant


Cable Assembly Type **Mini I/O**

Equalized **No**

Wire Size (AWG) **26**

Wire Size (mm<sup>2</sup>) **.129**

Overall Outside Cable Diameter **.244 in, 6.2 mm**



### Product Drawings

#### CA MINI IO TYPE II PIGTAIL

PDF  
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

### Product Type Features

Cable Assembly Type

**Mini I/O**

Shielded

**Yes**

Connector Type (End A)

**RJ45 Plug**

Product Type

**Cable Assembly**

Cable Assembly Category

**Industry Standard**

Product Designation

**Patch Cord**



	Performance Category	<b>Category 5E Performance for 10/100/1000BASE-T</b>
	Latching Style	<b>Slide Latch</b>
	Twisted Pairs	<b>Yes</b>
Configuration Features	Number of Positions	<b>8</b>
	Number of Signal Positions	<b>8</b>
	Configuration	<b>Single-Ended</b>
Electrical Characteristics	Impedance ( $\Omega$ )	<b>100</b>
Signal Characteristics	Data Rate (Gb/s)	<b>1</b>
Body Features	Equalized	<b>No</b>
	Color	<b>Black</b>
	Shield Material	<b>Copper Alloy</b>
	Jacket Material	<b>PVC</b>
Contact Features	Contact Mating Area Plating Material	<b>Gold</b>
	Contact Mating Area Plating Thickness	<b>.5 <math>\mu\text{m}</math>, 19.68 <math>\mu\text{in}</math></b>
Mechanical Attachment	Jackscrew	<b>Without</b>
Housing Features	Housing Material	<b>Thermoplastic</b>
Dimensions	Wire Size (AWG)	<b>26</b>
	Wire Size (mm <sup>2</sup> )	<b>.129</b>
	Overall Outside Cable Diameter	<b>.244 in, 6.2 mm</b>
	Cable Assembly Length	<b>2 m [ 6.56 ft ]</b>
Operation/Application	Halogen Free	<b>Yes</b>
Industry Standards	Flammability Rating	<b>UL 444</b>
	IEEE 1394	<b>No</b>
Other	CLOUDSPLITTER	<b>No</b>

Product Compliance

Statement of Compliance

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

