

1825200-1 Product Details



1825200-1
(MSSA245004)

TE Internal Number: 1825200-1

 [Active](#)

Slide Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 4 Positions
- Double Pole - Four Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Top
- Actuator Color = Black
- MSSA Series

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [OUTLINE DRAWING SLIDE SWITCH, DP 4 POS. \(MSSA-2450 S...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Four Throw
- Actuator Style = Extended, Top
- Series = MSSA
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC, 300mA @ 125 VAC

Body Features:

- [Number of Positions](#) = 4
- Actuator Color = Black
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 3.51 [0.136]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 10.40 [0.410]
- Actuator Material = Polyester
- Actuator Travel = 2.50 [.098]

Contact Features:

- Contact Plating = Silver

Housing Features:

- UL Flammability Rating = UL 94V-0

Configuration Features:

- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

