
SB® Smart Connector - up to 230 Amps





The SB® Smart is designed for applications where storage batteries intelligently interact with the system. Two primary power positions (up to 230 amps each) are combined with sixteen auxiliary power / signal positions (up to 15 amps each) into a single interconnect solution. This allows one connection to be used to route high power lines, low power lines, and signal circuits.

Unique to the SB® Smart is it's selective keyed housings that allow only mating between select connector halves. This prevents motors from mating with chargers, chargers from mating with chargers, or other undesirable connection scenarios.

• Selective Keyed Housings

Unique keying feature only allows intended connector halves to mate

Power and Auxiliary Contacts

Provides power up to 230 amps plus signal & low power in a single connector

16 Last-Mate First-Break Auxiliary Power / Signal Poles

Enables the power connector to also transmit signals for intelligent power switching, battery monitoring, CAN communication, loop circuitry, and other signal or power circuits up to 15 amps

Sequencing of Auxiliary Contacts

Male auxiliary contacts available in 3 lengths

Wire and Busbar Connections

Satisfies multiple interconnect needs with one connection solution

Low Resistance Connection

- Silver plated power contacts are strongly forced together by stainless steel springs
- Gold plated auxiliary contacts ensure signal quality or reliable power


Hot Plug Capable Contacts


- Power contacts are hot plug capable up to 60A at 120VDC
- Auxiliary contacts are hot plug capable up to 5A at 120VDC

ORDERING INFORMATION |

SB® Smart Housings (Auxiliary Module Sold Separately)


| | | • | • | • • |
|---|---------|-------------------------|------------------|--------------|
| - | Color | Housing Type / Marking | Mates With | Part Numbers |
| | Minimun | n Quantity | | 100 |
| - | Black | Battery BAT-G1 | VEH-G2 & CHRG-G4 | 115158G1 |
| | Black | Vehicle / Device VEH-G2 | BAT-G1 | 115158G2 |
| - | Black | Charger CHRG-G4 | BAT-G1 | 115158G4 |
| | | | | |





Side View

[1.181 ± .005] 30.00 ± 0.13 [1.53] 38.8



Mated Pairings Illustrations


© 2018 Anderson Power Products, Inc. All rights reserved. APP®, Anderson Power Products®, A®, SB® and the APP Logo are registered trademarks of Anderson Power Products, Inc.

APP.
An IDEAL Company

SB®Smart Silver Plated Wire Contacts

Silver plated contacts offer superior electrical performance and durability up to 10,000 mating cycles. New contacts for #1 to 1/0 AWG (35 to 50 mm²) offer extended capability in the same housings.

| | | Mating | | | | - A | | - E | 3 - |
|-------|--------------|--------------|-----------|----------------------|----------------|--------------|----------------|--------|--------------|
| AWG | mm² | Force | Loose | Piece Part N | umbers | inches | mm | inches | mm |
| Minin | num Qua | antity | 600 | 500 | 50 | | | | |
| 1/0 | 53.5 | Low | 1323G2-BK | - | 1323G2 | 0.52 | 13.21 | 0.44 | 11.18 |
| 1 | 42.4 | Low | 1323G1-BK | - | 1323G1 | 0.47 | 11.94 | 0.39 | 9.91 |
| 2 | 33.6 | High | - | 1319-BK | 1319 | 0.44 | 11.18 | 0.34 | 8.64 |
| 4 | 21.1 | High | - | 1319G4-BK | 1319G4 | 0.44 | 11.18 | 0.29 | 7.37 |
| 6 | 13.3 | High | - | 1319G6-BK | 1319G6 | 0.44 | 11.18 | 0.22 | 5.59 |
| 4 | 33.6 21.1 | High High | - | 1319-BK 1319G4-BK | 1319 1319G4 | 0.44 0.44 | 11.18 11.18 | 0.34 | 8.64 7.37 |




SB®Smart Silver Plated Busbar Contacts

Use 2 busbar contacts per housing to provide a quick disconnect input or output busbar connection. Busbar contacts are for mating with wire contacts only. Part number 120BBS includes lock nuts. Locknuts must be ordered separately for B01997P1.

| | | Mating | | | | |
|----------|------------|--------|---------|--------------|------------|--------|
| Туре | Thread | Force | L | oose Piece P | art Numbei | rs |
| Minimum | Quantity . | | 1,000 | 300 | 20 | 10 |
| Busbar | #10-24 | High | - | B01997P1 | - | 120BBS |
| Lock Nut | #10-24 | - | H1216P8 | - | 110G54 | - |


See Busbar contact drawing on website for further detail.




Reducing Bushings

Use with contact part number 1319-BK or 6811G6-BK to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

| | | | | | Dimei | ISIONS |
|--------------------------------|--|---------|------------|------|--------|--------|
| | | | | | - 10 | O - |
| Contact Barrel Size | Wire Size | Pa | rt Numbers | | inches | mm |
| Minimum Quantity | | 2,000 | 1,000 | 100 | | |
| #2 AWG [33.6 mm ²] | #4 AWG [21.2 mm ²] | 5919-BK | - | 5919 | 0.28 | 7.11 |
| #2 AWG [33.6 mm ²] | #6 AWG [16 mm²] | - | 5920-BK | 5920 | 0.23 | 5.84 |
| #2 AWG [33.6 mm ²] | #10 - 8 AWG [5.3 - 8.4 mm ²] | 5921-BK | - | 5921 | 0.18 | 4.57 |




SB®Smart Auxiliary Module



Retaining Pins

Retaining pins are used to hold the auxiliary module in the SB $^{\circ}$ Smart housings. Dimension "B" is +/- 0.01 in or 0.25 mm.


| Description | - Part Number - | - A - | | - B- |
|------------------|-----------------|---------------|-------------|-------------|
| Minimum Quantity | 100 | inche | es . | mm |
| For SB® Smart | | | | |
| Auxiliary Module | 111812P16 | 0.099 / 0.106 | 2.51 / 2.69 | 1.125 28.58 |



Pin Contacts for 1x4 Auxiliary Connector

Gold plated contacts are available in 3 lengths to allow sequencing of circuits.

| Description | AWG | mm² | Part N | lumbers |
|-----------------------|----------|--------------|--------------|-----------------|
| Minimum Quantity | | | 500 | 50 |
| Standard Length 7.7mm | 12 | 2.5 | PM16P12S30 | PM16P12S30-50 |
| | 16 to 14 | 1.0 to 1.5 | PM16P1416S30 | PM16P1416S30-50 |
| | 20 to 16 | 0.75 to 1.0 | PM16P1620S30 | PM16P1620S30-50 |
| | 24 to 20 | 0.50 to 0.75 | PM16P2024S30 | PM16P2024S30-50 |
| Pre-Mate 9.3mm | 12 | 2.5 | PM16P12A30 | PM16P12A30-50 |
| | 16 to 14 | 1.0 to 1.5 | PM16P1416A30 | PM16P1416A30-50 |
| | 20 to 16 | 0.75 to 1.0 | PM16P1620A30 | PM16P1620A30-50 |
| | 24 to 20 | 0.50 to 0.75 | PM16P2024A30 | PM16P2024A30-50 |
| Post-Mate 6.4mm | 12 | 2.5 | PM16P12C30 | PM16P12C30-50 |
| | 16 to 14 | 1.0 to 1.5 | PM16P1416C30 | PM16P1416C30-50 |
| | 20 to 16 | 0.75 to 1.0 | PM16P1620C30 | PM16P1620C30-50 |
| | 24 to 20 | 0.50 to 0.75 | PM16P2024C30 | PM16P2024C30-50 |




| Auxiliary Pin | - L | - L - | | 1 - |
|------------------------|------|-------|------|-----|
| Contact Lengths | in. | mm | in. | mm |
| Standard Length 7.7mm | 0.77 | 19.6 | 0.30 | 7.7 |
| Pre-Mate 9.3mm | 0.83 | 21.2 | 0.37 | 9.3 |
| Post-Mate 6.6mm | 0.72 | 18.3 | 0.25 | 6.4 |

Socket Contacts for 1x4 Auxiliary Connector

Selectively gold plated contacts offer low resistance and durability up to 10,000 mating cycles.

| Description | AWG | mm² | Pa | art Numbers |
|------------------|----------|--------------|--------------|-----------------|
| Minimum Quantity | | | 500 | 50 |
| Socket Contact | 12 | 2.5 | PM16S12S32 | PM16S12S32-50 |
| | 16 to 14 | 1.0 to 1.5 | PM16S1416S32 | PM16S1416S32-50 |
| | 20 to 16 | 0.75 to 1.0 | PM16S1620S32 | PM16S1620S32-50 |
| | 24 to 20 | 0.50 to 0.75 | PM16S2024S32 | PM16S2024S32-50 |



| Auxiliary Socket Contacts Crimp Barrel ID | | | | | |
|---|------|-----|--|--|--|
| Wire Gauge | in. | mm. | | | |
| #24 / 20 | 0.04 | 1.1 | | | |
| #20 / 16 | 0.07 | 1.7 | | | |
| #16 / 14 | 0.08 | 2.1 | | | |
| #12 | 0.10 | 2.6 | | | |

| SPECIFICATIONS |

| Electrical | | |
|--------------------------------------|--------------|-------------|
| Current Rating (Amperes) 1 | | |
| Primary Contacts | 230 | |
| Auxiliary Contacts | 15 | |
| Operating Temperature ² | °C | °F |
| PC Housing | -20° to 105° | -4° to 221° |
| Voltage Rating (AC/DC) | | 600 |
| Dielectric Withstanding Voltage (AC) | | 2,200 |


| PC |
|---------------------------------|
| UL94 V-0 |
| Copper alloy, silver plate |
| Copper alloy, tin plate |
| Copper alloy, Au over Ni |
| BeCu, Au over Ni |
| Copper alloy, Sn Bright over NI |
| |


| Mechanical | | | |
|--|--------------|-----------------------------------|--|
| Contact Wire Range | (AWG) | Power 10 to 1/0 5.3 to 53.5 | Auxiliary Power #24 to #12*** 0.25 to 3.3*** |
| MAX Wire Insulation Diameter | (in) (mm) | 0.65 16.25 | 0.12 3.2 |
| AVG Contact Resistance (milli-ohms) ³ | | 0.136 | 3.00 |
| AVG Contact Retention Force | (lbf) (N) | 60 267 | 18 80 |
| Mating Cycles (no load) | | 10,000 | 10,000 |
| Mating Cycles (hot plug @ 120V) | | 250 @ 50A | 250@ 5A |
| Connector AVG Connect / Disconnect | (lbf) (N) | 82 365 | |


- ¹ Based on: 105°C rated or better cable of the largest size, Properly calibrated APP recommended tooling, and a 25°C ambient temperature.
- ² Limited by the thermal properties of the connector plastic housing.
- ³ Use APP recommended tooling only. Alternate tools may adversely affect the performance of our connectors.




For Temperature Rise Above 60°C, Consult the Extended Temperature Rise Charts in the Appropriate Product Section on the Website.








Current - Temperature Derating per IEC 60512-5-2 Test 5B





TOOLING INFORMATION |

| Wire Size | | Loose Piece Part Numbers | | Loose Piece Contact Crimp Tool | | | | | | |
|-----------|------|--------------------------|-------------------|--------------------------------|----------------------------|--------|-----------|---------------------|--|--|
| AWG | mm² | Tin Plating | Silver Plating | Hand Tool or | Pneumatic Bench Tool | + Die | + Locator | Number of Crimps | | |
| | | | | | | | | | | |
| 1/0 | 53.5 | N/A | 1323G2 | 1368 | 1387G1 | 1388G3 | 1389G4 | Single | | |
| #1 | 42.4 | | 1323G1 | | | | | | | |
| #2 | 33.6 | | 1319 | | | 1388G4 | | | | |
| #4 | 21.2 | | 1319G4 | | | | | | | |
| #6 | 13.3 | | 1319G6 | | | | | | | |
| | | | | | | | | | | |

NOTE: See website for the most current information.

www.andersonpower.com

| Wire Size | | | | | | | | | | | |
|-----------|------------|----------------------------------|--------------------------------------|--------|---------------------------------------|--------|--------------------|------------------|---|------------------------------------|--|
| AWG | mm² | Auxiliary Contact Part Number | APP Hand Tool w/ Integral Locator | 1 | Mil Std. Hand Tool* M22520/1-01 | | Pneumatic Tool* | Number of Crimps | | Locator for: TM0001 & TP0001 | |
| #12 / 24 | 2.5 / 0.25 | All Crimp Pins | PM1000G1 | O R | TM0001 | O R | TP0001 | Single | + | TL0001 | |
| | | All Crimp Sockets | | | | | | | | TL0002 | |

^{*} TP0001 and TM0001 tools require locators TL0001 for Pins and TL0002 for Sockets. NOTE: See website for the most current information.

