


**Product:** [8777SB](#) 

Audio & Instrumentation, #22-3pr, TC, Individ. Shielded, Shipboard



## Product Description

22 AWG stranded (7x30) tinned copper conductors, twisted pairs, polypropylene insulation, individually Beldfoil® shielded (100% coverage), 22 AWG stranded tinned copper drain wire each pair, LSZH jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	shipboard applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	TC - Tinned Copper	0.03 in	3

Conductor Count:	6
Total Number of Pairs:	3

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.05 in	0.01 in

#### Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

#### Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.031 in	22

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.273 in	0.034 in

### Electrical Characteristics

#### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
10.6 Ohm/1000ft	15 Ohm/1000ft	15 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	55 pF/ft

#### Inductance

Nominal Inductance
--------------------

0.18 µH/ft

#### Impedance

##### Nominal Characteristic Impedance

50 Ohm

#### Current

##### Max. Recommended Current [A]

2 Amps per Conductor at 25°C

#### Voltage

##### UL Voltage Rating

300 V RMS (CMG)

### Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

### Mechanical Characteristics

Bulk Cable Weight:	42 lbs/1000ft
Max. Pull Tension:	79 lbs
Min Bend Radius/Minor Axis:	2.75 in

### Standards

NEC/(UL) Compliance:	CMG-LS
CEC/C(UL) Compliance:	CMG-LS
CPR Euroclass:	Eca
IEEE Compliance:	Std. 45 clause 23
Other Compliance:	UL444, ABS Type Approval Certificate 05-H500072B

### Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-08-01
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray^UL1685 FT4 Loading, Limited Smoke
CSA Flammability:	FT4
IEC Flammability:	60332-1^60332-3-22 (Category A)
IEEE Flammability:	1202
UL voltage rating:	300 V RMS (CMG)

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Part Number

#### Variants

Item #	Color	Putup Type	Length	UPC
8777SB 0101000	Black	Reel	1,000 ft	612825216308

Footnote: C - CRATE REEL PUT-UP.

### History

Update and Revision: Revision Number: 0.265 Revision Date: 08-25-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.