



Part Number: 9L26010

Flat Gray Ribbon Cable 9L260 Series, #26-10c, .050" Pitch

Product Description

Belden .050" pitch gray ribbon cable was designed for general purpose electronic interconnect applications. The cable provides reliable mass-termination to standard IDC connectors.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Material	Construction n x D	No. of Conductors
26	TC - Tinned Copper	Stranded	10

Conductor Count:	10
------------------	----

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.01 in

Color Chart

Number	Color
2	Gray

Color Chart 2

Number
2

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Nominal Wall Thickness
0.039 in

Construction and Dimensions

Cond Spacing Center-Center:	0.05 in
OuterJacket1, Nominal Width:	0.5 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
43 Ohm/1000ft

Capacitance

Element	Nom. Capacitance Conductor to Conductor
@ 1 kHz (GSG)	23 pF/ft

@ 1 MHz (GS)	11 pF/ft
@ 1 MHz (GSG)	18 pF/ft

Inductance

Element	Nominal Inductance
@ 1 MHz (GS)	0.23 μ H/ft
@ 1 MHz (GSG)	0.15 μ H/ft

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
135 Ohm	(GS)
90 Ohm	(GSG)

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
10 MHz	3.9 dB/100ft
20 MHz	6.4 dB/100ft
30 MHz	8.7 dB/100ft
40 MHz	13 dB/100ft
50 MHz	16.9 dB/100ft
60 MHz	20.1 dB/100ft
70 MHz	22.5 dB/100ft
80 MHz	23.9 dB/100ft
90 MHz	25.1 dB/100ft
100 MHz	26.4 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.48 ns/ft	67.60 %

Unbalanced Crosstalk

Element	Typical Unbalanced NEXT %	Typical Unbalanced FEXT %	Typical Cross Talk Pulse Rise Time (ns)
10 ft. sample length	5.2 MHz	6.2 MHz	3 ns
10 ft. sample length	4.2 MHz	5 MHz	5 ns
10 ft. sample length	3.3 MHz	3.8 MHz	7 ns

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
10 MHz	2 dB/100m
20 MHz	
30 MHz	
40 MHz	
50 MHz	
60 MHz	
70 MHz	
80 MHz	
90 MHz	
100 MHz	

Current

Max. Recommended Current [A]
per conductor @ 20°C: 1.5 A

Voltage

Dielectric Withstand Voltage	UL Voltage Rating
2,000 V RMS	300 V RMS

Temperature Range

Operating Temp Range:	-40°C To +105°C
-----------------------	-----------------

Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft
Min Bend Radius During Installation:	2.0 in
Min Bend Radius/Minor Axis:	0.5 in

Standards

UL Rating:	AWM 2651
UL AWM Style:	2651
CSA AWM Specification:	I A

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-07-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length
9L26010 008H100	Gray	612825221517	100 ft
9L26010 008H300	Gray	612825221524	300 ft

Product Notes

Notes:	GS=Ground-Signal Mode; GSG=Ground-Signal-Ground Mode
--------	--

History

Update and Revision:	Revision Number: 0.298 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.