


FSK - 21A - 20 Product Details

[Live Product Chat](#)



FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? 2.54 mm Centerline
- ? Kapton Insulation Material
- ? Insulation Length = 25.40 mm
- ? Pin Arrangement (Left) = A
- ? Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

FSK - 21A - 20

(1437211 - 8)

TE Part Number: 1437211 - 8

[Active](#)

[Add to Part List](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

? [None Available](#)

Catalog Pages/Data Sheets:

? [None Available](#)

Product Specifications:

? [None Available](#)

Application Specifications:

? [None Available](#)

Instruction Sheets:

? [None Available](#)

CAD Files:

? [None Available](#)

Additional Information:

? [Product Line Information](#)

Additional Product Images:

? [Product View](#)

? [Product View](#)

Related Products:

? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Insulation Material](#) = Kapton
- ? [Number of Conductors](#) = 20

Electrical Characteristics:

- ? Current Rating (Amps.) = 3
- ? Impedance (?) = 117
- ? Voltage Rating (VAC) = 300

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Insulation Length \(mm \[in\]\)](#) = 25.40 [1.000]

Configuration Related Features:

- ? [Pin Arrangement \(Left\)](#) = A
- ? [Pin Arrangement \(Right\)](#) = A

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

? Operating Temperature (°C [°F]) = -40 – +150 [-40 – +302]

Other:

? Brand = Tyco Electronics