



DB9M	DB9F
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHIELD	SHIELD



ELECTRICAL TEST:

- 1.100% SHORT,OPEN,MISWIRE TEST
- 2.CONTACTOR RESISTANCE: 2 Ohm (MAX.)
- 3.INSULATION RESISTANCE: 5M Ohm(MIN.)

⑥	THUMB SCREW: #4-40UNC
⑤	OUTER MOLD: PVC 45P COLOR BEIGE
④	INNER MOLD: PVC 65P
③	CONNECTOR: DB9 MALE SOLDER TYPE INSULATION:BLUE
②	CONNECTOR: DB9 FEMALE SOLDER TYPE INSULATION:BLUE
①	CABLE: NOUL 28AWG*9C+AD O.D:5.0MM PVC JACKET COLOR BEIGE(CS-B02)
NO.	DESCRIPTION



ITEM NO

AK131-2-R

TITLE

Serial Extension Cable -
9 Pin, Male <=> Female Molded, 2 Meters

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

© Copyright 2008 by Assmann Electronic Components
All International Rights Reserved