



+ CONNECTORS

DIP SOCKETS



✓ Active

TE CONNECTIVITY (TE)

828-AG11D=SOCKET ASSY

DIPLOMATE | 800 Series

828-AG11D

TE Internal Number: 1437538-4

Not EU RoHS Compliant

Not Yet Reviewed for EU ELV

Contact Style Screw Machine

Number of Positions 28

Profile Standard

Row-to-Row Spacing 15.24 mm [.6 in]

Mounting Angle Vertical

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

DIP SOCKET, 800 SERIES

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Catalog Pages/Data Sheets

DIP Sockets Quick Reference Guide (EN)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Profile Standard

Row-to-Row Spacing 15.24 mm [.6 in]

Leg Style Straight

Product Type Socket

Configuration Features

Number of Positions 28

Number of Rows 2

Electrical Characteristics

Contact Resistance (mΩ) 10

Insulation Resistance (MΩ) 5000

Body Features

Color Black

Frame Style Ladder

Sleeve Plating Material Tin-Lead

Sleeve Material Brass

Contact Features

Contact Style Screw Machine

Contact Mating Area Plating Material Gold

Contact Mating Area Plating Thickness (μin) 25

Solder Tail Contact Plating Material Tin-Lead

Contact Current Rating (Max) (A) 3

Mating Contact Type Four-Fingered

Contact Type Pin

Contact Base Material Beryllium Copper

Socket Style Standard

Socket Type DIP

Termination Features

Contact Termination Type Through Hole
Termination Post Length 3.18 mm [.125 in]

Mechanical Attachment

Mounting Angle Vertical
Mating Alignment With
Mating Alignment Type Polarization
PCB Mount Retention Without

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]
Housing Material Polyester

Dimensions

Height above PC Board 2.67 mm [.105 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 17
Packaging Method Box & Tube, Tube

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
