



## PermaSleeve™ Wire Marking Sleeves

- Flame retardant Permasleeves-excellent for applications requiring self extinguishing sleeve markers
- Meets MIL-23053/5 (Class 1) Standard
- Full circle tube heat-shrinkable Permasleeves available in white polyolefin
- Withstands temperatures ranging from -65°F to 221°F

Approx. Wire Gauge	Range of Wire Diameter		Sleeve Dimensions		Max. Lines of Print	Max. Characters Across		Part#	Price Each
	Min.	Max.	Width	Height		Large	Small		
22-16	.062(1.57)	.110(2.79)	1.0(25.4)	.235(6.0)	1	8	11	PSIDP-111-125	\$56.97
18-12	.094(2.39)	.150(3.81)	1.0(25.4)	.335(8.5)	1	8	11	PSIDP-111-187	\$63.69
16-10	.125(3.18)	.215(5.46)	1.0(25.4)	.439(11.2)	3	8	11	PSIDP-211-250	\$76.83
12-6	.188(4.78)	.320(8.13)	1.0(25.4)	.645(16.4)	3	8	11	PSIDP-311-375	\$113.45

## BradySleeve™ Wire Marking Sleeves

- Exclusive topcoat “soaks up” ink & retains it permanently, without additional curing
- Durable BradySleeve markers stand up to tough conditions 500 per roll

Approx. Wire Gauge	Range of Wire Diameter		Sleeve Dimensions		Max. Lines of Print	Max. Characters Across		Part#	Price Each
	Min.	Max.	Inch (mm) Width	Height		Large	Small		
12-18	.075(1.90)	.13(3.30)	1.0(25.40)	3.5(8.90)	1	7	10	WMS-111-321	\$264.90

## Multiple-Across Wire Marking Strips

- Approx. wire gauge - 10-14

Label Material	Number of Strips Across	Quantity Per Roll Strips/Sets	Label Dimensions Inch (mm)		Maximum Max. Lines of Print	Characters Across		Part#	Price Each
			Width	Height		Large	Small		
Nylon Cloth	2	500-250	.5(12.7)	.75(19.05)	4	3	4	WML-505-499-2S*	\$53.60
White Vinyl Cloth	2	500/250	.5(12.7)	.75(19.05)	4	3	4	WML-505-502-2S*	\$52.13

\*Labels are scored in half, length-wise. The width is only .25"



## Cable Marking Labels

- Self-Laminating transparent vinyl
- Clear overlaminates is ideal for cable marking applications

- Resistant to oil, water and solvents
- Withstands temperatures from -40°F to 150°F
- Excellent for underground wiring

Labels Per Roll	Label Dimensions Inch (mm)		Write-on Area Height	Max. Lines of Print	Max. Characters Across		Part#	Price Each
	Width	Height			Large	Small		
100	1.0(25.4)	2.5(63.5)	.75(19.05)	4	7	10	WML-511-292	\$32.13
100	1.5(38.1)	2.5(63.5)	.75(19.05)	4	10	15	WML-517-292	\$39.83
100	1.0(25.4)	4.0(101.6)	1.0(25.4)	6	7	10	WML-711-292	\$38.04
100	1.5(38.1)	4.0(101.6)	1.0(25.4)	6	10	15	WML-717-292	\$51.65

## Component & General Identification Labels

- Suitable for marking components in control panels, electronic components and circuit boards, faceplates and electrical receptacles
- Available in white vinyl cloth with a printable topcoat
- Withstands temperatures from -40°F to 180°F

- Resistant to oil, water and humidity
- Leaves no adhesive residue when removed
- Ideal for permanent or temporary applications



Label Material	Labels per Roll	Label Dimensions Inch (mm)		Maximum Lines of Print	Max. Characters Across		Part#	Price Each
		Width	Height		Large	Small		
Polyester	500	.5(12.7)	.275(7.0)	1	3	4	CL-105-619	\$32.95
Vinyl Cloth	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-502	\$51.48
Tamper-Proof Vinyl	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-607	\$54.24
Polyester	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-619	\$39.50
Metallized Polyester	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-969	\$52.13
Polyester	500	1.0(25.4)	.275(7.0)	1	10	15	CL-117-619	\$44.94
Vinyl Cloth	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-502	\$63.79
Polyester	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-619	\$48.70
Metallized Polyester	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-969	\$65.41
Polyester	500	1.5(38.1)	.50(12.7)	3	10	15	CL-317-619	\$54.76
Polyester	250	1.5(38.1)	.75(19.05)	4	10	15	CL-517-619	\$37.22
Polyester	250	1.5(38.1)	1.25(31.75)	8	10	15	CL-917-619	\$46.05