# AZ9321\_

## **20 AMP MINIATURE** PC BOARD RELAY

## **FEATURES**

- High performance
- 6kV lightning surge withstand
- Flux tight and sealed versions available
- Class F insulation system standard
- UL, CUR file E44211

#### **CONTACTS**

Arrangement	SPST - N.O. (1 Form A)				
	SPDT (1 Form C)				
Ratings	Form A and C Max. switched power: 480 W or 4700VA Max. switched current: 16A (DC), 20A (AC) Max. switched voltage: 30VDC or 277VAC				
Rated Load					
UL/CUR	1 Form A 20A at 125VAC, Res., 100k cycles [1][2] 17A at 277VAC, Res., 100k cycles [2] 15A at 125VAC, Res., 100k cycles [1][2] 16A at 250VAC, Res., 50k cycles [1] 1HP at 250VAC [1][2] 1HP at 125VAC [2] TV-8 at 125VAC [1]  1 Form C 20A at 125VAC Res. 100k cycles N.O. [1][2] 20A at 125VAC Res. 50k cycles N.C.[2] 20A at 125VAC Res. 17k cycles N.C.[1] 17A at 125VAC Res. 50k cycles N.C.[1] 17A at 277VAC Res. 100k cycles N.O. [2] 15A at 277VAC Res. 50k cycles N.C. [2] 1HP at 250VAC N.O. [1][2] 1HP at 125VAC N.O. [2] 1/2HP at 125VAC N.C. [2] 1/2HP at 277VAC N.C. [2] TV-8 at 125VAC N.O./ N.C. [1]				
Material	Silver nickel [2] or Silver tin oxide [1] (gold plating available)				
Resistance	< 100 milliohms initially (6V, 1A voltage drop method)				



### **GENERAL DATA**

Life Expectancy Mechanical Electrical	1x10 <sup>7</sup> 5 x 10 <sup>4</sup> at 20A, 120VAC Res.			
Operate Time	10ms max.			
Release Time	5ms max. (with no coil suppression)			
Dielectric Strength (at sea level for 1 min.)	3000Vrms contact to coil 1000Vrms across contacts			
Insulation Resistance	100 megohms min. at 500VDC, 50% RH			
Dropout	Greater than 10% of nominal coil voltage			
Ambient Temperature Operating Storage	At nominal coil voltage -40°C(-40°F) to 95°C(203°F) -40°C(-40°F) to 155°C(311°F)			
Vibration	0.062" DA at 10-55 Hz			
Shock	10 g			
Enclosure	P.B.T. polyester			
Terminals	Tinned copper alloy, P.C.			
Max. Solder Temp.	270°C (500°F)			
Max. Solder Time	5 seconds			
Max. Solvent Temp.	80°C (176°F)			
Max. Immersion Time	30 seconds			
Weight (approx.)	14 grams			

#### COIL

Power At Pickup Voltage Max Continuous Dissipation	203mW 1.4W at 20°C (68°F)		
Temperature Rise (at nominal coil voltage)	20°C (36°F)		
Temperature	Max. 155°C (311°F)		

#### **NOTES**

- 1. All values at 20°C (68°F).
- 2. Relay may pull in with less than "Must Operate" value.
- 3. Unsealed relays should not be dip cleaned.
- 4. Specifications subject to change without notice.

# AMERICAN ZETTLER, INC.

www.azettler.com


# **AZ9321**

#### **RELAY ORDERING DATA**

STANDARD RELAYS						
COIL SPECIFICATIONS			ORDER NUMBER*			
Nominal Coil VDC	Max. Continuous VDC	Coil Resistance	Must Operate VDC	1 Form A (SPST-N.O.)	1 Form C (SPDT)	
5	6.0	70 ±10%	3.8	AZ9321-1A-5DF	AZ9321-1C-5DF	
6	7.2	100 ±10%	4.5	AZ9321-1A-6DF	AZ9321-1C-6DF	
9	10.8	225 ±10%	6.8	AZ9321-1A-9DF	AZ9321-1C-9DF	
12	14.4	400 ±10%	9.0	AZ9321-1A-12DF	AZ9321-1C-12DF	
18	21.6	900 ±10%	13.5	AZ9321-1A-18DF	AZ9321-1C-18DF	
24	28.8	1,600 ±15%	18.0	AZ9321-1A-24DF	AZ9321-1C-24DF	
48	57.6	6,400 ±15%	36.0	AZ9321-1A-48DF	AZ9321-1C-48DF	

<sup>\*</sup>Replace "-1A" or "-1C" with "-1AE" or "-1CE" for silver tin oxide contacts. Replace "F" with "EF" for epoxy sealed version. Replace "F" or "EF" with "AF" or "AEF" for gold plated contacts.

### **MECHANICAL DATA**



## AMERICAN ZETTLER, INC.