



**Part Number Code** 

## **WEIGHT**

.40 g/cm (.036 oz/in)

## **MATERIALS AND FINISH**

### Material:

.41 (.016) thick Stainless Steel Type 301, Cond. 1/2 H, ASTM -A240

#### Finish:

Passivated per MILS-5002

# **SPRING RATE**

60.4N/cm (34.5lbs/in) of deflection per spring finger

Coined edges allow smooth insertion and extraction without damage to card	PCB Thickness  1.6 (.063) 2.4 (.094)  Length 31.75 (1.25) to 311.15 (12.25) in 25.4 (1.00) increments Other lengths available on requirements
G Dimension +0.0 (.00) \-0.80 (.03)	Spring fingers hold card against rigid side providing dampening under shock and vibration
1.14 (.045)	Turned in tabs and rigid wall limit card excursion under dynamic loading
1.91 (.075)	graphias of the state of the st

Mounting holes are offset from card path and occur every inch, offering a

# 

# **Part Number Code Example:**

125-06-4.25

Series 125 passivated stainless steel, 107.95 (4.25) long designed for 1.6 (.063) thick printed circuit boards

	Dash No.	PCB Thickness	B Dimension +0.38 (.015) \-0.0 (.000)	G Dimension +0.0 (.00) \-0.80 (.03)
	-06	1.6 (1/16)	1.91 (.075)	1.14 (.045)
	-09	2.4 (3/32)	2.67 (.105)	1.91 (.075)



