


INSTRUMENTATION KNOBS

MATERIAL:


KNOB: Black ABS

INLAY: Spun aluminum with clear coated finish

BUSHING INSERT: Aluminum (Supplied with two set screws)



PART NUMBER		STYLE	KNOB DIA.	SHAFT DIA.	(2) SET SCREW	A +.025/-0.005	ROUND TYPE NUT CLEARANCE			HOLE DEPTH E MIN.	F ±.030	G ±.030	SKIRTED & DIAL NUT CLEARANCE		
WITH INDICATOR	PLAIN						B MIN.	C MIN.	D MAX.				H MIN.	J MIN.	L MAX.
790-1250	790-1255	ROUND	.500	.125	4-40	.505	.435	.026	.158	.405	.510	-	-	-	-
790-1251	790-1256		.700	.250	4-40	.700	.485	.026	.187	.405	.610	-	-	-	-
790-1252	790-1257		.900	.250	8-32	.905	.640	.114	.260	.520	.790	-	-	-	-
790-1253	790-1258		1.250	.250	8-32	1.250	.750	.114	.260	.455	.700	-	-	-	-
790-1260	790-1265	SKIRTED ROUND	.500	.125	4-40	.505	-	-	.158	.405	.510	.150	.360	.177	-
790-1261	790-1266		.700	.250	4-40	.705	-	-	.187	.405	.610	.170	.485	.188	-
790-1262	790-1267		.900	.250	8-32	.905	-	-	.260	.520	.790	.220	.640	.320	-
790-1263	790-1268		1.250	.250	8-32	1.250	-	-	.250	.455	.700	.150	.750	.250	-
790-1270	790-1275	ROUND WITH DIAL	.500	.125	4-40	.505	-	-	.158	.405	.510	.150	.360	.177	.900
790-1271	790-1276		.700	.250	4-40	.700	-	-	.187	.405	.610	.170	.485	.188	1.150
790-1272	790-1277		.900	.250	8-32	.905	-	-	.260	.520	.790	.220	.640	.320	1.525
790-1273	790-1278		1.250	.250	8-32	1.250	-	-	.250	.455	.700	.150	.750	.250	1.860



PART NUMBER		STYLE	KNOB DIA.	SHAFT DIA.	(2) SET SCREW	A +.025/-0.005	ROUND TYPE NUT CLEARANCE			HOLE DEPTH E MIN.	F ±.030	K +.025/-0.005	L	M MAX. MAX.
WITH INDICATOR	PLAIN						B MIN.	C MIN.	D MAX.					
-	790-1280	POINTER	.500	.125	4-40	-	.435	.026	.158	.405	.510	.490	-	-
-	790-1281		.700	.250	4-40	-	.485	.026	.187	.405	.610	.680	-	-
-	790-1282		.900	.250	8-32	-	.640	.114	.260	.520	.790	.885	-	-
790-1283		DOUBLE BAR	.700	.250	4-40	-	.485	.026	.187	.405	.610	-	1.150	-
790-1284			.900	.250	8-32	-	.640	.114	.260	.520	.790	-	1.525	-
790-1285		SINGLE BAR	.500	.125	4-40	.505	.435	.026	.158	.405	.510	-	-	.350
790-1286			.700	.250	4-40	.700	.485	.026	.187	.405	.610	-	-	.460
790-1287			.900	.250	8-32	.905	.640	.114	.260	.520	.790	-	-	.590

