

# Sealed Rocker Switch



## Single (and Double)<sup>1</sup> Pole KS Series

### Features

- Snap-in mounting
- RoHS compliant
- IP56
- 100,000 cycles mechanical life

### Standard Parts<sup>1</sup>


North America and Europe

KSF2ANB1BBD      KSF2BNB1BBB

<sup>1</sup>The part number configuration matrix below provides details to the part numbers above.

For configurable part numbers that are not listed above, not listed in your region, or for custom part numbers, contact the factory or your distributor.

### Part Number Breakdown



## Electrical Specifications

Dielectric Strength	1500 VAC for 1 minute
Insulation Resistance	100 MΩ min at 500 VDC
Initial Contact Resistance	0.050 Ω max

Electrical Ratings:

UL1054:		VDC <sup>3</sup> :
16 A 125 VAC / 10 A 277 VAC ¾ HP 125/277 VAC		21 A 14 VDC


Electrical Life at Rated Load	UL:
Minimum Operations	6,000

<sup>3</sup>DC ratings not agency approved  
UL File No: E23301

## Material and Environmental Specifications

Actuator	Nylon 66 with Glass Fiber
Housing	Nylon 66 94 V-2
Bezel	Nylon 66 with Glass Fiber
Spring	Steel
Contacts	Silver Inlay Copper Alloy
Movable Arm	Silver-Plated Copper Alloy
Terminals	Silver-Plated Copper Alloy
Operating Temperature Range	-20 °C to +85 °C (-4 °F to +185 °F)
Ingress Protection	IP56

## Circuitry and Switch Functions



## Dimensions mm (inches)

