



## 2410SFV3.00FM/125-2 Product Details

[Share](#) | [Print](#) | [Email](#)


2410SFV3.00FM/125-2

TE Internal Number: RF1945-000

Active

### Fuses

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Type = DC/AC Very Fast Acting Chip Fuse
- Surface Mount Construction
- Form Factor (inches) = 2410
- Form Factor (mm) = 6125
- Rated Current = 3 A

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [CP CATALOG 2011-FUSES](#) (PDF, English)

#### Product Specifications:

- [2410SFV Family \(Marked\)](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Family Name = SFV
- UL Listed = File No. E197536

#### Electrical Characteristics:

- Rated Current (A) = 3
- Cold DCR (Nominal) ( $\Omega$ ) = 0.0249
- $I^2t$  ( $A^2sec$ )<sup>2</sup> (Nominal) ( $\Omega$ ) = 1.73
- Interrupt Voltage, Max. (VDC) = 125
- Interrupt Voltage, Max. (VAC) = 125
- Interrupt Current, Max. (A) = 50A@125VAC

#### Termination Features:

- Construction = Surface Mount

#### Body Features:

- Type = DC/AC Very Fast Acting Chip Fuse

#### Configuration Features:

- Form Factor (inches) = 2410
- Form Factor (mm) = 6125

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Environmental:

- Operating Temperature (Max.) ( $^{\circ}C$ ) = 125

#### Conditions for Usage:

- Min Clear Time @ 100% Rated Current (Hr) = 4
- Min Clear Time @ 200% Rated Current (Seconds) = 0.01

#### Other:

- Brand = Raychem

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

