

## Tedlar<sup>®</sup> Adhesive Wire & Cable Labels (B-642)

- **B-642 Material** - Self-extinguishing material used for wire & cable marking applications, particularly in aerospace, defense and mass transit industries.




Diagram	Catalog #	B#	Material	Color	Approx. Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Print-On Height C Inch (mm)	Labels Per Roll	Rec. Ribbon
Fig 32	M71-19-642	B-642	Tedlar	White	12 to 10	1.000 (25.400)	1.000 (25.400)	0.375 (9.530)	250	M71-R4300
Fig 32	M71-31-642	B-642	Tedlar	White	10 to 4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	250	M71-R6200
Fig 32	M71-21-642	B-642	Tedlar	White	25 Pair Copper	1.000 (25.400)	2.500 (63.500)	0.750 (38.1)	100	M71-R6200

Approx. wire gauge based on AWG for THHN wire. **TEDLAR<sup>®</sup>** is a registered trademark of DuPont.

## Self Laminating Wire & Cable Labels (B-427)

- **B-427 Self-Laminating Vinyl Material** - Wire markers with superior chemical and abrasion resistance. Non-printed clear area wraps around to overlaminate the printed text. UL recognized and Rohs compliant.






Diagram	Catalog #	B#	Color	Approx. Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Print-On Height C Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
<b>B-427 Self-Laminating Vinyl Labels</b>										
Fig. 32	M71-10-427	B-427	White	16-10	0.250 (6.350)	0.750 (19.050)	0.375 (9.530)	1	750	M71-R4300
Fig. 32	M71-11-427	B-427	White	16-10	0.500 (12.700)	0.750 (19.050)	0.375 (9.530)	1	500	M71-R4300
Fig. 32	BM71-11-427	B-427	White	16-10	0.500 (12.700)	0.750 (19.050)	0.375 (9.530)	1	5000	M71-R4300
Fig. 32	M71-96-427	B-427	White	16-10	1.000 (25.400)	0.750 (19.050)	0.375 (9.530)	1	250	M71-R4300
Fig. 29	M71-30-427-AW	B-427	White	10-4	1.500 (38.100)	0.750 (19.050)	-	1	250	M71-R4300
Fig. 32	M71-17-427	B-427	White	12-10	0.500 (12.700)	1.000 (25.400)	0.375 (9.530)	1	500	M71-R4300
Fig. 32	BM71-17-427	B-427	White	12-10	0.500 (12.700)	1.000 (25.400)	0.375 (9.530)	1	5000	M71-R4300
Fig. 32	M71-18-427	B-427	White	10-4	0.750 (19.050)	1.000 (25.400)	0.375 (9.530)	1	250	M71-R4300
Fig. 32	BM71-18-427	B-427	White	10-4	0.750 (19.050)	1.000 (25.400)	0.375 (9.530)	1	2500	M71-R4300
Fig. 32	M71-19-427	B-427	White	12-10	1.000 (25.400)	1.000 (25.400)	0.375 (9.530)	1	250	M71-R4300
Fig. 32	BM71-19-427	B-427	White	12-10	1.000 (25.400)	1.000 (25.400)	0.375 (9.530)	1	2500	M71-R4300
Fig. 32	M71-104-427	B-427	White	12-10	1.500 (38.100)	1.000 (25.400)	0.375 (9.530)	1	250	M71-R4300
Fig. 32	M71-103-427	B-427	White	10-4	1.000 (25.400)	1.250 (31.750)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-28-427	B-427	White	10-4	0.250 (6.350)	1.500 (38.100)	0.500 (12.700)	1	750	M71-R4300
Fig. 32	M71-29-427	B-427	White	10-4	0.500 (12.700)	1.500 (38.100)	0.500 (12.700)	1	500	M71-R4300
Fig. 32	BM71-29-427	B-427	White	10-4	0.500 (12.700)	1.500 (38.100)	0.500 (12.700)	1	5000	M71-R4300
Fig. 32	M71-30-427	B-427	White	10-4	0.750 (19.050)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	BM71-30-427	B-427	White	10-4	0.750 (19.050)	1.500 (38.100)	0.500 (12.700)	1	2500	M71-R4300
Fig. 32	M71-31-427	B-427	White	10-4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	BM71-31-427	B-427	White	10-4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	1	2500	M71-R4300
Fig. 32	M71-32-427	B-427	White	10-4	1.500 (38.100)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	BM71-32-427	B-427	White	10-4	1.500 (38.100)	1.500 (38.100)	0.500 (12.700)	1	1000	M71-R4300
Fig. 32	M71-88-427	B-427	White	10-4	1.750 (44.450)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-107-427	B-427	White	10-4	2.000 (50.800)	1.500 (38.100)	0.500 (12.700)	1	100	M71-R4300
Fig. 32	BM71-107-427	B-427	White	10-4	2.000 (50.800)	1.500 (38.100)	0.500 (12.700)	1	1000	M71-R4300
Fig. 32	M71-21-427	B-427	White	Cables	1.000 (25.400)	2.500 (63.500)	0.750 (19.050)	1	100	M71-R4300
Fig. 32	BM71-21-427	B-427	White	Cables	1.000 (25.400)	2.500 (63.500)	0.750 (19.050)	1	1000	M71-R4300
Fig. 32	M71-66-427	B-427	White	Cables	1.938 (49.230)	3.150 (80.000)	1.000 (25.400)	1	100	M71-R4300
Fig. 43	M71-64-427	B-427	White	Cables	1.000 (25.400)	3.375 (85.730)	1.125 (28.580)	1	100	M71-R4300
Fig. 43	BM71-64-427	B-427	White	Cables	1.000 (25.400)	3.375 (85.730)	1.125 (28.580)	1	1000	M71-R4300
Fig. 32	M71-23-427	B-427	White	Cables	1.000 (25.400)	4.000 (101.600)	1.000 (25.400)	1	100	M71-R4300
Fig. 32	BM71-23-427	B-427	White	Cables	1.000 (25.400)	4.000 (101.600)	1.000 (25.400)	1	1000	M71-R4300
Fig. 32	M71-109-427	B-427	White	Cables	1.500 (38.100)	4.000 (101.600)	1.500 (38.100)	1	100	M71-R4300
Fig. 32	M71-33-427	B-427	White	Cables	1.500 (38.100)	4.000 (101.600)	1.000 (25.400)	1	100	M71-R4300
Fig. 32	BM71-109-427	B-427	White	Cables	1.500 (38.100)	4.000 (101.600)	1.500 (38.100)	1	500	M71-R4300
Fig. 32	BM71-33-427	B-427	White	Cables	1.500 (38.100)	4.000 (101.600)	1.000 (25.400)	1	500	M71-R4300
Fig. 32	M71-34-427	B-427	White	Cables	1.500 (38.100)	6.000 (152.400)	1.500 (38.100)	1	50	M71-R4300
Fig. 32	BM71-34-427	B-427	White	Cables	1.500 (38.100)	6.000 (152.400)	1.500 (38.100)	1	500	M71-R4300
Fig. 32	M71-19-427-YL	B-427	Yellow	12-10	1.000 (25.400)	1.000 (25.400)	0.375 (9.530)	1	250	M71-R4300
Fig. 32	M71-31-427-YL	B-427	Yellow	10-4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-32-427-YL	B-427	Yellow	10-4	1.500 (38.100)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-21-427-YL	B-427	Yellow	Cables	1.000 (25.400)	2.500 (63.500)	0.750 (19.050)	1	100	M71-R4300
Fig. 32	M71-33-427-YL	B-427	Yellow	Cables	1.500 (38.100)	4.000 (101.600)	1.000 (25.400)	1	100	M71-R4300
Fig. 32	M71-30-427-BL	B-427	Blue	10-4	0.750 (19.050)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-30-427-PL	B-427	Purple	10-4	0.750 (19.050)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-31-427-GN	B-427	Green	10-4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-30-427-RD	B-427	Red	10-4	0.750 (19.050)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300
Fig. 32	M71-31-427-RD	B-427	Red	10-4	1.000 (25.400)	1.500 (38.100)	0.500 (12.700)	1	250	M71-R4300

\* Approx. wire gauge based on AWG for THHN wire.