

## ASMD030F-2 Product Details



ASMD030F-2

TE Internal Number: RF1631-000

 [Active](#)

### PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Automotive, Surface Mount Application
- Vmax Operating = 60 V
- Imax = 10 A
- Family Name = ASMD
- Surface Mount Construction

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [ASMD030F](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Electrical Characteristics:

- [Vmax Operating \(V\)](#) = 60
- [Imax \(A\)](#) = 10
- [IH \(Room Temperature\) \(A\)](#) = 0.23
- [IT \(Room Temperature\) \(A\)](#) = 0.59
- [Rmin \(Ω\)](#) = 0.98
- [R1 Max \[Post Trip\] \(Ω\)](#) = 4.80
- Power Dissipation (Typical) (W) = 1.10

#### Termination Related Features:

- Construction = Surface Mount

#### Contact Related Features:

- [Family Name](#) = ASMD

#### Configuration Related Features:

- [Form Factor \(inches\)](#) = 2920
- [Form Factor \(mm\)](#) = 7555

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

#### Operation/Application:


- Application = Automotive, Surface Mount

#### Packaging Related Features:

- Packaging Method = Tape & Reel

#### Other:

- Brand = Raychem

 [BOOKMARK](#) 

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

