

PART NUMBER	LENGTH INCHES	+/- LENGTH	LENGTH CM	MAX VSWR :1 @ 18GHz.	MAX INSERTION LOSS [dB] @ 18GHz
1-3636-600-5206	06	0.25	15.2	1.30	0.79
1-3636-600-5209	09	0.25	22.9	1.30	1.08
1-3636-600-5212	12	0.25	30.5	1.30	1.37
1-3636-600-5215	15	0.15	38.1	1.30	1.67
1-3636-600-5218	18	0.18	45.7	1.30	1.96
1-3636-600-5221	21	0.21	53.3	1.30	2.25
1-3636-600-5224	24	0.24	61.0	1.30	2.54
1-3636-600-5227	27	0.27	68.6	1.35	2.83
1-3636-600-5230	30	0.30	76.2	1.35	3.12
1-3636-600-5233	33	0.33	83.8	1.35	3.42
1-3636-600-5236	36	0.36	91.4	1.35	3.71
1-3636-600-5239	39	0.39	99.1	1.40	4.00
1-3636-600-5242	42	0.42	106.7	1.40	4.29
1-3636-600-5245	45	0.45	114.3	1.40	4.58
1-3636-600-5248	48	0.48	121.9	1.40	4.87
1-3636-600-5251	51	0.51	129.5	1.40	5.17
1-3636-600-5254	54	0.54	137.2	1.40	5.46
1-3636-600-5257	57	0.57	144.8	1.40	5.75
1-3636-600-5260	60	0.60	152.4	1.40	6.04
1-3636-600-5263	63	0.63	160.0	1.40	6.33
1-3636-600-5266	66	0.66	167.6	1.40	6.62
1-3636-600-5269	69	0.69	175.3	1.40	6.91
1-3636-600-5272	72	0.72	182.9	1.40	7.21
1-3636-600-5275	75	0.75	190.5	1.40	7.50
1-3636-600-5278	78	0.78	198.1	1.40	7.79
1-3636-600-5281	81	0.81	205.7	1.40	8.08
1-3636-600-5284	84	0.84	213.4	1.40	8.37
1-3636-600-5287	87	0.87	221.0	1.40	8.66
1-3636-600-5290	90	0.90	228.6	1.40	8.96
1-3636-600-5293	93	0.93	236.2	1.40	9.25
1-3636-600-5296	96	0.96	243.8	1.40	9.54
1-3636-600-5299	99	0.99	251.5	1.40	9.83
2-3636-600-5209	108	1.08	274.3	1.40	10.71
2-3636-600-5210	120	1.20	304.8	1.40	11.87
2-3636-600-5215	180	1.80	457.2	1.40	17.71

ASSEMBLIES ELECTRICAL & MECHANICAL SPECIFICATIONS	
IMPEDANCE, NOMINAL:	50 OHMS
CABLE VELOCITY OF PROPAGATION, NOMINAL	70.7 %
CABLE MAX. DIAMETER:	0.089 INCHES
MINIMUM BEND RADIUS:	0.13 INCHES
TEMPERATURE RANGE:	-50 to +105 DEGREES C
MATING TORQUE:	7-10 INCH POUNDS

NOTES:

NO MARKER IS REQUIRED FOR CABLE LESS THAN 4.0\"/>

ASSEMBLY LENGTHS NOT LISTED ABOVE WILL HAVE THE SAME INSERTION LOSS AND VSWR LIMITS AS THE NEXT LONGER ASSEMBLY SHOWN IN THE TABLE ABOVE.



EXAMPLE: 1-3636-600-5222 WILL HAVE THE SAME INSERTION LOSS AND VSWR LIMITS AS 1-3636-600-5224.

MAXIMUM SPECIFICATIONS ARE PRODUCT MAXIMUM INCLUDING MEASURING SYSTEM UNCERTAINTY.


NOTE: PRODUCT SPECIFICATIONS ARE VERIFIED AT 73 DEG. F, SEA LEVEL AND 20 TO 80% RELATIVE HUMIDITY.

NOTE: FOR CABLES OVER 120 INCHES LONG AND/OR INSERTION LOSSES IN EXCESS OF 20DB THE VSWR AND INSERTION LOSS VALUES ARE TYPICAL ONLY.

VISIT OUR WEB SITE AT <http://www.carlisleit.com>



ELECTRICAL SPECIFICATIONS table with columns for IMPEDANCE, CAPACITANCE, VELOCITY, etc.



NOTE: NO MARKER IS REQUIRED FOR 6.0" OR LESS


MECHANICAL SPECIFICATIONS table with columns for CABLE MAX. DIAMETER, MIN. BEND RADIUS, etc.

MATERIALS AND FINISHES table with columns for DESCRIPTION, MATERIAL, FINISH OR COLOR.

Main data table with columns: ITEM INFORMATION, MECHANICAL CHARACTERISTICS, S11 AND S22 CHARACTERISTICS, S12 AND S21 CHARACTERISTICS, LENGTH CM.

NOTE: PRODUCT SPECIFICATIONS ARE VERIFIED AT 73 DEG. F. SEA LEVEL AND 20 TO 80% RELATIVE HUMIDITY. INCLUDING MEASURING SYSTEM UNCERTAINTY.

ELECTRICAL SPECIFICATIONS	
IMPEDANCE, NOMINAL:	50 OHMS
CAPACITANCE NOMINAL:	28.7 pF/FOOT
VELOCITY OF PROPAGATION, NOMINAL:	70.7 %
RELATIVE SHIELDING:	-100 db MIN.
INSULATION RESISTANCE:	1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE:	1000 VRMS MIN.
ELECTRICAL DELAY NOMINAL:	1.44 ns/FOOT
ELECTRICAL DELAY NOMINAL:	120 ps/INCH
MAX. PULSE RF POWER:	1250 WATTS
(INTO A 50 OHM SYSTEM, WITH DUTY CYCLE LESS THAN CW RATING)	
F (IN GHz) ----->	1 2 4 6 12 18
MAX. CW WATTS -->	200 136 91 71 46 36



NOTE: NO MARKERS REQUIRED ON CABLES LESS THAN 6 INCHES.

MECHANICAL SPECIFICATIONS:	
CABLE MAX. DIAMETER:	0.141 INCHES
MIN. BEND RADIUS:	0.19 INCHES
PREFERRED BEND RADIUS:	0.50 INCHES
CONNECTOR RETENTION:	50 POUNDS MIN.
TEMPERATURE RANGE:	-50 to +105 DEGREES C
MATING TORQUE:	7-10 INCH POUNDS
CONNECTOR INTERFACE:	MIL-STD-348 PAGE 310.3

MATERIALS AND FINISHES		
DESCRIPTION	MATERIAL	FINISH OR COLOR
CABLE JACKET:	HIGH STRENGTH WIRE BRAID	TIN FILLED
MARKER:	MIL-I-23053/5	GRAY / BLACK
RoHS MARKER:	MIL-I-23053/5	GREEN
SMA BODY:	ASTM-A-582, 303 STAINLESS STEEL	MIL-G-45204 GOLD PLATED
SMA NUT:	ASTM-A-582, 303 STAINLESS STEEL	QQ-P-35 PASSIVATED
SMA CAP:	ASTM-A-582, 303 STAINLESS STEEL	QQ-P-35 PASSIVATED
SMA GASKET:	ZZ-R-765, SILICON RUBBER	NONE
SOLVENTS:	NO OZONE DEPLETING MATERIALS ARE USED	

PART NUMBER	LENGTH INCHES	+ - LENGTH	WEIGHT OUNCES	MAXIMUM VSWR :1 AT FREQUENCY (IN GHz.)								MAXIMUM INSERTION LOSS IN dB AT FREQ. (IN GHz.)								NOM DELAY nS	LENGTH CM
				UP TO 1	1 TO 2	2 TO 4	4 TO 6	6 TO 12	12 TO 18	UP TO 1	1 TO 2	2 TO 4	4 TO 6	6 TO 12	12 TO 18						
1-3737-601- 3202	2.00	0.05	0.3	1.10	1.15	1.20	1.25	1.30	1.35	0.10	0.13	0.19	0.22	0.32	0.41	0.24	5.08				
1-3737-601- 3203	3.00	0.05	0.4	1.10	1.15	1.20	1.25	1.30	1.35	0.11	0.15	0.21	0.25	0.36	0.48	0.36	7.62				
1-3737-601- 3204	4.00	0.05	0.4	1.10	1.15	1.20	1.25	1.30	1.35	0.12	0.16	0.24	0.28	0.41	0.54	0.48	10.2				
1-3737-601- 3205	5.00	0.05	0.4	1.10	1.15	1.20	1.25	1.30	1.35	0.13	0.18	0.26	0.31	0.46	0.60	0.60	12.7				
1-3737-601- 3206	6.00	0.10	0.5	1.10	1.15	1.20	1.25	1.30	1.35	0.15	0.20	0.28	0.34	0.50	0.66	0.72	15.2				
1-3737-601- 3207	7.00	0.10	0.5	1.10	1.15	1.20	1.25	1.30	1.35	0.16	0.21	0.31	0.38	0.55	0.72	0.84	17.8				
1-3737-601- 3208	8.00	0.10	0.5	1.10	1.15	1.20	1.25	1.30	1.35	0.17	0.23	0.33	0.41	0.60	0.78	0.96	20.3				
1-3737-601- 3209	9.00	0.10	0.6	1.10	1.15	1.20	1.25	1.30	1.35	0.18	0.24	0.35	0.44	0.64	0.84	1.08	22.9				
1-3737-601- 3210	10.0	0.10	0.6	1.10	1.15	1.20	1.25	1.30	1.35	0.19	0.26	0.38	0.47	0.69	0.90	1.20	25.4				
1-3737-601- 3211	11.0	0.15	0.6	1.10	1.15	1.20	1.25	1.30	1.35	0.20	0.28	0.40	0.50	0.74	0.96	1.32	27.9				
1-3737-601- 3212	12.0	0.15	0.7	1.10	1.15	1.20	1.25	1.30	1.35	0.21	0.29	0.43	0.53	0.78	1.02	1.44	30.5				
1-3737-601- 3213	13.0	0.15	0.7	1.10	1.15	1.20	1.25	1.30	1.35	0.22	0.31	0.45	0.56	0.83	1.08	1.56	33.0				
1-3737-601- 3214	14.0	0.15	0.7	1.10	1.15	1.20	1.25	1.30	1.35	0.23	0.32	0.47	0.59	0.88	1.15	1.68	35.6				
1-3737-601- 3215	15.0	0.15	0.8	1.10	1.15	1.20	1.25	1.30	1.35	0.24	0.34	0.50	0.62	0.92	1.21	1.80	38.1				
1-3737-601- 3216	16.0	0.20	0.8	1.10	1.15	1.20	1.25	1.30	1.35	0.25	0.36	0.52	0.65	0.97	1.27	1.92	40.6				
1-3737-601- 3217	17.0	0.20	0.8	1.10	1.15	1.20	1.25	1.30	1.35	0.26	0.37	0.55	0.68	1.02	1.33	2.04	43.2				
1-3737-601- 3218	18.0	0.20	0.9	1.10	1.15	1.20	1.25	1.30	1.35	0.28	0.39	0.57	0.71	1.06	1.39	2.16	45.7				
1-3737-601- 3220	20.0	0.20	0.9	1.10	1.15	1.20	1.25	1.30	1.35	0.30	0.42	0.62	0.77	1.16	1.51	2.40	50.8				
1-3737-601- 3221	21.0	0.20	1.0	1.10	1.15	1.20	1.25	1.30	1.35	0.31	0.44	0.64	0.80	1.20	1.57	2.52	53.3				
1-3737-601- 3222	24.0	0.24	1.0	1.10	1.15	1.20	1.25	1.30	1.35	0.34	0.48	0.71	0.89	1.35	1.75	2.88	61.0				
1-3737-601- 3225	25.0	0.25	1.1	1.10	1.15	1.20	1.25	1.30	1.35	0.35	0.50	0.74	0.92	1.39	1.82	3.00	63.5				
1-3737-601- 3226	26.0	0.26	1.1	1.10	1.15	1.20	1.25	1.30	1.35	0.36	0.52	0.76	0.95	1.44	1.88	3.12	66.0				
1-3737-601- 3227	27.0	0.27	1.1	1.10	1.15	1.20	1.25	1.30	1.35	0.37	0.53	0.78	0.98	1.49	1.94	3.24	68.6				
1-3737-601- 3228	28.0	0.28	1.2	1.10	1.15	1.20	1.25	1.30	1.35	0.38	0.55	0.81	1.01	1.53	2.00	3.36	71.1				
1-3737-601- 3229	29.0	0.29	1.2	1.10	1.15	1.20	1.25	1.30	1.35	0.39	0.56	0.83	1.04	1.58	2.06	3.48	73.7				
1-3737-601- 3232	32.0	0.32	1.3	1.10	1.15	1.20	1.25	1.30	1.35	0.43	0.61	0.90	1.13	1.72	2.24	3.83	81.3				
1-3737-601- 3236	36.0	0.36	1.4	1.10	1.15	1.20	1.25	1.30	1.35	0.47	0.68	1.00	1.26	1.91	2.48	4.31	91.4				
1-3737-601- 3240	40.0	0.40	1.6	1.15	1.20	1.25	1.30	1.35	1.40	0.51	0.74	1.09	1.38	2.09	2.73	4.79	102				
1-3737-601- 3244	44.0	0.44	1.7	1.15	1.20	1.25	1.30	1.35	1.40	0.56	0.80	1.19	1.50	2.28	2.97	5.27	112				
1-3737-601- 3248	48.0	0.48	1.8	1.15	1.20	1.25	1.30	1.35	1.40	0.60	0.87	1.28	1.62	2.47	3.22	5.75	122				
1-3737-601- 3249	49.0	0.49	1.8	1.15	1.20	1.25	1.30	1.35	1.40	0.61	0.88	1.31	1.65	2.51	3.28	5.87	124				
1-3737-601- 3252	52.0	0.52	1.9	1.15	1.20	1.25	1.30	1.35	1.40	0.64	0.93	1.38	1.74	2.65	3.46	6.23	132				
1-3737-601- 3256	56.0	0.56	2.1	1.15	1.20	1.25	1.30	1.35	1.40	0.69	0.99	1.47	1.86	2.84	3.70	6.71	142				
1-3737-601- 3260	60.0	0.60	2.2	1.15	1.20	1.25	1.30	1.35	1.40	0.73	1.06	1.57	1.99	3.03	3.95	7.19	152				
1-3737-601- 3264	64.0	0.64	2.3	1.15	1.20	1.25	1.30	1.35	1.40	0.77	1.12	1.67	2.11	3.21	4.19	7.67	163				
1-3737-601- 3268	68.0	0.68	2.5	1.20	1.25	1.30	1.35	1.40	1.45	0.82	1.19	1.76	2.23	3.40	4.43	8.15	173				
1-3737-601- 3272	72.0	0.72	2.6	1.20	1.25	1.30	1.35	1.40	1.45	0.86	1.25	1.86	2.35	3.59	4.68	8.63	183				
1-3737-601- 3276	76.0	0.76	2.7	1.20	1.25	1.30	1.35	1.40	1.45	0.90	1.31	1.95	2.47	3.78	4.92	9.11	193				
1-3737-601- 3280	80.0	0.80	2.8	1.20	1.25	1.30	1.35	1.40	1.45	0.95	1.38	2.05	2.59	3.96	5.16	9.59	203				
1-3737-601- 3284	84.0	0.84	3.0	1.20	1.25	1.30	1.35	1.40	1.45	0.99	1.44	2.14	2.71	4.15	5.41	10.1	213				
1-3737-601- 3288	88.0	0.88	3.1	1.20	1.25	1.30	1.35	1.40	1.45	1.03	1.51	2.24	2.84	4.34	5.65	10.5	224				
1-3737-601- 3292	92.0	0.92	3.2	1.20	1.25	1.30	1.35	1.40	1.45	1.08	1.57	2.33	2.96	4.52	5.90	11.0	234				
1-3737-601- 3296	96.0	0.96	3.4	1.20	1.25	1.30	1.35	1.40	1.45	1.12	1.63	2.43	3.08	4.71	6.14	11.5	244				
2-3737-601- 3210	120	1.2	4.1	1.20	1.25	1.30	1.35	1.40	1.45	1.38	2.02	3.00	3.81	5.83	7.60	14.4	305				
2-3737-601- 3215	180	1.8	6.0	1.20	1.25	1.30	1.35	1.40	1.45	2.03	2.97	4.43	5.63	8.64	11.3	21.6	457				
2-3737-601- 3220	240	2.4	8.0	1.20	1.25	1.30	1.35	1.40	1.45	2.68	3.93	5.86	7.45	11.4	14.9	28.8	610				
2-3737-601- 3225	300	3.0	9.9	1.20	1.25	1.30	1.35	1.40	1.45	3.33	4.89	7.29	9.28	14.3	18.6	36.0	762				

D = DISTRIBUTOR ITEM MAXIMUM SPECIFICATIONS ARE PRODUCT MAXIMUM PLUS MEASURING SYSTEM UNCERTAINTY.

NOTE: ALL SPECIFICATIONS APPLY AT 73 DEG. F. SEA LEVEL AND 20 TO 80% RELATIVE HUMIDITY.


PRODUCT SPECIFICATIONS APPLY AT 5 TO 99% (NON CONDENSING) RELATIVE HUMIDITY, CONSULT FACTORY FOR PRODUCT CHARACTERISTICS AT OTHER CONDITIONS.

THESE ASSEMBLIES ARE ALSO AVAILABLE IN RoHS COMPLIANT VERSIONS. TO ORDER, REPLACE THE "1" PREFIX WITH A "Y" OR REPLACE THE "2" PREFIX WITH A "Z".

SEMI-FLEX IS A REGISTERED TRADEMARK OF TENSOLITE CO.

VISIT OUR WEB SITE AT <http://www.tensolite.com>

ELECTRICAL SPECIFICATIONS	
IMPEDANCE, NOMINAL:	50 OHMS
CAPACITANCE NOMINAL:	25.4 pF/FOOT
VELOCITY OF PROPAGATION, NOMINAL:	80.0 %
RELATIVE SHIELDING:	<-90 dB MIN.
INSULATION RESISTANCE:	1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE:	1000 VRMS MIN.
ELECTRICAL DELAY:	1.27 ns/FOOT
ELECTRICAL DELAY:	106 ps/INCH
MAX. PULSE RF POWER:	1250 WATTS
(INTO A 50 OHM SYSTEM, WITH DUTY CYCLE LESS THAN CW RATING)	
F (IN GHz) ----->	1 2 4 6 12 18
MAX. CW WATTS ---->	299 210 147 119 83 67



MECHANICAL SPECIFICATIONS:	
CABLE MAX. DIAMETER:	0.200 INCHES
MIN. BEND RADIUS:	1.17 INCHES
PREFERRED BEND RADIUS:	3.90 INCHES
CONNECTOR RETENTION:	60 POUNDS MIN.
TEMPERATURE RANGE:	-65 to +105 DEGREES C
MATING TORQUE:	7-10 SMA 10-15 N INCH POUNDS
CONNECTOR INTERFACES:	MIL-STD-348 (N WITH SOLID OUTER)

MATERIALS AND FINISHES		
DESCRIPTION	MATERIAL	FINISH OR COLOR
CABLE JACKET:	L-P-389 FEP	GREY TINT
MARKER :	MIL-I-23053/5	WHITE / BLACK MARKING
BOOT:	MIL-I-23053/4	BLACK
CONTACTS:	ASTM-B-196, BeCu	MIL-G-45204, GOLD PLATED
INSULATORS:	ASTM-D-1710, PTFE	NONE
SMA BODY	ASTM-A-582, STAINLESS STEEL	QQ-P-35, PASSIVATED
SMA NUT	ASTM-A-582, STAINLESS STEEL	QQ-P-35, PASSIVATED
TYPE N BODY:	ASTM-B-16, BRASS	QQ-S-365, SILVER PLATED
TYPE N NUT:	ASTM-B-16, BRASS	QQ-N-290, NICKEL PLATED
GASKETS:	ZZ-R-765, SILICON RUBBER	RED
SOLVENTS:	NO OZONE DEPLETING MATERIALS ARE USED	

ITEM INFORMATION PART NUMBER	MECHANICAL CHARACTERISTICS			S11 AND S22 CHARACTERISTICS							S21 AND S12 CHARACTERISTICS							LENGTH CM
	LENGTH INCHES	+ / - LENGTH	WEIGHT OUNCES	MAXIMUM VSWR :1 AT FREQUENCY (IN GHz.)							MAXIMUM INSERTION LOSS IN dB AT FREQ. (IN GHz.)							
				UP TO 1	1 TO 2	2 TO 4	4 TO 6	6 TO 12	12 TO 18	UP TO 1	1 TO 2	2 TO 4	4 TO 6	6 TO 12	12 TO 18	NOM DELAY nS		
1-1836-301-3206	6.00	0.25	1.5	1.15	1.18	1.20	1.25	1.30	1.50	0.15	0.21	0.29	0.35	0.49	0.63	0.64	15.2	
1-1836-301-3207	7.00	0.25	1.6	1.15	1.18	1.20	1.25	1.30	1.50	0.16	0.22	0.31	0.37	0.52	0.66	0.74	17.8	
1-1836-301-3208	8.00	0.25	1.6	1.15	1.18	1.20	1.25	1.30	1.50	0.17	0.23	0.32	0.39	0.55	0.70	0.85	20.3	
1-1836-301-3209	9.00	0.25	1.7	1.15	1.18	1.20	1.25	1.30	1.50	0.18	0.24	0.34	0.41	0.58	0.73	0.95	22.9	
1-1836-301-3210	10.00	0.25	1.7	1.15	1.18	1.20	1.25	1.30	1.50	0.18	0.25	0.35	0.43	0.60	0.76	1.06	25.4	
1-1836-301-3211	11.00	0.25	1.8	1.15	1.18	1.20	1.25	1.30	1.50	0.19	0.26	0.37	0.44	0.63	0.80	1.16	27.9	
1-1836-301-3212	12.00	0.25	1.8	1.15	1.18	1.20	1.25	1.30	1.50	0.20	0.27	0.38	0.46	0.66	0.83	1.27	30.5	
1-1836-301-3213	13.00	0.25	1.9	1.15	1.18	1.20	1.25	1.30	1.50	0.21	0.28	0.40	0.48	0.69	0.87	1.38	33.0	
1-1836-301-3214	14.00	0.25	1.9	1.15	1.18	1.20	1.25	1.30	1.50	0.21	0.29	0.41	0.50	0.71	0.90	1.48	35.6	
1-1836-301-3215	15.00	0.25	2.0	1.15	1.18	1.20	1.25	1.30	1.50	0.22	0.30	0.43	0.52	0.74	0.94	1.59	38.1	
1-1836-301-3216	16.00	0.25	2.1	1.15	1.18	1.20	1.25	1.30	1.50	0.23	0.31	0.45	0.54	0.77	0.97	1.69	40.6	
1-1836-301-3217	17.00	0.25	2.1	1.15	1.18	1.20	1.25	1.30	1.50	0.24	0.32	0.46	0.56	0.80	1.01	1.80	43.2	
1-1836-301-3218	18.00	0.25	2.2	1.15	1.18	1.20	1.25	1.30	1.50	0.24	0.34	0.48	0.58	0.82	1.04	1.91	45.7	
1-1836-301-3219	19.00	0.25	2.2	1.15	1.18	1.20	1.25	1.30	1.50	0.25	0.35	0.49	0.60	0.85	1.07	2.01	48.3	
1-1836-301-3220	20.00	0.25	2.3	1.15	1.18	1.20	1.25	1.30	1.50	0.26	0.36	0.51	0.62	0.88	1.11	2.12	50.8	
1-1836-301-3221	21.00	0.25	2.3	1.15	1.18	1.20	1.25	1.30	1.50	0.27	0.37	0.52	0.64	0.91	1.14	2.22	53.3	
1-1836-301-3222	22.00	0.25	2.4	1.15	1.18	1.20	1.25	1.30	1.50	0.27	0.38	0.54	0.65	0.93	1.18	2.33	55.9	
1-1836-301-3223	23.00	0.25	2.4	1.15	1.18	1.20	1.25	1.30	1.50	0.28	0.39	0.55	0.67	0.96	1.21	2.44	58.4	
1-1836-301-3224 F	24.00	0.25	2.5	1.15	1.18	1.20	1.25	1.30	1.50	0.29	0.40	0.57	0.69	0.99	1.25	2.54	61.0	
1-1836-301-3225	25.00	0.25	2.5	1.15	1.18	1.20	1.25	1.30	1.50	0.30	0.41	0.58	0.71	1.02	1.28	2.65	63.5	
1-1836-301-3226	26.00	0.26	2.6	1.15	1.18	1.20	1.25	1.30	1.50	0.30	0.42	0.60	0.73	1.04	1.32	2.75	66.0	
1-1836-301-3227	27.00	0.27	2.6	1.15	1.18	1.20	1.25	1.30	1.50	0.31	0.43	0.61	0.75	1.07	1.35	2.86	68.6	
1-1836-301-3228	28.00	0.28	2.7	1.15	1.18	1.20	1.25	1.30	1.50	0.32	0.44	0.63	0.77	1.10	1.39	2.97	71.1	
1-1836-301-3229	29.00	0.29	2.7	1.15	1.18	1.20	1.25	1.30	1.50	0.33	0.45	0.64	0.79	1.13	1.42	3.07	73.7	
1-1836-301-3230	30.00	0.30	2.8	1.15	1.18	1.20	1.25	1.30	1.50	0.33	0.46	0.66	0.81	1.15	1.45	3.18	76.2	
1-1836-301-3231	31.00	0.31	2.9	1.15	1.18	1.20	1.25	1.30	1.50	0.34	0.47	0.68	0.83	1.18	1.49	3.28	78.7	
1-1836-301-3232	32.00	0.32	2.9	1.15	1.18	1.20	1.25	1.30	1.50	0.35	0.48	0.69	0.84	1.21	1.52	3.39	81.3	
1-1836-301-3233	33.00	0.33	3.0	1.15	1.18	1.20	1.25	1.30	1.50	0.36	0.50	0.71	0.86	1.24	1.56	3.49	83.8	
1-1836-301-3234	34.00	0.34	3.0	1.15	1.18	1.20	1.25	1.30	1.50	0.36	0.51	0.72	0.88	1.26	1.59	3.60	86.4	
1-1836-301-3235	35.00	0.35	3.1	1.15	1.18	1.20	1.25	1.30	1.50	0.37	0.52	0.74	0.90	1.29	1.63	3.71	88.9	
1-1836-301-3236 F	36.00	0.36	3.1	1.15	1.18	1.20	1.25	1.30	1.50	0.38	0.53	0.75	0.92	1.32	1.66	3.81	91.4	
1-1836-301-3239	39.00	0.39	3.3	1.15	1.18	1.20	1.25	1.30	1.50	0.40	0.56	0.80	0.98	1.40	1.76	4.13	99.1	
1-1836-301-3242	42.00	0.42	3.4	1.15	1.18	1.20	1.25	1.30	1.50	0.42	0.59	0.84	1.03	1.49	1.87	4.45	106.7	
1-1836-301-3248	48.00	0.48	3.8	1.15	1.18	1.20	1.25	1.30	1.50	0.47	0.66	0.94	1.15	1.65	2.07	5.08	121.9	
1-1836-301-3254	54.00	0.54	4.1	1.20	1.22	1.25	1.30	1.40	1.50	0.51	0.72	1.03	1.26	1.82	2.28	5.72	137.2	
1-1836-301-3260	60.00	0.60	4.4	1.20	1.22	1.25	1.30	1.40	1.50	0.56	0.78	1.12	1.38	1.98	2.49	6.35	152.4	
1-1836-301-3264	64.00	0.64	4.6	1.20	1.22	1.25	1.30	1.40	1.50	0.59	0.83	1.18	1.45	2.09	2.63	6.78	162.6	
1-1836-301-3266	66.00	0.66	4.7	1.20	1.22	1.25	1.30	1.40	1.50	0.60	0.85	1.21	1.49	2.15	2.70	6.99	167.6	
1-1836-301-3272	72.00	0.72	5.0	1.20	1.22	1.25	1.30	1.40	1.50	0.65	0.91	1.30	1.60	2.31	2.90	7.63	182.9	
1-1836-301-3278	78.00	0.78	5.4	1.20	1.22	1.25	1.30	1.40	1.50	0.69	0.98	1.40	1.72	2.48	3.11	8.26	198.1	
1-1836-301-3284	84.00	0.84	5.7	1.20	1.22	1.25	1.30	1.40	1.50	0.74	1.04	1.49	1.83	2.64	3.32	8.90	213.4	
1-1836-301-3290	90.00	0.90	6.0	1.20	1.22	1.25	1.30	1.40	1.50	0.78	1.10	1.58	1.95	2.81	3.52	9.53	228.6	
1-1836-301-3296	96.00	0.96	6.3	1.20	1.22	1.25	1.30	1.40	1.50	0.83	1.17	1.67	2.06	2.97	3.73	10.17	243.8	
1-1836-301-3299	99.00	0.99	6.5	1.20	1.22	1.25	1.30	1.40	1.50	0.85	1.20	1.72	2.12	3.06	3.83	10.48	251.5	
2-1836-301-3209	108.00	1.08	7.0	1.20	1.22	1.25	1.30	1.40	1.50	0.92	1.30	1.86	2.29	3.31	4.14	11.44	274.3	
2-1836-301-3210	120.00	1.20	7.6	1.20	1.22	1.25	1.30	1.40	1.50	1.01	1.42	2.04	2.52	3.64	4.56	12.71	304.8	
2-1836-301-3212	144.00	1.44	8.9	1.20	1.22	1.25	1.30	1.40	1.50	1.19	1.68	2.41	2.97	4.30	5.38	15.25	365.8	
2-1836-301-3215	180.00	1.80	10.8	1.20	1.22	1.25	1.30	1.40	1.50	1.45	2.07	2.96	3.66	5.29	6.63	19.06	457.2	
2-1836-301-3221	252.00	2.52	14.7	1.20	1.22	1.25	1.30	1.40	1.50	1.99	2.83	4.06	5.02	7.28	9.11	26.69	640.1	
2-1836-301-3225	300.00	3.00	17.2	1.20	1.22	1.25	1.30	1.40	1.50	2.35	3.35	4.80	5.94	8.60	10.76	31.77	762.0	
2-1836-301-3233	396.00	3.96	22.4	1.20	1.22	1.25	1.30	1.40	1.50	3.07	4.37	6.27	7.76	11.25	14.07	41.94	1005.8	

F = FACTORY STANDARD ITEM MAXIMUM SPECIFICATIONS ARE PRODUCT MAXIMUM PLUS MEASURING SYSTEM UNCERTAINTY.
NOTE: ALL SPECIFICATIONS APPLY AT 73 DEG. F, SEA LEVEL AND 20 TO 80% RELATIVE HUMIDITY.
PRODUCT SPECIFICATIONS APPLY AT 5 TO 99% (NON CONDENSING) RELATIVE HUMIDITY, CONSULT FACTORY FOR PRODUCT CHARACTERISTICS AT OTHER CONDITIONS.

VISIT OUR WEB SITE AT <http://www.tensolite.com>

