








TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
0.750"									
Fig. 4	PTL-10-425	750	Polypropylene	White	B-425	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-432	750	Polyester	Clear	B-432	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-8425	750	Polypropylene	White	B-425	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-473	750	Polyester	White	B-473	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-423	750	Polyester	White	B-423	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-426	750	Polyimide	Amber	B-426	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-457	750	Polyimide	White	B-457	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-477	750	Polyimide	White	B-477	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-478	750	Polyimide	White	B-478	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-479	750	Polyimide	White	B-479	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-437	750	Polyvinylfluoride	White	B-437	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-423	750	Polyester	White	B-423	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-10-432	750	Polyester	Clear	B-432	0.750 (19.1)	0.250 (6.4)	–	–
Fig. 4	PTL-11-432	500	Polyester	Clear	B-432	0.750 (19.1)	0.500 (12.7)	–	–
Fig. 4	PTL-11-432	500	Polyester	Clear	B-432	0.750 (19.1)	0.500 (12.7)	–	–
Fig. 14	PTL-80-424	250	Paper	White	B-424	0.750 (19.1)	0.900 (22.9)	–	–
Fig. 14	PTL-80-488	250	Polyester	White	B-488	0.750 (19.1)	0.900 (22.9)	–	–
Fig. 6	PTL-18-499	250	Nylon	White	B-499	0.750 (19.1)	1.000 (25.4)	–	12 to 10
Fig. 6	PTL-18-498	250	Vinyl	White	B-498	0.750 (19.1)	1.000 (25.4)	–	12 to 10
Fig. 6	BPTL-18-498	2500	Vinyl	White	B-498	0.750 (19.1)	1.000 (25.4)	–	12 to 10
Fig. 7	PTL-18-427	250	Vinyl	White	B-427	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	10 to 4
Fig. 7	BPTL-18-427	2500	Vinyl	White	B-427	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	10 to 4
Fig. 7	PTL-18-427-YL	250	Vinyl	Yellow	B-427	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	10 to 4
Fig. 6	PTL-30-499	250	Nylon	White	B-499	0.750 (19.1)	1.500 (38.1)	–	10 to 4
Fig. 6	PTL-30-498	250	Vinyl	White	B-498	0.750 (19.1)	1.500 (38.1)	–	10 to 4
Fig. 7	PTL-30-427	250	Vinyl	White	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	BPTL-30-427	2500	Vinyl	White	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-BL	250	Vinyl	Blue	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-BR	250	Vinyl	Brown	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-GR	250	Vinyl	Green	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-GY	250	Vinyl	Gray	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-OR	250	Vinyl	Orange	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-PL	250	Vinyl	Purple	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-RD	250	Vinyl	Red	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-30-427-YL	250	Vinyl	Yellow	B-427	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 2	PTL-79-461	100	Polyester	White	B-461	0.750 (19.1)	3.750 (95.3)	1.000 (25.4)	–



TLS 2200®/TLS PC Link™ Label Index By Size