



PRODUCTS & SERVICES:

Switches

Connectors

Defense/Aerospace Connectors

Contract Manufacturing

Custom Assembly

Custom Switches and Connectors



Search Catalog

By Keyword

- All Categories Top Actuated Panel Mount
Miniature Slide Switches (Swidgets)

[All Categories](#) > [Switches](#) > [Slide Switches](#) > [Miniature Slide Switches](#) > [Top Actuated Panel Mount Miniature Slide Switches \(Swidgets\)](#) > Item # GF-126-0327

- [Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # GF-126-0327, Top Actuated Panel Mount Miniature Slide Switches (Swidgets)



larger image

MORE IMAGES

Features of Top-Actuated Panel Mount Miniature Swidgets

DOWNLOADS

- [Mini Swidgets Terminal Layouts Chart \(PDF, 1856KB\)](#)
- [Toppers for use with CW Miniature Slide Switch Product \(PDF, 576KB\)](#)
- [Slide Switch Schematic \(PDF, 187KB\)](#)
- [Dim Dwg GF-126-0327 \(PDF, 115KB\)](#)

[Check Distributor Stock](#) · [Specifications](#) · [Materials](#) · [Actuator Knob](#) · [Performance Standards](#) · [Care in Switch Installation](#) · [CW Patents](#)

Check Distributor Stock

Check Distributor Stock	
-------------------------	--

Specifications

Circuitry	DPDT
Switch Function	ON-ON
Electrical Ratings	0.5 A @ 125 VDC 8.5 A @ 125 VAC
Actuator Style	Standard
Actuator Height	0.200
Mounting Type	Mounting Ears Removed
Orientation	Top
Terminations	PC
Illumination	Non Illuminated
Terminal	G-20-098
Terminal Option	Dimension A - 0.038 ± 0.010 in (0.97 ± 0.25 mm) Dimension B - 0.078 ± 0.003 in (1.98 ± 0.08 mm) Dimension C - 0.181 ± 0.010 in (4.60 ± 0.25 mm) Dimension D - 0.50 in (1.27 mm) Style No. 1
Toppers	With Topper Without Topper (Standard)
Button Options	0.125" (3.18 mm) 0.200" (5.08 mm) Standard 0.328" (8.33 mm) 0.453" (11.51 mm)
Mounting	PANEL - Two 0.100" diameter holes on 0.812" centers. 4-40 extruded and tapped mounting holes are also available. PRINTED CIRCUIT BOARD - Plug directly into board having hole pattern suggested in drawing. TERMINALS Standard is solder terminal G-20-28 as shown. For PC applications, we suggest G-20-18, but you may specify the terminal of your choice from those on page 15. SOLDER SHIELD Vulcanized fiber shield 0.020" thick may be shipped assembled or separate as requested.
Listing Agency (Consult drawing or factory for specific rating) ¹	 Listing Agencies
Compliance	
Solder Shield	Vulcanized Fiber Shield 0.020" thick that fits over the switch terminals is also available

¹ Due to ongoing advancements, additional agency certifications may be available, contact us for more information.

Materials

Button Material	Black Type 6/6 Nylon
Housing	Cold Rolled Steel
Housing Plating	4-point PC board mount switches-electro-tin; others - zinc followed by clear chromate.
Moving Contact	Copper Copper Alloy
Moving Contact Plating	Silver is standard. Gold (30 microinches of gold over 50 microinches of nickel) is available. Other gold thicknesses are available if your quantities are sufficient.
Moving Contact Spring	Beryllium Copper Phosphor Bronze
Terminals	Copper
Terminal Plating	Silver is standard. Gold (30 microinches over 50 microinches of nickel) on many popular types is available.
Terminal Board	NEMA Grade XP Phenolic Laminate
Note	Other materials to suit your application are available if volume is sufficient. Contact us for more information.

Actuator Knob

Decorative aluminum sleeved actuating knob is available. Specify GB-125 or GB-126 with appropriate suffix indicating your current requirements. 0.453" knob height shown is standard. Also available in heights of 0.162" (4.11 mm), 0.200 (5.08 mm), 0.562" (14.27 mm), and 0.709 (18.01 mm).

Performance Standards

CW switches are designed to perform to the standards listed when operated within ambient conditions detailed below:
Operating Temperature - 104°C maximum, -10°C minimum.
Relative Humidity - Switches will be operable and insulation resistance shall be greater than 100 megohms if allowed to dry for 100 hours at room temperature of 25°C and after exposure for one hour in an atmosphere having 95% relative humidity and a temperature of 50°C
High Voltage Breakdown - Minimum of 1000 volts RMS 60 Hz for one minute between parts of opposite polarity.
Contact Resistance - Less than 0.01 ohm at 20 milliamperes DC.
Life Cycling (No Load) - Switches will be operative after 10,000 (minimum) cycles at the rate of 10 cycles per minute.
Life Cycling (Load) - Switches will be operative after 6000 (minimum) cycles at the rate of 10 cycles per minute at rated load.

Care in Switch Installation

CW switches will perform properly if they are installed and used properly. Causes for failure often encountered in the field that are the responsibility of the user are:

1. Removal of factory applied lubricants from switch contacts and moving parts.
2. Introduction of foreign material into switching mechanism...flux, solder cleaning materials, potting compounds.
3. Restriction of movement of switch button.
4. Excessive heat often introduced while soldering.
5. Switching loads in excess of rating.

Manufacturing Engineers are cautioned to avoid misusing switches and resultant switch failures.

CW Patents

CW Engineers are constantly trying to upgrade the quality and cost effectiveness of our switches. Often this results in new inventions. Switch products shown in this catalog may be covered by one or more of the following U.S. patents:
 3,270,149; 3,993,881; 3,271,535; 4,404,437; 3,311,719; 4,128,745; 3,461,252; 4,410,232
 Other patent applications are pending.

Request Information