

Elma IEEE hot-swap injector/ejector handle

Scope of delivery

- Handle grey, button dark grey (plastic, UL94HB)
Handle black, button red (plastic, UL94V-0)
- Card holder (die-cast tin, galvanized)
- Fixing material (screws M2.5 for fixing of card holder/printed board)

Bottom handle *with* ESD pin



| Color | 1 piece | 100 pcs. |
|-------|---------|----------|
| grey | 81-098 | 81-098-2 |
| black | 81-096 | 81-096-2 |

Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Bottom handle *without* ESD pin



| Color | 1 piece | 100 pcs. |
|-------|-----------|-------------|
| grey | 81-098-01 | 81-098-01-2 |
| black | 81-096-01 | 81-096-01-2 |

Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Top handle *with* ESD pin



| Color | 1 piece | 100 pcs. |
|-------|---------|----------|
| grey | 81-097 | 81-097-2 |
| black | 81-095 | 81-095-2 |

Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Top handle *without* ESD pin



| Color | 1 piece | 100 pcs. |
|-------|-----------|-------------|
| grey | 81-097-01 | 81-097-01-2 |
| black | 81-095-01 | 81-095-01-2 |

Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Microswitch to injector/ejector handle





| Description | 10 pcs. | 100 pcs. |
|-------------------------------------|----------|----------|
| Microswitch with pre-assembled wire | 81-088-1 | 81-088-2 |

Technical data

| | | |
|---------------|----------------------|---------------|
| Life circuit: | 30 V DC, 5-50 mA | 30 000 cycles |
| | 60 V DC, 5 mA | 30 000 cycles |
| | 60 V DC, 500 mA | 15 000 cycles |
| Temperature: | - 25 °C to +70 °C | |
| Humidity: | RF 85% max. | |
| Vibration: | 10 Hz to 55 Hz, 18 g | |
| Shock: | 30 g, 11 msec | |

Assembly instruction



1 mm = 0.0394 inch, 1 inch = 25.4 mm

Elma IEEE hot-swap injector/ejector handle

NEW!

Offset version

- Offset by 2.54 mm (½HP) to the right
- Thus giving more space on the solder side of the printed board

Scope of delivery

- Offset handle grey, button dark grey (plastic, UL94HB)
Offset handle black, button red (plastic, UL94V-0)
- Card holder (die-cast tin, galvanized)
- Fixing material (screws M2.5 for fixing of card holder/printed board)

Offset bottom handle *with* ESD pin



| Color | 1 piece | 100 pcs. |
|---------------|---------|----------|
| grey, offset | 81-183 | 81-183-2 |
| black, offset | 81-185 | 81-185-2 |

Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Offset top handle *with* ESD pin



| Color | 1 piece | 100 pcs. |
|---------------|---------|----------|
| grey, offset | 81-182 | 81-182-2 |
| black, offset | 81-184 | 81-184-2 |



Optional: screws for fixing front panels M2.5/100 pcs.: 1904-41

Microswitch to injector/ejector handle



| Description | 10 pcs. | 100 pcs. |
|-------------------------------------|----------|----------|
| Microswitch with pre-assembled wire | 81-088-1 | 81-088-2 |

Assembly instruction



Technical data

| | | |
|---------------|----------------------|---------------|
| Life circuit: | 30 V DC, 5-50 mA | 30 000 cycles |
| | 60 V DC, 5 mA | 30 000 cycles |
| | 60 V DC, 500 mA | 15 000 cycles |
| Temperature: | - 25°C to +70°C | |
| Humidity: | RF 85% max. | |
| Vibration: | 10 Hz to 55 Hz, 18 g | |
| Shock: | 30 g, 11 msec | |

1 mm = 0.0394 inch, 1 inch = 25.4 mm