

Rigid/Intermediate Grade Conduit Fittings

- Combination Couplings
- Fitting Locknuts
- Grounding Locknuts

- Conduit Locknuts
- Insulated Throat Bushings

CP

CP
Rigid
Intermediate

COMBINATION COUPLINGS

(Concrete Tight) EMT (Set Screw) To Rigid (Set Screw)
 • Standard material: Steel
 • Standard finish: Zinc Plated

UL File No. E-19189

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
420	1/2"-1/2"	25	100	17
421	3/4"-3/4"	20	100	25
422	1"-1"	10	50	37

COMBINATION COUPLINGS - MALLEABLE IRON

Flexible Steel (Squeeze Type) To Rigid (Threaded)

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
65	1/2"-1/2"	10	100	17
66	3/4"-3/4"	10	100	22
67	1"-1"	5	25	31
68	1 1/4"-1 1/4"	5	25	31

COMBINATION COUPLINGS - DIE CAST ZINC

(Concrete Tight) EMT (Set Screw) To Rigid (Set Screw)

UL File No. E-19189

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
2420	1/2"-1/2"	50	500	8
2421	3/4"-3/4"	25	250	12

FITTING LOCKNUTS

STEEL

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
11X	1/2"	500	2500	1
12X	3/4"	100	1000	2
13X	1"	50	500	5
14X	1 1/4"	100	500	7
15X	1 1/2"	50	250	8
16X	2"	50	250	13
17X	2 1/2"	25	100	14
18X	3"	20	100	19
19X	3 1/2"	10	50	24
20X	4"	10	50	29

GROUNDING LOCKNUTS

STEEL

For use with bushing to bond 1/2" to 4" rigid conduit to boxes, cabinets or other enclosures, only where a locknut is exposed.

UL File No. E-6225

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
GL-11	1/2"	100	1000	4
GL-12	3/4"	50	500	4
GL-13	1"	50	500	6
GL-14	1 1/4"	50	250	8
GL-15	1 1/2"	50	250	10
GL-16	2"	25	100	20
GL-17	2 1/2"	20	100	25
GL-18	3"	10	50	42
GL-19	3 1/2"	10	50	60
GL-20	4"	5	25	80

CONDUIT LOCKNUTS

3/8" - 2" STEEL, 2 1/2" - 6" MALLEABLE IRON

UL File No. E-19189

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
10	3/8"	100	2500	1
11	1/2"	100	2500	1
12	3/4"	100	1000	2
13	1"	50	500	5
14	1 1/4"	100	500	7
15	1 1/2"	50	250	8
16	2"	50	250	13
17	2 1/2"	20	100	26
18	3"	10	50	42
19	3 1/2"	10	50	54
20	4"	5	25	68
22	5"	2	2	110
23	6"	1	1	154

INSULATED THROAT BUSHINGS

Malleable Iron Threaded 105°C Rated Plastic Throat Liner

UL File No. E-19189

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
1031	1/2"	100	1000	3
1032	3/4"	100	500	4
1033	1"	50	250	7
1034	1 1/4"	50	250	15
1035	1 1/2"	10	100	19
1036	2"	20	100	22
1037	2 1/2"	10	50	44
1038	3"	10	50	54
1039	3 1/2"	5	25	72
1040	4"	5	25	95
•1041	5"	1	1	100
•1042	6"	1	1	127

Set Screw Type - Threadless 105°C Rated Plastic Throat Liner

UL File No. E-19189

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
S1031	1/2"	100	1000	3
S1032	3/4"	100	500	4
S1033	1"	50	250	7
S1034	1 1/4"	50	250	15
S1035	1 1/2"	10	100	19
S1036	2"	20	100	22
S1037	2 1/2"	10	50	44
S1038	3"	10	50	54
S1039	3 1/2"	5	25	72
S1040	4"	5	25	95
S1041	5"	1	1	100
S1042	6"	1	1	127

• Not UL Listed

CP Rigid/Intermediate Grade Conduit Fittings

- Insulated Throat Grounding Bushings
- Threaded and Threadless
- Copper or Aluminum Ground Lug
- 105°C Rated

Rigid
Intermediate
CP

INSULATED THROAT GROUNDING BUSHINGS

IRON-105°C Rated Plastic Throat Liner

Copper Lug – For Copper Grounding Conductors – Threaded

UL File No. E-6225

Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight	
					Lbs.	Per 100
GLL-1C	1/2"	#4 - #14	50	500	8	
GLL-2C	3/4"	#4 - #14	50	250	12	
GLL-3C	1"	#4 - #14	50	250	14	
GLL-4C	1 1/4"	#4 - #14	25	125	19	
GLL-4-10C	1 1/4"	#1/0 - #8	25	125	30	
GLL-5C	1 1/2"	#4 - #14	10	100	21	
GLL-5-10C	1 1/2"	#1/0 - #8	10	100	32	
GLL-6C	2"	#4 - #14	10	50	29	
GLL-6-10C	2"	#1/0 - #8	10	50	40	
GLL-7C	2 1/2"	#1/0 - #8	10	50	65	
GLL-7-30C	2 1/2"	#3/0 - #6	10	50	88	
GLL-7-250C	2 1/2"	250MCM - #6	10	50	97	
GLL-8C	3"	#1/0 - #8	5	25	77	
GLL-8-30C	3"	#3/0 - #6	5	25	100	
GLL-8-250C	3"	250MCM - #6	5	25	109	
GLL-9C	3 1/2"	#3/0 - #6	1	1	125	
GLL-9-250C	3 1/2"	250MCM - #6	1	1	134	
GLL-10C	4"	#3/0 - #6	1	1	145	
GLL-10-250C	4"	250MCM - #6	1	1	154	
GLL-11C	5"	#3/0 - #6	1	1	165	
GLL-11-250C	5"	250MCM - #6	1	1	174	
GLL-12C	6"	#3/0 - #6	1	1	195	
GLL-12-250C	6"	250MCM - #6	1	1	204	

Aluminum Lug – For Copper Or Aluminum Grounding Conductors – Threaded 105°C Rated Plastic Throat Liner

UL File No. E-6225

Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight	
					Lbs.	Per 100
GLL-1	1/2"	#4 - #14	50	500	5	
GLL-2	3/4"	#4 - #14	50	250	9	
GLL-3	1"	#4 - #14	50	250	12	
GLL-4	1 1/4"	#4 - #14	25	125	19	
GLL-4-10	1 1/4"	#1/0 - #8	25	125	23	
GLL-5	1 1/2"	#4 - #14	10	100	24	
GLL-5-10	1 1/2"	#1/0 - #8	10	100	28	
GLL-6	2"	#4 - #14	10	50	26	
GLL-6-10	2"	#1/0 - #8	10	50	32	
GLL-7	2 1/2"	#1/0 - #8	10	50	53	
GLL-7-30	2 1/2"	#3/0 - #6	10	50	60	
GLL-7-250	2 1/2"	250MCM - #6	10	50	67	
GLL-8	3"	#1/0 - #8	5	25	70	
GLL-8-30	3"	#3/0 - #6	5	25	72	
GLL-8-250	3"	250MCM - #6	5	25	76	
GLL-9	3 1/2"	#3/0 - #6	1	1	100	
GLL-9-250	3 1/2"	250MCM - #6	1	1	100	
GLL-10	4"	#3/0 - #6	1	1	110	
GLL-10-250	4"	250MCM - #6	1	1	120	
GLL-11	5"	#3/0 - #6	1	1	140	
GLL-11-250	5"	250MCM - #6	1	1	143	
GLL-12	6"	#3/0 - #6	1	1	160	
GLL-12-250	6"	250MCM - #6	1	1	163	

Copper Lug – For Copper Grounding Conductors – Threadless – Set Screw Type 105°C Rated Plastic Throat Liner

UL File No. E-6225

Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight	
					Lbs.	Per 100
GLS-1C	1/2"	#4 - #14	50	500	8	
GLS-2C	3/4"	#4 - #14	50	250	12	
GLS-3C	1"	#4 - #14	50	250	14	
GLS-4C	1 1/4"	#4 - #14	25	125	19	
GLS-4-10C	1 1/4"	#1/0 - #8	25	125	30	
GLS-5C	1 1/2"	#4 - #14	10	100	21	
GLS-5-10C	1 1/2"	#1/0 - #8	10	100	32	
GLS-6C	2"	#4 - #14	10	50	29	
GLS-6-10C	2"	#1/0 - #8	10	50	40	
GLS-7C	2 1/2"	#1/0 - #8	10	50	65	
GLS-7-30C	2 1/2"	#3/0 - #6	10	50	88	
GLS-7-250C	2 1/2"	250MCM - #6	10	50	97	
GLS-8C	3"	#1/0 - #8	5	25	77	
GLS-8-30C	3"	#3/0 - #6	5	25	100	
GLS-8-250C	3"	250MCM - #6	5	25	109	
GLS-9C	3 1/2"	#3/0 - #6	1	1	125	
GLS-9-250C	3 1/2"	250MCM - #6	1	1	134	
GLS-10C	4"	#3/0 - #6	1	1	145	
GLS-10-250C	4"	250MCM - #6	1	1	154	
GLS-11C	5"	#3/0 - #6	1	1	165	
GLS-11-250C	5"	250MCM - #6	1	1	174	
GLS-12C	6"	#3/0 - #6	1	1	195	
GLS-12-250C	6"	250MCM - #6	1	1	204	

Aluminum Lug – For Copper Or Aluminum Grounding Conductors – Threadless – Set Screw Type 105°C Rated Plastic Throat Liner

UL File No. E-6225

Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight	
					Lbs.	Per 100
GLS-1	1/2"	#4 - #14	50	500	5	
GLS-2	3/4"	#4 - #14	50	250	9	
GLS-3	1"	#4 - #14	50	250	12	
GLS-4	1 1/4"	#4 - #14	25	125	19	
GLS-4-10	1 1/4"	#1/0 - #8	25	125	23	
GLS-5	1 1/2"	#4 - #14	10	100	24	
GLS-5-10	1 1/2"	#1/0 - #8	10	100	28	
GLS-6	2"	#4 - #14	10	50	26	
GLS-6-10	2"	#1/0 - #8	10	50	32	
GLS-7	2 1/2"	#1/0 - #8	10	50	53	
GLS-7-30	2 1/2"	#3/0 - #6	10	50	60	
GLS-7-250	2 1/2"	250MCM - #6	10	50	67	
GLS-8	3"	#1/0 - #8	5	25	70	
GLS-8-30	3"	#3/0 - #6	5	25	72	
GLS-8-250	3"	250MCM - #6	5	25	76	
GLS-9	3 1/2"	#3/0 - #6	1	1	100	
GLS-9-250	3 1/2"	250MCM - #6	1	1	100	
GLS-10	4"	#3/0 - #6	1	1	110	
GLS-10-250	4"	250MCM - #6	1	1	120	
GLS-11	5"	#3/0 - #6	1	1	140	
GLS-11-250	5"	250MCM - #6	1	1	143	
GLS-12	6"	#3/0 - #6	1	1	160	
GLS-12-250	6"	250MCM - #6	1	1	163	

Rigid/Intermediate Grade Conduit Fittings

- Insulated Bushings
- Insulated Throat Bushings
- Insulated Throat Grounding Bushings

CP

CP
Rigid
Intermediate

INSULATING BUSHINGS

UL File No. E-19189

● Materials: Plastic



Rated 105°C Cat. #	Rated 150°C Cat. #	Trade Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
931	H-931	1/2"	50	500	1
932	H-932	3/4"	50	500	1
933	H-933	1"	50	200	2
934	H-934	1 1/4"	50	200	3
935	H-935	1 1/2"	25	100	3
936	H-936	2"	25	100	4
937	H-937	2 1/2"	10	50	8
938	H-938	3"	10	50	10
939	H-939	3 1/2"	5	25	11
940	H-940	4"	5	25	11
941		5"	5	5	40
942	H-942	6"	5	5	42

INSULATED THROAT BUSHINGS

Features:

- Plastic liner will not chip, crack, swell or shrink. It resists corrosion, chemicals and temperature extremes.

Standard Materials:

- Body - Malleable Iron
- Insuliner - ULTEM1000 rated at 150°C

Standard Finish:

- Body - Zinc Plated

IRON - 150°C RATED Threaded

UL File No. E-19189

Cat. #	Trade Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
H1031	1/2"	100	1000	6
H1032	3/4"	100	500	8
H1033	1"	50	250	11
H1034	1 1/4"	50	250	14
H1035	1 1/2"	10	100	17
H1036	2"	20	100	24
H1037	2 1/2"	10	50	51
H1038	3"	10	50	62
H1039	3 1/2"	5	25	85
H1040	4"	5	25	104
H1041	5"	1	1	130
H1042	6"	1	1	167

Set Screw Type - Threadless 150°C Rated Thermo Plastic Throat Liner

UL File No. E-19189

Cat. #	Trade Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
HS1031	1/2"	100	1000	6
HS1032	3/4"	100	500	7
HS1033	1"	50	250	10
HS1034	1 1/4"	50	250	13
HS1035	1 1/2"	10	100	15
HS1036	2"	20	100	21
HS1037	2 1/2"	10	50	42
HS1038	3"	10	50	51
HS1039	3 1/2"	5	25	65
HS1040	4"	5	25	80
HS1041	5"	1	1	100
HS1042	6"	1	1	128

INSULATED THROAT GROUNDING BUSHINGS

Features:

- Resilient plastic liner, resists corrosion, chemicals and temperature extremes.
- Insuliner - ULTEM1000 rated at 150°C
- 1 Set screw provided with each fitting locks bushing in any desired position
- External stainless steel hardware as standard

Standard Finish:

- Body - Zinc Plated

IRON - 150°C RATED

Copper Lug - For Copper Grounding Conductors - Threaded

UL File No. E-6225



Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
HGLL1C	1/2"	#4 - #14	50	500	12
HGLL2C	3/4"	#4 - #14	50	250	14
HGLL3C	1"	#4 - #14	50	250	17
HGLL4C	1 1/4"	#4 - #14	25	125	20
HGLL4-10C	1 1/4"	#1/0 - #8	25	125	32
HGLL5C	1 1/2"	#4 - #14	10	100	23
HGLL5-10C	1 1/2"	#1/0 - #8	10	100	35
HGLL6C	2"	#4 - #14	10	50	30
HGLL6-10C	2"	#1/0 - #8	10	50	42
HGLL7C	2 1/2"	#1/0 - #8	10	50	69
HGLL7-30C	2 1/2"	#3/0 - #6	10	50	92
HGLL7-250C	2 1/2"	250MCM - #6	10	50	101
HGLL8C	3"	#1/0 - #8	5	25	80
HGLL8-30C	3"	#3/0 - #6	5	25	103
HGLL8-250C	3"	250MCM - #6	5	25	112
HGLL9C	3 1/2"	#3/0 - #6	1	1	126
HGLL9-250C	3 1/2"	250MCM - #6	1	1	135
HGLL10C	4"	#3/0 - #6	1	1	145
HGLL10-250C	4"	250MCM - #6	1	1	155
HGLL11C	5"	#3/0 - #6	1	1	171
HGLL11-250C	5"	250MCM - #6	1	1	180
HGLL12C	6"	#3/0 - #6	1	1	210
HGLL12-250C	6"	250MCM - #6	1	1	317

Aluminum Lug - For Copper Or Aluminum Grounding Conductors - Threaded

UL File No. E-6225



Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
HGLL-1	1/2"	#4 - #14	50	500	9
HGLL-2	3/4"	#4 - #14	50	250	11
HGLL-3	1"	#4 - #14	50	250	14
HGLL-4	1 1/4"	#4 - #14	25	125	17
HGLL4-10	1 1/4"	#1/0 - #8	25	125	24
HGLL-5	1 1/2"	#4 - #14	10	100	20
HGLL5-10	1 1/2"	#1/0 - #8	10	100	24
HGLL-6	2"	#4 - #14	10	50	27
HGLL6-10	2"	#1/0 - #8	10	50	31
HGLL-7	2 1/2"	#1/0 - #8	10	50	58
HGLL7-30	2 1/2"	#3/0 - #6	10	50	67
HGLL7-250	2 1/2"	250MCM - #6	10	50	70
HGLL-8	3"	#1/0 - #8	5	25	69
HGLL8-30	3"	#3/0 - #6	5	25	78
HGLL8-250	3"	250MCM - #6	5	25	81
HGLL-9	3 1/2"	#3/0 - #6	1	1	101
HGLL9-250	3 1/2"	250MCM - #6	1	1	104
HGLL-10	4"	#3/0 - #6	1	1	120
HGLL10-250	4"	250MCM - #6	1	1	123
HGLL-11	5"	#3/0 - #6	1	1	145
HGLL11-250	5"	250MCM - #6	1	1	150
HGLL-12	6"	#3/0 - #6	1	1	185
HGLL12-250	6"	250MCM - #6	1	1	186

CP Rigid/Intermediate Grade Conduit Fittings

- Insulated Throat Grounding Bushings
- Three Piece Conduit Couplings
- Conduit Bushed Nipples

CP Rigid Intermediate

INSULATED THROAT GROUNDING BUSHINGS





Features:

- Resilient plastic liner resists corrosion, chemicals and temperature extremes
- Insuliner - ULTEM1000 rated at 150°C
- 2 Set-screws provided with each fitting, locks bushings in any desired position
- Standard Finish: Zinc Plated

IRON - 150°C RATED





Set Screw Type - Copper Lug - For Copper Grounding Conductors - Threadless

UL File No. E-6225

	Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
	HGLS1C	1/2"	#4 - #14	50	500	12
	HGLS2C	3/4"	#4 - #14	50	250	13
	HGLS3C	1"	#4 - #14	50	250	16
	HGLS4C	1 1/4"	#4 - #14	25	125	19
	HGLS4-10C	1 1/4"	#1/0 - #8	25	125	31
	HGLS5C	1 1/2"	#4 - #14	10	100	21
	HGLS5-10C	1 1/2"	#1/0 - #8	10	100	33
	HGLS6C	2"	#4 - #14	10	50	27
	HGLS6-10C	2"	#1/0 - #8	10	50	39
	HGLS7C	2 1/2"	#1/0 - #8	10	50	60
	HGLS7-30C	2 1/2"	#3/0 - #6	10	50	83
	HGLS7-250C	2 1/2"	250MCM - #6	10	50	92
	HGLS8C	3"	#1/0 - #8	5	25	70
	HGLS8-30C	3"	#3/0 - #6	5	25	92
	HGLS8-250C	3"	250MCM - #6	5	25	100
	HGLS9C	3 1/2"	#3/0 - #6	1	1	105
	HGLS9-250C	3 1/2"	250MCM - #6	1	1	115
	HGLS10C	4"	#3/0 - #6	1	1	100
	HGLS10-250C	4"	250MCM - #6	1	1	130
	HGLS11C	5"	#3/0 - #6	1	1	140
	HGLS11-250C	5"	250MCM - #6	1	1	150
	HGLS12C	6"	#3/0 - #6	1	1	170
	HGLS12-250C	6"	250MCM - #6	1	1	180

Set Screw Type - Aluminum Lug - For Copper Or Aluminum Grounding Conductors - Threadless

UL File No. E-6225

	Cat. #	Trade Size	Lug Size	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
	HGLS1	1/2"	#4 - #14	50	500	9
	HGLS2	3/4"	#4 - #14	50	250	10
	HGLS3	1"	#4 - #14	50	250	13
	HGLS4	1 1/4"	#4 - #14	25	125	16
	HGLS4-10	1 1/4"	#1/0 - #8	25	125	20
	HGLS5	1 1/2"	#4 - #14	10	100	18
	HGLS5-10	1 1/2"	#1/0 - #8	10	100	22
	HGLS6	2"	#4 - #14	10	50	24
	HGLS6-10	2"	#1/0 - #8	10	50	28
	HGLS7	2 1/2"	#1/0 - #8	10	50	50
	HGLS7-30	2 1/2"	#3/0 - #6	10	50	58
	HGLS7-250	2 1/2"	250MCM - #6	10	50	60
	HGLS8	3"	#1/0 - #8	5	25	58
	HGLS8-30	3"	#3/0 - #6	5	25	67
	HGLS8-250	3"	250MCM - #6	5	25	70
	HGLS9	3 1/2"	#3/0 - #6	1	1	80
	HGLS9-250	3 1/2"	250MCM - #6	1	1	85
	HGLS10	4"	#3/0 - #6	1	1	90
	HGLS10-250	4"	250MCM - #6	1	1	100
	HGLS11	5"	#3/0 - #6	1	1	115
	HGLS11-250	5"	250MCM - #6	1	1	120
	HGLS12	6"	#3/0 - #6	1	1	145
	HGLS12-250	6"	250MCM - #6	1	1	150




THREE PIECE CONDUIT COUPLINGS

Application:

Used to join two lengths of threaded conduit. Couples conduit when conduit can be turned.

MALLEABLE IRON (Concrete Tight)

- Heavy duty casting
 - Standard Finish: Zinc Plated
- UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	190M	1/2"	25	125	23
	191	3/4"	25	100	35
	192	1"	10	50	60
	193	1 1/4"	5	25	91
	194	1 1/2"	5	25	167
	195	2"	5	5	215
	196	2 1/2"	2	10	430
	197	3"	1	5	463
	198	3 1/2"	1	5	655
	199	4"	1	1	800
	188†	5"	1	1	1200
† Not UL Listed	189†	6"	1	1	2100




CONDUIT BUSHED NIPPLES

Use:

- Use thru knockout to connect box to conduit coupling.
- Use with a locknut to connect two boxes side by side or back to back.
- Use with a locknut to connect fixture housing to continuous runs.




MALLEABLE IRON Non-Insulated Threaded NPSM for rigid conduit and IMC

UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	50*	1/2"	50	500	3
	51	3/4"	25	250	8
	52	1"	10	100	13
	53	1 1/4"	10	100	19
	54	1 1/2"	10	50	30
	55	2"	10	50	37
	56	2 1/2"	5	25	68
	57	3"	5	25	92
	58	3 1/2"	1	5	130
* Steel	59	4"	1	5	200
† Not UL Listed	60†	5"	1	1	350
	61†	6"	1	1	425

Insulated

UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	1050*	1/2"	50	500	3
	1051	3/4"	25	250	4
	1052	1"	10	100	11
	1053	1 1/4"	10	100	19
	1054	1 1/2"	10	50	30
	1055	2"	10	50	37
	1056	2 1/2"	5	25	72
	1057	3"	5	25	96
	1058	3 1/2"	1	5	113
	1059	4"	1	5	187
* Steel	1060	5"	1	1	350
	1061	6"	1	1	450

Rigid/Intermediate Grade Conduit Fittings




- Conduit Bushed Nipples
- 90° Pull Elbows
- Offset Conduit Nipples
- Knockout Snap-In Blanks
- Push Plugs

CP

CP
Rigid
Intermediate

CONDUIT BUSHED NIPPLES – DIE CAST ZINC

Non-Insulated
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	50D	1/2"	100	1000	4
	51D	3/4"	50	500	5
	52D	1"	25	250	10
	53D	1 1/4"	25	100	11
	54D	1 1/2"	25	100	20
	55D	2"	10	40	30
	56D	2 1/2"	10	40	40
	57D	3"	10	40	49
	58D	3 1/2"	10	40	68
	59D	4"	5	20	70


90 DEGREE PULL ELBOWS – MALLEABLE IRON

Features:




- Raintight
- Furnished with Neoprene gasketed steel cover
- Furnished with Steel lock nut
- Furnished with Stamped Steel cover
- Threaded for rigid conduit and IMC
- For outdoor use
- Standard Finish: Zinc plated

(Gasketed – Liquidtight)

Male To Female
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	810	1/2"	20	100	34
	811	3/4"	10	50	56
	812	1"	5	25	88
	813	1 1/4"	2	10	92
	814	1 1/2"	2	10	200
	815	2"	1	5	344




Female To Female
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	820	1/2"	20	100	36
	821	3/4"	10	50	49
	822	1"	5	25	94
	823	1 1/4"	2	10	140
	824	1 1/2"	2	10	200
	825	2"	1	5	344

90 DEGREE PULL ELBOWS – DIE CAST ZINC




(Gasketed – Liquidtight)

Male To Female; Combination Rigid and EMT
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	810DC	1/2"	10	100	31
	811DC	3/4"	5	50	31
					

Female To Female; Combination Rigid and EMT


UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	820DC	1/2"	10	100	28
	821DC	3/4"	5	50	35
	822DC	1"	5	25	64
	823DC	1 1/4"	2	20	66

OFFSET CONDUIT NIPPLES – MALLEABLE IRON




Features:

- Threaded NPSM for rigid conduit and IMC
- Standard Finish: Zinc Plated
- USE: To offset the axis of raceways 3/4 of an inch


	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	300	1/2"	25	100	24
	301	3/4"	25	100	34
	302	1"	10	50	49
	303	1 1/4"	10	50	54

OFFSET CONDUIT NIPPLES – DIE CAST ZINC


UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	300DC	1/2"	10	100	9
	301DC	3/4"	10	100	15
	302DC	1"	10	100	21
	303DC	1 1/4"	5	50	33
	304	1 1/2"	5	50	40
	305	2"	2	20	65

KNOCKOUT SNAP-IN BLANKS – STEEL

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	335	1/2"	100	1000	2
	336	3/4"	100	1000	2
	337	1"	50	500	2
	338	1 1/4"	50	250	3
	339	1 1/2"	25	250	5
	340	2"	20	200	7

PUSH PLUGS – PLASTIC*

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	PPC-50	1/2"	100	1000	1
	PPC-75	3/4"	100	1000	1
	PPC-100	1"	50	500	1
	PPC-125	1 1/4"	50	200	1
	PPC-150	1 1/2"	25	100	1
	PPC-200	2"	25	100	1
	PPC-250	2 1/2"	—	100	2
	PPC-300	3"	—	100	3
	PPC-350	3 1/2"	—	50	6
	PPC-400	4"	—	50	8

*Temperature Rating: 180° – 200°F
Tensile Strength: 600 – 2300 PSI

CP Rigid/Intermediate Grade Conduit Fittings

- Bushing Pennies
- Knockout Reducing Washers
- Nailing Straps

- Clamps
- Clampbacks/Spacers
- Straps

Rigid Intermediate
CP

BUSHING PENNIES – STEEL

A penny under a bushing will seal the end of conduit during construction.



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
90	1/2"	100	1000	1
91	3/4"	100	1000	1
92	1"	100	1000	1
93	1 1/4"	50	500	1
94	1 1/2"	50	500	2
95	2"	50	50	3
96	2 1/2"	50	50	5
97	3"	50	50	7
98	3 1/2"	50	50	10
99	4"	50	50	14

KNOCKOUT REDUCING WASHERS – STEEL



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
342	3/4"-1/2"	100	2500	1
343	1"-1/2"	100	100	2
344	1"-3/4"	100	100	2
345	1 1/4"-1/2"	100	100	3
346	1 1/4"-3/4"	100	100	2
347	1 1/4"-1"	100	100	2
348	1 1/2"-1/2"	50	50	5
349	1 1/2"-3/4"	50	50	4
350S	1 1/2"-1"	50	50	4
351	1 1/2"-1 1/4"	50	50	3
352	2"-1/2"	50	50	7
353	2"-3/4"	50	50	7
354	2"-1"	50	50	6
355	2"-1 1/4"	50	50	5
356	2"-1 1/2"	50	50	3
360	2 1/2"-1/2"	25	250	7
361	2 1/2"-3/4"	25	250	7
362	2 1/2"-1"	25	250	7
363	2 1/2"-1 1/4"	25	250	7
364	2 1/2"-1 1/2"	25	250	7
365	2 1/2"-2"	25	250	7
366	3"-1"	25	250	14
367	3"-1 1/4"	25	250	14
368	3"-1 1/2"	25	250	14
369	3"-2"	25	250	14
370S	3"-2 1/2"	25	250	14
371	3"-1 1/2"	25	100	25
372	3 1/2"-2"	25	100	25
373	3 1/2"-2 1/2"	25	100	25
374	3 1/2"-3"	25	100	25
375	4"-2"	25	100	35
376	4"-2 1/2"	25	100	35
377	4"-3"	25	100	35
378	4"-3 1/2"	25	100	35

NAILING STRAPS – CAST STEEL


Support rigid conduit and IMC to mounting surface

- Standard material: Cast Steel
- Standard finish: Zinc plated



Cat. #	Conduit Sizes		Unit Quantity	Standard Package	Weight Lbs. Per 100
	EMT	Rigid			
NS-1	1/2"	3/8"	100	1000	2
NS-2	3/4"	1/2"	100	1000	2
NS-3	1"	3/4"	100	1000	3

Nailing Straps Dimensions – Inches



Cat. #	A	B	C	D
NS-1	3/16	1	17/8	3/4
NS-2	3/4	1 1/4	2	15/16
NS-3	3/16	1 1/2	2 1/2	1 1/8

CLAMPS – MALLEABLE IRON

UL File No. E-184283



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
510	1/2"	50	500	6
511	3/4"	50	250	8
512	1"	50	250	13
513	1 1/4"	25	100	20
514	1 1/2"	20	100	30
515	2"	10	50	64
516*	2 1/2"	5	25	104
517*	3"	2	10	120
518*	3 1/2"	2	10	150
519*	4"	2	10	220
520+	5"	1	5	380
521+	6"	1	5	690

* Also for use with Thinwall (EMT) Conduit
+ Not UL Listed

CLAMPBACKS/SPACERS – MALLEABLE IRON

UL File No. E-184283



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
CB1	1/2"	25	250	8
CB2	3/4"	25	250	10
CB3	1"	25	100	12
CB4	1 1/4"	25	100	21
CB5	1 1/2"	25	100	42
CB6	2"	10	50	40
CB7	2 1/2"	10	50	49
CB8	3"	10	50	62
CB9	3 1/2"	10	10	91
CB10	4"	10	10	110
CB11+	5"	5	5	135
CB12+	6"	5	5	225

+ Not UL Listed

STRAPS – STEEL GALVANIZED

(Two Hole)

UL File No. E-184283



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
496-2	3/8"	250	250	2
496-3	1/2"	150	150	2
496-4	3/4"	100	100	3
496-5	1"	50	50	7
496-6	1 1/4"	50	50	8
496-7	1 1/2"	50	50	10
496-8	2"	25	25	15
496-9	2 1/2"	25	25	19
496-10	3"	25	25	23
496-11	3 1/2"	25	25	93
496-12	4"	10	10	108

Rigid/Intermediate Grade Conduit Fittings

- Clamps "Snap-On"
- Clamps
- Cable And Conduit Hangers

- Beam Clamps/Insulator Supports
- Conduit Clamps

CP

CP Rigid Intermediate

CLAMPS "SNAP-ON" - STEEL

UL File No. E-184283
(Heavy Gauge)

Application:

- To support rigid conduit and IMC to mounting service



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
410*	1/2"	100	500	5
411*	3/4"	100	500	6
412*	1"	50	250	11
413*	1 1/4"	50	250	13
414	1 1/2"	25	100	20
415	2"	25	25	22
206	2 1/2"	25	25	64
207	3"	25	25	71
208	3 1/2"	10	10	120
209	4"	10	10	130

* CSA Certified

CLAMPS - STEEL


(Light Gauge)



Cat. #	Conduit Size Rigid	Conduit Size of Strap Inside	Unit Quantity	Standard Package	Weight Lbs. Per 100
566	1/4"	.540	500	500	2
567	3/8"	.675	200	1000	2

CABLE AND CONDUIT HANGERS - STEEL

With Bolts



Cat. #	Conduit Size Rigid	Conduit Size EMT	Unit Quantity	Standard Package	Weight Lbs. Per 100
0B	1/2"	3/8" & 1/2"	100	100	6
1-B	3/4"	3/4"	100	100	6
2-B	1"	1"	100	100	8
2 1/2-B	1 1/4"	—	100	100	10
3-B	1 1/2"	1 1/4"	100	100	11
4-B	—	1 1/2"	100	100	16
5-B	2"	2"	50	50	23
6-B	2 1/2"	2 1/2"	50	50	29
7-B	3"	3"	25	25	31
8-B	3 1/2"	3 1/2"	10	10	38
9-B	4"	4"	10	10	38

BEAM CLAMPS/INSULATOR SUPPORTS - MALLEABLE IRON

UL File No. E-184283

- Standard finish: Zinc Plated



Cat. #	Base Size	Jaw Open	Max. Wt. Support	Tapped Unit Qty.	Std. Pkg.	Wt. Lbs./100	
528*	3/4"	5/8"	230	10 - 24	25	100	14
529*	3/4"	5/8"	230	1/4" - 20	25	100	13
530	1"	3/4"	230	10 - 24	25	100	23
531	1"	3/4"	230	1/4" - 20	25	100	24
532	1 1/2"	3/4"	290	5/16" - 18	50	50	47
533	2"	7/8"	330	3/8" - 16	25	25	81
534	2 1/2"	7/8"	800	1/2" - 13	25	25	155

* Not UL listed

BEAM CLAMPS/INSULATOR SUPPORTS - STEEL



Cat. #	Base Size	Jaw Opening	Tapped Holes	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
529-S	3/4"	5/8"	1/4" - 20	50	50	13

CONDUIT CLAMPS

Application:

Right Angle - to attach the conduit run at a 90° angle to a beam or structural member

Right Angle Type - Electrogalvanized - Iron



Cat. #	Trade Size	Load Rating Lbs	Standard Package	Weight Lbs. Per 100
RAC50HD	1/2"	30	50	37
RAC75HD	3/4"	50	50	40
RAC100HD	1"	60	50	42
RAC125HD	1 1/4"	75	25	49
RAC150HD	1 1/2"	80	25	54
RAC200HD	2"	100	25	71
RAC250HD	2 1/2"	125	10	95
RAC300HD	3"	165	10	107
RAC350HD	3 1/2"	200	10	120
RAC400HD	4"	330	10	131

Application:

Parallel Type - to attach the conduit run parallel to a beam or structural member

Parallel Type - Electrogalvanized - Iron




Cat. #	Trade Size	Load Rating Lbs	Standard Package	Weight Lbs. Per 100
PARC50HD	1/2"	30	50	50
PARC75HD	3/4"	50	50	53
PARC100HD	1"	60	50	60
PARC125HD	1 1/4"	75	25	70
PARC150HD	1 1/2"	80	25	82
PARC200HD	2"	100	25	132
PARC250HD	2 1/2"	125	25	192
PARC300HD	3"	165	10	194
PARC350HD	3 1/2"	200	10	216
PARC400HD	4"	330	10	232

CONDUIT CLAMPS

Applications:

Edge Type - to attach the conduit run at a 90° angle to a thin beam or structural member.

Edge Type - Electrogalvanized - Iron



Cat. #	Trade Size	Standard Package	Weight Lbs. Per 100
ETC50HD	1/2"	50	63
ETC75HD	3/4"	50	69
ETC100HD	1"	50	82
ETC125HD	1 1/4"	25	95
ETC150HD	1 1/2"	25	108
ETC200HD	2"	25	121
ETC250HD	2 1/2"	25	153
ETC300HD	3"	10	214

Conduit Beam Clamp - J Type - Iron

UL File No. E-184283



Cat. #	Size	Max Weight Support	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
JCC1	1/2"	150	25	25	35
JCC2	3/4"	150	25	25	43
JCC34	1" & 1 1/4"	225	10	10	90
JCC56	1 1/2" & 2"	300	5	5	190
JCC78	2 1/2" & 3"	500	2	2	380
JCC910	3 1/2" & 4"	700	2	2	575

CONDUIT REDUCERS – STEEL/FERALLOY®



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
251	3/4"-1/2"	50	50	4
252	1"-1/2"	25	25	13
253	1 1/4"-1/2"	10	10	30
254	1 1/2"-1/2"	10	10	43
255	2"-1/2"	5	5	83
260	1"-3/4"	25	25	7
261	1 1/4"-3/4"	10	10	23
262	1 1/2"-3/4"	10	10	40
263	2"-3/4"	5	5	79
268	1 1/4"-1"	10	10	18
269	1 1/2"-1"	10	10	27
270S	2"-1"	5	5	66
275	1 1/2"-1 1/4"	10	10	13
276	2"-1 1/4"	5	5	24
281	2"-1 1/2"	5	5	27
282	2 1/2"-1"	10	10	120
283	2 1/2"-1 1/4"	10	10	130
285	2 1/2"-2"	10	10	150
288	3"-1 1/2"	5	5	210
289	3"-2"	2	2	160
290M	3"-2 1/2"	5	5	120
291	3 1/2"-2"	2	10	200
292	3 1/2"-2 1/2"	2	10	225
293	3 1/2"-3"	2	10	150
294	4"-2"	2	10	270
295	4"-2 1/2"	2	10	270
296	4"-3"	2	10	260
297	4"-3 1/2"	2	10	160
298	5"-4"	1	1	385
299	6"-5"	1	1	475

PLUGS – CAST IRON

Recessed



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
PLG1M	1/2"	50	50	6
PLG2M	3/4"	50	50	11
PLG3M	1"	25	25	22
PLG4M	1 1/4"	25	25	34
PLG5M	1 1/2"	10	10	48
PLG6M	2"	10	10	82
PLG7M	2 1/2"	2	2	150
PLG8M	3"	2	2	222
PLG9M	3 1/2"	1	1	340
PLG10M	4"	1	1	380

Square Head



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
PLG15M	1/2"	50	50	12
PLG25M	3/4"	50	50	16
PLG35M	1"	25	25	25
PLG45M	1 1/4"	25	25	34
PLG55M	1 1/2"	10	10	48
PLG65M	2"	10	10	80
PLG75M	2 1/2"	1	1	116
PLG85M	3"	1	1	185
PLG95M	3 1/2"	1	1	232
PLG105M	4"	1	1	310


Rigid/Intermediate Grade Conduit Fittings

- Heavy-Duty Conduit U-Bolts with Hex Nuts
- Plugs
- Conduit Hubs®
- Split Conduit Couplings

CP

HEAVY-DUTY CONDUIT U-BOLTS WITH HEX NUTS

Electrogalvanized – Iron




Cat. #	Trade Size	Thread Size	Standard Package	Weight Lbs. Per 100
UBM50HD	1/2"	5/16"-18	200	12
UBM75HD	3/4"	5/16"-18	200	14
UBM100HD	1"	5/16"-18	100	17
UBM125HD	1 1/4"	5/16"-18	50	19
UBM150HD	1 1/2"	5/16"-18	50	21
UBM200HD	2"	3/8"-16	50	28
UBM250HD	2 1/2"	3/8"-16	25	37
UBM300HD	3"	3/8"-16	25	42
UBM350HD	3 1/2"	3/8"-16	20	46
UBM400HD	4"	3/8"-16	20	51

SPLIT CONDUIT COUPLINGS

Body-Ductile Iron
Clamping Hardware-Electrogalvanized Steel
Gasket-Neoprene

- Concrete Tight
- Suitable for use in Class 1, Division 2 Areas



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
TCC1	1/2"	10	20	39
TCC2	3/4"	10	20	45
TCC3	1"	10	20	68
TCC4	1 1/4"	5	20	82
TCC5	1 1/2"	5	20	116
TCC6	2"	5	20	111
TCC7	2 1/2"	2	10	283
TCC8	3"	2	10	323
TCC9	3 1/2"	1	5	395
TCC10	4"	1	5	506
TCC12	5"	1	1	944
TCC14	6"	1	1	1218

CONDUIT HUBS – CAST IRON

(Insulated Throat)


UL File No. E-19189

Applications:

Conduit hubs are ideal for terminating electrical conduit through the walls of enclosures. Designed for use indoors or outdoors with rigid conduit and IMC, specific applications include food processing plants, distilleries, breweries, sewage disposal plants, chemical plants, paper processing mills and refineries.

Features:

- Male thread is on the nut for space saving
- Quick and easy when installing rigid conduit nipple between two existing enclosures
- Insulated throat provides smooth pulling surface
- Furnished with SG sealing gasket
- Hub fits standard knockouts. No special tools required




Furnished with SG Sealing Gaskets



Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
HUB1	1/2"	25	100	18
HUB2	3/4"	10	100	36
HUB3	1"	5	50	51
HUB4	1 1/4"	5	20	75
HUB5	1 1/2"	2	20	94
HUB6	2"	1	10	119
HUB7	2 1/2"	1	5	238
HUB8	3"	1	5	300
HUB9	3 1/2"	1	5	388
HUB10	4"	1	5	544

Conduit Hub Dimension



Cat. #	Conduit Size	a	b	c	d	x
HUB1	1/2"	1	1 1/4	1	1/8	9/64
HUB2	3/4"	1 1/8	1 9/16	1 3/8	5/32	1/4
HUB3	1"	1 3/8	1 7/8	1 5/8	3/16	9/32
HUB4	1 1/4"	1 1/2	2 5/16	2	1/4	7/16
HUB5	1 1/2"	1 5/8	2 1/2	2 3/8	1/4	7/16
HUB6	2"	1 11/16	3	2 13/16	1/4	7/16
HUB7	2 1/2"	2 3/16	3 3/8	3 7/16	1/4	7/16
HUB8	3"	2 7/16	4 1/4	4 1/16	1/4	7/16
HUB9	3 1/2"	2 7/16	4 3/4	4 11/16	5/16	3/4
HUB10	4"	2 9/16	5 1/4	5 1/16	5/16	1 1/8

NOTE: Dimension "x" is maximum wall thickness of box that will meet the requirement for three full threads engagement of nipple and fitting body when liquidtight box connector or rigid conduit hub is installed in a knockout or slip hole.

CONDUIT HUBS – MALLEABLE IRON

(Insulated Throat)

Features:



- Male thread type
- Tapered female thread for rigid conduit and IMC
- Recessed O-ring gasket assures raintight and dust tight connections
- Insulated throat provides smooth pulling surface
- Locking screw on the nut doubles as a grounding screw for added safety
- Complete size range from 1/2" to 6"
- Hubs fit standard knockouts. No special tools required

Certifications and Compliances:

- Class I, Division 2 – NEC 501.4(B)
- Class II, Divisions 1 & 2 – NEC 502.4(A)(B)
- Class III, Division 1 & 2 – NEC 503.3(A)(B)
- UL Listed – UL Standard 514B
- cUL Listed – Certified by UL to CSA Standard C22.2 No. 18
- NEMA: FB-1
- Suitable for wet locations






Cat. #	Trade Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
MHUB1	1/2"	25	100	18
MHUB2	3/4"	25	100	25
MHUB3	1"	5	50	50
MHUB4	1 1/4"	5	25	25
MHUB5	1 1/2"	2	20	20
MHUB6	2"	1	10	10
MHUB7	2 1/2"	1	10	10
MHUB8	3"	1	5	5
MHUB9	3 1/2"	1	5	5
MHUB10	4"	1	2	2
MHUB11	5"	1	1	1
MHUB12	6"	1	1	1

CP Sealing Locknuts

UL File No. E-19189

CP Sealing Locknuts



U.S. Patent #4022262

- Integrally fused PVC gasket provides positive seal against water, oils and other liquids.
- Designed for use with raintight, watertight and oiltight enclosures, NEMA 2, 3, 3R, 4 and 12.

Only one Sealing Locknut is required to:

- functionally replace rigid threaded enclosure connectors.
- provide raintight, watertight, or oiltight seal in any position.
- provide positive ground connection.
- provide economies in installation and fitting costs.
- UL Listed Raintight.
- UL Listed Liquidtight.
- Can be used with either sheet metal or standard cast metal boxes.
- CSA Certified watertight.
- 1/2" – 2" Heavy-duty steel.
- 2 1/2" – 6" Malleable iron.

Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
SL1	1/2"	100	100	2
SL2	3/4"	50	500	2
SL3	1"	25	250	3
SL4	1 1/4"	25	250	8
SL5	1 1/2"	25	100	10
SL6	2"	25	100	14
SL7	2 1/2"	10	50	36
SL8	3"	10	50	38
SL9	3 1/2"	10	50	58
SL10	4"	5	25	72
SL11	5"	2	2	110
SL12	6"	1	1	190