

# LFZVC65/72NP Series



## Features

- Universal Input / Desktop Style.
- Convection cooled.
- Efficiency to 85%.
- EN55022-B-Level B.
- Energy Star IV Compliant / CEC Compliant.
- -10°C to 50°C Operating.
- Class 1 Product.

## Electrical Specifications


AC Input	90 to 264V
Input Frequency	47-63 Hz
Input Current	1.8A Max
Efficiency <sup>1</sup>	85%
Hold-up Time	10ms
Output Power	65 to 72 W
Line Regulation	+/-2.0% Max.
Load Regulation	+/-5.0% Max.
Over Current Protection	Auto Recovery
Over Voltage Protection	Yes
Short Circuit Protection	Short term
Isolation Voltage	I/P-O/P: 3000 VAC
Operating Temperature	-10°C to +50°C De-Rate from 40° C @ 100% to 50°C @ 75% Load
Storage Temperature	-20 to +85°C
Relative Humidity	20% to 90% RH
Cooling	Convection

Model Number	Voltage	Max. Load	Min. Load <sup>2</sup>	Wattage
ZVC65NP19E4	+19 V	3.42 A	0.0 A	65W
ZVC65NP19E8	+19 V	3.42 A	0.0 A	65W
ZVC65NP24E4	+24 V	2.7 A	0.0 A	65W
ZVC65NP24E8	+24 V	2.7 A	0.0 A	65W
ZVC72NP36E4	+36 V	2.0 A	0.0 A	72W
ZVC72NP36E8	+36 V	2.0 A	0.0 A	72W
ZVC72NP48E4	+48 V	1.5 A	0.0 A	72W
ZVC72NP48E8	+48 V	1.5 A	0.0 A	72W

## Mechanical Specifications

AC Input Connector	IEC320-C14 OR C8
DC Output Connector	Rt angle Jack Connector ID : 2.54, OD : 5.54 & L : 9.5
Dimensions	110.5mm x 53.0mm x 30.5mm with C8      117.0mm x 53.0mm x 31.5mm with C14
Weight	250 g
<b>EMC</b>	
CEC Mark	Complies with standby power ( @ no load ) < 0.5 W.
Conducted Emissions	EN55022,CISPR22, FCC Part 15 Class B
EMC Standards	EN61000-3-2,3 EN61000-4-2,3,4,5,6,8,11
<b>Safety</b>	
Safety Standard(s)	UL 60950-1, CE, IEC 60950-1 and EN60950-1
Approval Agency	UL / TUV

## Mechanical Drawing



Innovations in Power