



1. MATERIAL: ALNICO 5, SINTERED
2. GAUSS LEVEL: METER (F.W. BELL 4048 WITH TRANVERSE PROBE)
 TYPICAL VALUE: 850g MIN. TO 1300g MAX.
 NOTE: GAUSS VALUE MEASURED WITH PROBE HELD DIRECTLY AGAINST THE END OF THE MAGNET WITH THE HALL EFFECT CENTERED ON THE MAGNET AXIS.
3. MAGNETIZATION DIRECTION: PARALLEL TO LENGTH
4. DIMENSIONS: ARE IN INCHES
5. SQUARENESS: 1°
6. PACKING: PREFERRED METHOD IS 100 MAGNETS SHRINK WRAPPED ON CARDBOARD FLATS.
 OTHER METHODS MAY BE ACCEPTABLE WITH APPROVAL.
 MAXIMUM WEIGHT IS 25 Lbs. PER BOX.

H-31 MAGNET							H A M L I N, Inc.			DCR No.
AI	UPDATE PACKAGING	A0854	JC	3/9/94	JC	3/15/94	Dwn. TM	DATE 4/10/68	250-70-207	
REV.	DESCRIPTION OF REVISION	DCR No.	BY	DATE	APP.	DATE	App'd FH	DATE 4/16/68	Page 1 of 1	