



Excerpt from Master Catalogue Wiring Duct

Specifically For You



Wire Management Wiring Duct - BA7

Flammability: Self extinguishing UL94V-0. Maintains dimensional stability under heat:

Other colors available

Halogen-free version available

Includes Base and Cover 2 Meter Lengths -5°c to 60°c



Type Size Color

BA7 Grey 2 Meters Grey - RAL7030

Approvals

(IP (B)


Dimensions Width x Height mm (nominal inch)
25 x 25 (1" x 1")
25 x 40 (1" x 1 1/2")
25 x 60 (1" x 2")
25 x 80 (1" x 3")
40 x 25 (1 1/2" x 1")
40 x 40 (1 1/2" x 1 1/2")
40 x 60 (1 1/2" x 2")
40 x 80 (1 1/2" x 3")
60 x 40 (2" x 1 1/2")
60 x 60 (2" x 2")
60 x 80 (2" x 3")

(
25 x 40 (1" x 1 1/2")							
25 x 60 (1" x 2")							
25 x 80 (1" x 3")							
40 x 25 (1 1/2" x 1")							
40 x 40 (1 1/2" x 1 1/2")							
40 x 60 (1 1/2" x 2")							
40 x 80 (1 1/2" x 3")							
60 x 40 (2" x 1 1/2")							
60 x 60 (2" x 2")							
60 x 80 (2" x 3")							
60 x 100 (2" x 4")							
80 x 40 (3" x 1 1/2")							
80 x 60 (3" x 2")							
80 x 80 (3" x 3")							
80 x 100 (3" x 4")							
100 x 40 (4" x 1 1/2")							
100 x 60 (4" x 2")							
100 x 80 (4" x 3")							
100 x 100 (4" x 4")							
120 x 60 (5" x 2")							


	Part Number	Std. Pack of 2 m lengths	Part Number Model Number	Part Number Model Number	Part Number Model Number
	34.285.2525.0) 25			
	34.285.4025.0) 24			
	34.285.6025.0	30			
	34.285.8025.0) 10			
	34.285.2540.0) 24			
	34.285.4040.0) 25			
	34.285.6040.0) 20			
	34.285.8040.0	10			
	34.285.4060.0) 20			
	34.285.6060.0) 12			
	34.285.8060.0) 10			
	34.285.1060.0	8			
	34.285.4080.0) 15			
	34.285.6080.0) 10			
	34.285.8080.0) 6			
	34.285.1080.0	8			
	34.285.4100.0) 10			
	34.285.6100.0) 8			
	34.285.8100.0) 6			
	34.285.1100.0	6			
	34.285.6120.0) 6			
	34.285.8120.0) 8			


120 x 80 (5" x 3")






BA7A | HA7 lateral punched openings







for duct height 40 mm



for duct height 60 mm




for duct height 80 mm



for duct height 100 mm

BA7A | BA7B | B7A | HA7 bottom holes EN50085




for duct width 25 mm




for duct width 40 mm




for duct width 60 mm



for duct width 80 mm



for duct width 100 mm



for duct width 120 mm



Wieland Electric Inc.

1 800-Wieland (943-5263) Tel. (905) 829-8414 Fax. (905) 829-8413 www.wieland-electric.com info@wieland-electric.com

Industrial technology

Solutions for the control cabinet

- DIN rail terminal blocks
 - Screw and spring connection technology
 - Wire cross sections up to 240 mm²
 - Numerous special functions
 - Software solutions interfacing to CAE systems
- Safety
 - Safety sensors
 - Safety relays
 - Modular safety systems with fieldbus link
- PLC and fieldbus components
 - Standard applications in IP20
 - Increased environmental conditions with railroad and ship approvals
- Interface
 - Coupling relays, semiconductor switches
 - Measuring and monitoring relays
 - Timer and switching relays
 - Analog modules
 - Passive interfaces
 - Power supply units
 - Overvoltage protection

Solutions for field applications

- Remote automation technology
 - Power distribution
 - Fieldbus interfaces and motor starters
- Connectors for industrial applications
 - Square and round connectors
 - Aluminum or plastic housings
 - Degree of protection up to IP68
 - Current-carrying capacity up to 100A
 - Connectors for hazardous areas
 - Modular, application specific technology

PC board terminals and connectors

- Screw or spring clamp connection technology
- Spacings: 3.5 mm to 10.16 mm
- Reflow or wave soldering process

Building and installation technology

- Building installation systems
- Main power supply connectors IP20/IP65...IP68
- Bus connectors
- Combined connectors
- Low-voltage connectors
- Power distribution system with flat cables
- Distribution systems
- Bus systems in KNX, LON and radio technology
- DIN rail terminal blocks for electrical installations
- Overvoltage protection

contacts are green. **Product Range**