

## JMGAT-5M Product Details



**JMGAT-5M**  
(1617110-7)

TE Internal Number: 1617110-7

 [Active](#)

### Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- MGAT .100 Grid Relay Series
- Input Voltage = 5 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 1 A
- Non Polarized, Monostable Coil Magnetic System

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [RELAY](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Termination Type = Long Leads

#### Electrical Characteristics:

- Input Voltage (VDC) = 5
- Contact Current Rating (A) = 1
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil Resistance ( $\Omega$ ) = 39
- MOSFET Driver = With
- Coil Power Measurement = Milliwatts
- Coil Power, Nominal (mW) = 641
- Actuating System = DC
- Shock = 75 G's, 6ms
- Vibration = 30G's, 10 to 3000Hz

#### Body Related Features:

- [Series](#) = MGAT .100 Grid Relay

#### Contact Related Features:

- Mounting Options = PC Board
- Enclosure Type = Hermetically Sealed
- Approved Standards = M28776 Qualified, M Level

#### Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Coil Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = With

#### Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M28776/6-001M
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Conditions for Usage:

- Temperature Range ( $^{\circ}\text{C}$ ) = -65 - +125

#### Other:

- Brand = CII

 [BOOKMARK](#) 

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat with Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on:

