

Datasheet

Art.No. 76.360.4035.1

Hood BAS GOT GG 40HM40 50 A1

revos BASIC 500V size 16H hood with threaded collar M40, lateral cable entry, high design, single locking lever



Art.No.	76.360.4035.1
EAN	4015573802322
Order unit	1 pieces

Approvals

Technical data

General

Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16H
Model	male
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	40
Thread size PG	
Hinged lid	No
EMC-version	No

Classification

ECLASS 8.1	27440202
ETIM 6.0	EC000437
ETIM 5.0	EC000437
ETIM 4.0	EC000437

ETIM 3.0	EC000437
----------	----------

Drawings

gezeichnete Ausführung
drawn Version
76.360.4035.1

Weitere Daten siehe Katalog
Further data see catalog

Teilenummer	Type
76.360.4035.0	BAS GOT GG 16HM4.0 50 A0
76.360.4035.1	BAS GOT GG 16HM4.0 50 A1
76.360.4035.2	BAS GOT GG 16HM4.0 50 A2
76.360.4035.4	BAS GOT GG 16HM4.0 50 A4
76.360.4035.5	BAS GOT GG 16HM4.0 50 A5

IP65
Kabelverschraubung M40/
cable gland M40
76.360.4035.5

IP54
Kabelverschraubung M40
mit Zugentlastung/
cable gland M40
with strain relief
76.360.4035.4

IP54
Kabelverschraubung M40
cable gland M40
76.360.4035.0

Gewinde M40
thread M40
76.360.4035.1

Stiefzen M40
connection M40
76.360.4035.2

<p>Hersteller/Manufacturer: wieland Industrietechnik Industrietechnik</p>		<p>Typ: GEHÄUSEOBERTEIL hood size 16H M 40</p>
<p>Bestellnummer/Order number: 76.360.4035.0 01K</p>	<p>Material/Material: T</p>	<p>Produktionsjahr/Production year: 2012</p>
<p>Druck/Pressure: 1000</p>	<p>Temperatur/Temperature: 120</p>	<p>Umweltbedingungen/Environmental conditions: 1</p>
<p>IP-Schutzart/Protection class: IP65</p>	<p>Material/Material: 1:1</p>	<p>Druck/Pressure: 1000</p>
<p>Druck/Pressure: 1000</p>	<p>Temperatur/Temperature: 120</p>	<p>Umweltbedingungen/Environmental conditions: 1</p>