

Datasheet

Art.No. 83.040.0106.0

IP switch WIENET UMS 8G

wieNET IP Switch, 8 TP-RJ45-Ports, transfer rate 10/100/1000 MBit/s, unmanaged switch, Autonegotiation, Autosensing, Autocrossing-function, redundant power supply, supply voltage: 9-48 V, vertical mount



Art.No.	83.040.0106.0
EAN	4049088132742
Order unit	1 pieces

Approvals



Technical data

Allgemein

Mounting method	DIN rail (top hat rail)
Degree of protection (IP)	IP50
Housing material	Metal
Manageable	No
Ethernet	Yes
Power over Ethernet	No
Fast Ethernet	Yes
Gigabit Ethernet	Yes
Number of ports 10/100 Mbps RJ45	0
Diagnostic LEDs	Power/Link status/Data/Data rate
10 Gigabit Ethernet	No
Number of ports 10/100/1000 Mbps RJ45	8
Number of ports 100 Mbps SC	0
Number of 100 Mbps ST-Ports	0

Technical data

Voltage type	DC
Min. operating temperature	-10 °C
Max. operation temperature	70 °C
Redundant power supply	2 power inputs

Supply circuit

Voltage type	DC
--------------	----

Operating voltage min.	9 V
Operating voltage max.	48 V

Dimensions


Depth	80 mm
Width	45 mm
Height	90 mm

Classification

ECLASS 8.1	19170106
ETIM 6.0	EC000734
ETIM 5.0	EC000734
ETIM 4.0	EC000734
ETIM 3.0	EC000734



Drawings



B3_040_0106_001K_2 CADW4033 Koetzner 2018-01-08T10:09:56 1.000