

Wieland Electric



Datasheet

Item No. R1.188.0530.1

Two-hand control relay SNZ4052K-A AC/DC 24V (B)

Base unit, two-channel control, 2x N.C./N.O. startup inhibit circuit, cross circuit monitoring, synchronous time monitoring, 2 enab ling current paths, 1 signalling output, AC/DC 24 V 50-60Hz, screw-terminals pluggable



Item No.	R1.188.0530.1
EAN	4015573808515
order unit	1 Piece(s)

Approvals









Technical data

General		
Suited for safety functions	Yes	
Category according to EN 954-1	4	
Feedback circuit	Yes	
Start contact	No	
Performance level acc. to EN ISO 13849-1	e	
SIL according to IEC 62061	3	
Rail mounting possible	Yes	
Applicable in accordance with EN 574	Type III C	
Connection Data		
Detachable clamps	Yes	
Type of electric connection	Screw connection	
Output circuit		
Outputs, signalling function, undelayed, with contact	1	
Outputs, signalling function, delayed, with contact	0	
Outputs, safe, undelayed, with contact	2	
Outputs, safe, delayed, with contact	0	
Control circuit		
Type of switch function of the inputs	Change-over contact	
Supply circuit		
Min. rated control supply voltage at AC 50 Hz	20.4 V	
Max. rated AC voltage for controls, 50 Hz	26.4 V	
Min. rated DC voltage for controls	20.4 V	





Max. rated DC voltage for controls	26.4 V	
Min. rated control supply voltage at DC	20.4 V	
Rated control supply voltage at AC 60HZ	20.4 V	
Rated control supply voltage at AC 50HZ	26.4 V	
Dimensions		
Depth	114 mm	
Width	22.5 mm	