

Datasheet

Item No. Z5.507.1553.0

Cable screw gland M25x1,5

Cable gland IP 68 M25x1,5, plastic



Item No.	Z5.507.1553.0
EAN	4015573587175
order unit	10 Piece(s)

Technical data

General

Thread size M	25
Thread length	11 mm
Min. cable diameter	9 mm
Max. cable diameter	16 mm
Degree of protection (IP)	IP68
Material	Plastic
Surface	Other
Colour	Light grey
Wrench width	28 mm
Shock resistant	Yes
Bend radius protection/trumpet flare	No
Cross bracket strain relief	No
Type of sealing	Rubber-/neoprene ring
Separable screw gland	No
Multi seal area	No
Thread type	Metric
Halogen free	Yes
Inflammability class of insulation material acc. with UL94	V0



Drawings

<p>1 A B C D E F</p>	<p>2 3 4 5 6</p>	<p>1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 M1 M2 M3 L G I 11 12 13</p>	<p>1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 M1 M2 M3 L G I 11 12 13</p>	<p>1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 M1 M2 M3 L G I 11 12 13</p>	<p>1 2 3 4 5 6</p>																																																																										
<table border="1" style="margin: auto;"> <tr> <td style="width: 20px;">.F</td> <td>.0=lichtgrau/light grey RAL 7035 .1=schwarz/black RAL 9005</td> </tr> </table>						.F	.0=lichtgrau/light grey RAL 7035 .1=schwarz/black RAL 9005																																																																								
.F	.0=lichtgrau/light grey RAL 7035 .1=schwarz/black RAL 9005																																																																														
<table border="1" style="margin: auto;"> <thead> <tr> <th>Teilenummer part number</th> <th>MXx1,5</th> <th>Klemmbereich clamping range</th> <th>I</th> <th>L</th> <th>SW</th> </tr> </thead> <tbody> <tr> <td>Z5.507.1953.F</td> <td rowspan="2">M40x1,5</td> <td>16-28</td> <td>11</td> <td>45</td> <td>46</td> </tr> <tr> <td>Z5.507.1853.F</td> <td>16-28</td> <td>13</td> <td>48</td> <td>46</td> </tr> <tr> <td>Z5.507.1753.F</td> <td rowspan="2">M32x1,5</td> <td>10-21</td> <td>11</td> <td>38</td> <td>36</td> </tr> <tr> <td>Z5.507.1653.F</td> <td>18-25</td> <td>11</td> <td>39</td> <td>42</td> </tr> <tr> <td>Z5.507.1553.1</td> <td rowspan="3">M25x1,5</td> <td>13-18</td> <td>11</td> <td>30</td> <td>33</td> </tr> <tr> <td>Z5.507.1553.0</td> <td>9-16</td> <td>11</td> <td>28</td> <td>28</td> </tr> <tr> <td>Z5.507.1453.1</td> <td>7-16</td> <td>11</td> <td>30</td> <td>28</td> </tr> <tr> <td>Z5.507.1353.F</td> <td rowspan="2">M20x1,5</td> <td>6-12</td> <td>9</td> <td>28</td> <td>24</td> </tr> <tr> <td>Z5.507.1253.F</td> <td>4-9</td> <td>9</td> <td>28</td> <td>24</td> </tr> <tr> <td>Z5.507.1153.1</td> <td rowspan="4">M16x1,5</td> <td rowspan="2">4-8</td> <td>8</td> <td>24</td> <td>22</td> </tr> <tr> <td>Z5.507.1153.0</td> <td>8</td> <td>24</td> <td>20</td> </tr> <tr> <td>Z5.507.1053.1</td> <td rowspan="2">2-7</td> <td>8</td> <td>24</td> <td>20</td> </tr> <tr> <td>Z5.507.1053.0</td> <td>8</td> <td>24</td> <td>20</td> </tr> </tbody> </table>						Teilenummer part number	MXx1,5	Klemmbereich clamping range	I	L	SW	Z5.507.1953.F	M40x1,5	16-28	11	45	46	Z5.507.1853.F	16-28	13	48	46	Z5.507.1753.F	M32x1,5	10-21	11	38	36	Z5.507.1653.F	18-25	11	39	42	Z5.507.1553.1	M25x1,5	13-18	11	30	33	Z5.507.1553.0	9-16	11	28	28	Z5.507.1453.1	7-16	11	30	28	Z5.507.1353.F	M20x1,5	6-12	9	28	24	Z5.507.1253.F	4-9	9	28	24	Z5.507.1153.1	M16x1,5	4-8	8	24	22	Z5.507.1153.0	8	24	20	Z5.507.1053.1	2-7	8	24	20	Z5.507.1053.0	8	24	20
Teilenummer part number	MXx1,5	Klemmbereich clamping range	I	L	SW																																																																										
Z5.507.1953.F	M40x1,5	16-28	11	45	46																																																																										
Z5.507.1853.F		16-28	13	48	46																																																																										
Z5.507.1753.F	M32x1,5	10-21	11	38	36																																																																										
Z5.507.1653.F		18-25	11	39	42																																																																										
Z5.507.1553.1	M25x1,5	13-18	11	30	33																																																																										
Z5.507.1553.0		9-16	11	28	28																																																																										
Z5.507.1453.1		7-16	11	30	28																																																																										
Z5.507.1353.F	M20x1,5	6-12	9	28	24																																																																										
Z5.507.1253.F		4-9	9	28	24																																																																										
Z5.507.1153.1	M16x1,5	4-8	8	24	22																																																																										
Z5.507.1153.0			8	24	20																																																																										
Z5.507.1053.1		2-7	8	24	20																																																																										
Z5.507.1053.0			8	24	20																																																																										
<p>frei von lackbenetzungsstörenden Substanzen free from substances which inhibit paint adhesion</p>																																																																															
<p>Weitere Daten siehe Katalog further data see catalog</p>																																																																															
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="2"> Fertigung nach DIN 7167/Execution system acc. to DIN 7167. This DIN standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances. </td> <td colspan="2"> 2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared! </td> </tr> <tr> <td colspan="2"> Toleranzzone nach General tolerance </td> <td colspan="2"> CAD - Zeichnung, keine manuelle Änderungen. CAD - drawing, no manual modifications allowed. </td> </tr> <tr> <td colspan="2"> Veränderring: none First Use: </td> <td colspan="2"> Zeichnung Nr./Drawing No. </td> </tr> <tr> <td colspan="2"> 2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared! </td> <td colspan="2"> Made in mm/Dimensions are in mm </td> </tr> <tr> <td colspan="2"> b 27.09.2006/ </td> <td colspan="2"> Type </td> </tr> <tr> <td colspan="2"> a 16.09.2006/ </td> <td colspan="2"> Benennung/Title </td> </tr> <tr> <td colspan="2"> Index </td> <td colspan="2"> KABELVERSCHRAUBUNG für Anschlussdosen cable gland for junction boxes </td> </tr> <tr> <td colspan="2"> Änderung/Revision </td> <td colspan="2"> 01-PEB-05/91 </td> </tr> </table>						Fertigung nach DIN 7167/Execution system acc. to DIN 7167. This DIN standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances.		2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared!		Toleranzzone nach General tolerance		CAD - Zeichnung, keine manuelle Änderungen. CAD - drawing, no manual modifications allowed.		Veränderring: none First Use:		Zeichnung Nr./Drawing No.		2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared!		Made in mm/Dimensions are in mm		b 27.09.2006/		Type		a 16.09.2006/		Benennung/Title		Index		KABELVERSCHRAUBUNG für Anschlussdosen cable gland for junction boxes		Änderung/Revision		01-PEB-05/91																																											
Fertigung nach DIN 7167/Execution system acc. to DIN 7167. This DIN standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances.		2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared!																																																																													
Toleranzzone nach General tolerance		CAD - Zeichnung, keine manuelle Änderungen. CAD - drawing, no manual modifications allowed.																																																																													
Veränderring: none First Use:		Zeichnung Nr./Drawing No.																																																																													
2006 ISO Stahlwerks- und Oxfidationsklasse nach ISO 10445/453 ist anzubringen. Conformity with Wieland document 09-100-05/03 (List of prohibited / favorable hazardous substances) to be declared!		Made in mm/Dimensions are in mm																																																																													
b 27.09.2006/		Type																																																																													
a 16.09.2006/		Benennung/Title																																																																													
Index		KABELVERSCHRAUBUNG für Anschlussdosen cable gland for junction boxes																																																																													
Änderung/Revision		01-PEB-05/91																																																																													