



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

| Circuit Board Indicators - Through Hole Indicators | |
|----------------------------------------------------|-------------------------|
| P/N# 5219462F | 5 mm Lens |
| Description | Discrete LED Lamp |
| Package Options | 100 pieces per bag |
| Product Type | Through Hole Indicators |
| Sub Product Type | Discrete LED |
| Configuration | 5 mm Lens |
| Viewing Angle | 60 degrees |
| Absolute Maximum Ratings (Ta = 25 °) | |
| Solder Temp | 260Å° for 5 sec |
| Operating Temp | -55~+100° C |
| Storage Temp | -55~+100° C |

Distributor Stock Check

Check stock with our distributors now.

5219462F

[check stock](#)

- [how to purchase](#)
- [sales contacts](#)
- [stock check](#)



search

[Product Line Search](#)

Please select a Product Line to search.

[find](#)

[Part # / Text Search](#)

Part No.:

Text Search:

[search](#)

Operating Characteristics

| | |
|----------------------------|---------------------|
| LED Position | |
| Color | Red / Green |
| Lamp Type | Bi-Color / Bi-Color |
| LED Type | AlGaAs / GaP |
| Intensity Min (mcd) | 29.0 / 12.6 |
| Intensity Typ (mcd) | 90.0 / 40.0 |
| Intensity Max (mcd) | |
| Fwd Voltage Min | |
| Fwd Voltage Typ | 1.8 / 2.1 |
| Fwd Voltage Max | 2.4 / 2.8 |
| Dom Wavelength Min (nm) | |
| Dom Wavelength Typ (nm) | |
| Dom Wavelength Max (nm) | |
| Power Dissipation Max (mW) | |
| Backlighting | |
| Pitch Between Vertical | |
| Pitch Between Horizontal | |
| Lum Intensity Min | |
| Lum Intensity Typ | |
| Lum Intensity Max | |

- [quick links](#)
- [Dialight Corporate Video](#)
- [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. \[View PDF File\]\(#\)](#)
- [Application Notes](#)
- [FAQs](#)
- [Dialight Ltd \(UK\)](#)
- [Dialight Garufo](#)
- [Dialight BLP](#)
- [LumiDrives](#)