


# Specification Sheet

## EYECAP-SI for Terminals

EYECAP-SI



Size(mm)	AWG	B	b	D	A	L	T	E	PART NO.				
									BLACK	RED	BLUE	YELLOW	GREEN
1.5	20~16	2.8	5.9	2.8	13.1	7.6	0.8	5.3	BK	R	B	Y	G
2.5	16~14	3.4	6.9	3.5	13.8	8.1	0.8	5.4	BK	R	B	Y	G
4	14~12	3.8	7.5	4.3	16.2	9.6	0.8	7.0	BK	R	B	Y	G
6	12~10	4.8	8.7	5.0	17.4	9.7	1.0	7.7	BK	R	B	Y	G
10	8	6.2	10.1	6.7	20.4	10.9	1.1	8.3	BK	R	B	Y	G
16	6	7.0	12.5	8.3	23.5	13.0	1.4	10.0	BK	R	B	Y	G
25	4	10.1	15.5	10.2	31.5	17.1	1.5	14.6	BK	R	B	Y	G
35	2	10.6	16.5	10.8	35.1	19.0	1.6	16.8	BK	R	B	Y	G
50	1	12.4	18.2	12.1	37.7	19.1	1.8	19.1	BK	R	B	Y	G
70	2/0	14.2	21.8	15.2	38.3	19.5	1.9	20.5	BK	R	B	Y	G
95	3/0	15.9	23.5	16.2	42.6	21.6	2.0	21.9	BK	R	B	Y	G
120	250Kcmil	18.5	26.8	20.9	47.3	25.8	2.1	22.0	BK	R	B	Y	G
150	300Kcmil	19.9	30.3	23.7	55.5	27.5	2.3	30.8	BK	R	B	Y	G
185	350Kcmil	22.9	33.9	25.3	64.0	33.3	2.3	32.9	BK	R	B	Y	G
240	500Kcmil	25.4	39.7	30.1	70.0	36.6	2.4	37.7	BK	R	B	Y	G
300	600Kcmil	27.0	45.8	34.9	74.6	38.4	2.6	45.0	BK	R	B	Y	G


Example for Part Number

EYECAP-SIT (A) 1.5 BK  
① ② ③

- ① TYPE : (A)(Solderless terminal lugs type)  
(B)(Tubular terminal lugs type)
- ② SIZE : 1.5sq ~ 300sq
- ③ COLOR : BK(Black), R(RED), B(BLUE), Y(YELLOW), G(GREEN)

## EYECAP-SIT for Lugs

EYECAP-SIT



Size(mm)	AWG	B	b	D	A	L	T	E	PART NO.				
									BLACK	RED	BLUE	YELLOW	GREEN
25	4	8.6	13.9	9.0	10.3	25.3	1.2	14.0	BK	R	B	Y	G
35	2	10.2	15.5	10.5	10.1	27.5	1.3	17.3	BK	R	B	Y	G
50	1	11.6	17.2	11.5	12.2	43.2	1.5	34.3	BK	R	B	Y	G
70	2/0	13.8	20.3	13.9	12.3	48.2	1.8	36.7	BK	R	B	Y	G
95	3/0	16.5	22.8	16.0	18.8	56.2	1.9	36.4	BK	R	B	Y	G
120	250Kcmil	18.3	24.6	18.0	18.8	61.6	1.9	40.1	BK	R	B	Y	G
150	300Kcmil	20.8	27.2	21.4	24.0	66.7	2.0	40.1	BK	R	B	Y	G
185	350Kcmil	22.1	31.0	22.7	23.2	74.0	2.1	48.6	BK	R	B	Y	G
240	500Kcmil	28.1	35.1	26.8	25.5	83.0	2.1	54.5	BK	R	B	Y	G
300	600Kcmil	29.0	37.0	28.2	25.5	95.1	2.3	66.5	BK	R	B	Y	G
400	750Kcmil	32.5	40.9	32.8	25.7	98.9	2.5	72.7	BK	R	B	Y	G

Example for Part Number

EYECAP-SIT (B) 25 BK  
① ② ③

- ① TYPE : (A)(Solderless terminal lugs type)  
(B)(Tubular terminal lugs type)
- ② SIZE : 25sq ~ 500sq
- ③ COLOR : BK(Black), R(RED), B(BLUE), Y(YELLOW), G(GREEN)