225 Watt Industrial



Features

- 4 x 2 x 1 Inches Form factor
- 225 Watts with Forced Air Cooling
- Efficiencies upto 94%
- -40 to 70 degree operating temperature*
- 12V / 0.5A Fan Output, Thermal Shut-Down feature
- 3.37m Hours, Telcordia -SR332-issue 3 MTBF
- No Load Power < 0.5W

	Electrical Specifications	
Input Voltage	85-264 VAC/390 VDC, Universal (Derate from 100% at 100V AC to 95% at 85V AC)	
Input Frequency	47-63 Hz	
Input Current	115 VAC: 2.2 A max. 230 VAC: 1.1 A max.	
No Load Power	less than 0.5W typical	
Inrush Current	115 VAC – 25 A, 230 VAC – 45 A, 264 VAC – 75 A	
Leakage Current	300 uA Typical, (N.A. For Class II Option) Touch current <100uA	
Efficiency	94%(48V), 93%(24V,30V), 92%(12V,15V)	
Hold-up Time	at 225W:10 ms ; 110W: 16 ms	
Power Factor	exceeds 0.95 with Full Load	
Output Power	225W with 13 CFM, upto 120W Convection	
Line Regulation	+/-0.5%	
Load Regulation	+/-0.5%	
Transient Response	25% step load change, at 0.1A/uS slew rate, 50% duty cycle, 50Hz=4%,	
	recovery time < 5 ms	
Rise Time	55ms typical	
Set Point Tolerance	+/-1%	
Output Voltage Adjustment	+/-3% (Ref. Note 8)	
Over Current Protection	>110%	
Over Voltage Protection	110 to 140%	
Short Circuit Protection	Hiccup mode	
Switching Frequency	PFC - 70 to 130 KHz ,PWM - 50-80 KHz	
Operating Temperature ⁷	- 40 to +70°C, * -40 to 0°C startup is guaranteed with spec deviation	
Storage Temperature	-40 to +85°C	
Relative Humidity	5% to 95%, noncondensing	
Altitude	Operating: 16,000 ft.; Nonoperating: 40,000 ft.	
MTBF	3.37m Hours, Telcordia -SR332-issue 3	
Isolation Voltage	Input to Output – 3000V AC for ITE application	
	Input to GND - 1500 VAC (Not Applicable For Class II Option)	
Cooling	225W with 13 CFM forced air cooling ⁶ (refer Mechanical Drawing)	
	upto 120 W with natural convection cooling ⁶ (refer Derating Curve)	

4EM-18-331 39-DE60-46750-002 / D6

Model Number	Description	Voltage	Max. Load (Convection) (112.5W)	Max.Load (Convection) (120W)	Max. Load (13 CFM)	Min. Load	Ripple ¹
LFWLP225-1001	with Screw Terminal	12 V	9.37A	10.0A	18.75A	0.0 A	1%
LFWLP225-1301	with Molex Connector	12 V	9.37A	10.0A	18.75A	0.0 A	1%
LFWLP225-1002	with Screw Terminal	15 V	7.5A	8.0A	15A	0.0 A	1%
LFWLP225-1302	with Molex Connector	15 V	7.5A	8.0A	15A	0.0 A	1%
LFWLP225-1003	with Screw Terminal	24 V	4.68A	5.0A	9.37A	0.0 A	1%
LFWLP225-1303	with Molex Connector	24 V	4.68A	5.0A	9.37A	0.0 A	1%
LFWLP225-1004	with Screw Terminal	48 V	2.34A	2.5A	4.68A	0.0 A	1%
LFWLP225-1304	with Molex Connector	48 V	2.34A	2.5A	4.68A	0.0 A	1%
LFWLP225-1005	with Screw Terminal	30 V	3.75A	4.0A	7.5A	0.0 A	1%
LFWLP225-1305	with Molex Connector	30 V	3.75A	4.0A	7.5A	0.0 A	1%
LFWLP225-1006	with Screw Terminal	58 V	1.94A	2.07A	3.88A	0.0 A	1%
LFWLP225-1306	with Molex Connector	58 V	1.94A	2.07A	3.88A	0.0 A	1%
LFWLP225-CK metal co	ver kit accessory						

	Connecto	ors	
J1	Pin 1	AC LINE	
	Pin 2	NOT FITTED	
	Pin 3	AC NEUTRAL	
J2 Option 1 & 2	Pin 1,2,3	V1 +VE	
	Pin 4,5,6	V1 -VE	
J3	Pin 1	FAN +VE	
(Pin 2	FAN -VE	


Notes


- 1. Ripple is peak to peak with 20 MHz bandwidth and 10 μ F (Tantalum capacitor) in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.
- 2. Class II means without input Earth pin. Ensure non-metallic mounting stud when installing a class II product. Please add suffix –II to the model number to order a class II version of the same product. For eg WLP225-1001-II will be a class II version of 12V.
- 3. Combined output power of main output, fan supply shall not exceed max. Power rating.
- 4. Fan supply output voltage tolerance including set point accuracy, line and load regulation is +/-10% and Ripple and noise is less than 10%.
- 5. Specifications are for nominal input voltage, 25°C unless otherwise stated.
- 6. 225W with 13CFM forced air cooling and 12OW with natural convection cooling at 100 to 264VAC.
- 7. Output ripple can be more than 10% of the output voltage.
- 8. Adjustment potentiometer is located on the SMT side of the PCB.
- 9. When used in Cover Kit, de-rate output power to 70 % under all operating conditions




	Mechanical Specifications	3		
AC Input Connector (J1)				
	Mating: 09-50-3031; Pins: 08-50-0106			
DC Output Connector (J2) Option 1 (Screw Terminal)	Molex: 39357 Series or equivalent			
DC Output Connector (J2) Option 2	Molex: 26-60-4060			
(Molex Connector)	Mating: 09-50-3061; Pins: 08-50-0106			
Aux (Fan) Output(J3)	AMP :640456-2			
	Mating: 640440-2			
Dimensions	4 x 2 x 1 inches			
	(101.60 x 50.8x 25.4 mm)			
Weight	200 gm approx			
	EMC			
Parameter	Conditions/Description	Criteria		
Conducted Emissions	EN55032-B, CISPR22-B, FCC PART15-B	Pass		
Radiated Emissions	EN 55032 A	Pass		
		Level B with external core (King core K5B		
		RC 25x12x15-M in input cable)		
Input Current Harmonics	EN 61000-3-2	Class D		
Voltage Fluctuation and Flicker	EN 61000-3-3	Pass		
ESD Immunity	EN 61000-4-2	Level 3, Criterion A		
Radiated Field Immunity	EN 61000-4-3	Level 3, Criterion A		
Electrical Fast Transient Immunity	EN 61000-4-4	Level 3, Criterion A		
Surge Immunity	EN 61000-4-5	Level 3, Criterion A		
Conducted Immunity	EN 61000-4-6	Level 3, Criterion A		
Magnetic Field Immunity	EN 61000-4-8	Level 3, Criterion A		
Voltage dips, interruptions	EN 61000-4-11	Criterion A & B		
	Safety			
CE Mark	Complies with LVD Directive			
Approval Agency	Nemko, UL, C-UL , CCC			
Safety Standard(s) EN60950-1, IEC60950-1 (ed.2), UL 60950 (ed.2), CSA C22.2 No.60950-1 (ed.2), Clas				
	GB4943. 1-2011 ; GB9254-2008 ; GB17625. 1-	2012		
Safety File Number(s)	Class-I : Nemko: Certificate No. P1421907	72, CB Certif. No.:N083507		
	Class-II: Nemko: Certificate No. P14219134, CB Certif. No.N083790			
	UL: Certificate Number 20141217-E15056	55		


4EM-18-331 39-DE60-46750-002 / D6












4EM-18-331 39-DE60-46750-002 / D6

Mechanical Drawing

Option 2



MECHANICAL OUTLINE DIMENSIONS ALL DIMENSIONS ARE IN INCHES[MM] GEN TOLERANCE: +/-0.04[+/-1.0MM]

Notes: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following

- 1. Stand off, used to mount PCB has OD of 5.4 mm max.
- 2. Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3. Washer, if used, to have dia of 6.5 mm max.

