

D-SUBMINIATURE CONNECTORS (Cont.)






Fig. 1



Fig. 2



Fig. 3



Fig. 4




Fig. 5



Fig. 6




Fig. 7



Fig. 8



Fig. 9



Fig. 10

Solder Cup Type D-Subminiature Connectors

Retail Part No.	Bulk Part No.	Fig. No.	Descrip.	Contact Rating	Wire Size	Insulator Material	Shell/Finish Material	Contact Material	No. of Pins	Solder Cup Type	A In. (mm)	B In. (mm)	C In. (mm)	D In. (mm)	E In. (mm)	F In. (mm)	G In. (mm)	H In. (mm)
	41-1111-BU	1	Male Plug	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Brass	9	DB9	1.213 (30.8)	.697 (17.7)	.984 (25)	.359 (9.14)	.496 (12.6)	.422 (10.72)	.759 (19.3)	.370 (9.4)
	41-2111-BU	2	Female Socket	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Phosphor Bronze	9	DB9	1.213 (30.8)	.640 (16.22)	.984 (25)	.308 (7.82)	.496 (12.6)	.422 (10.72)	.759 (19.3)	.370 (9.4)
	41-1211-BU	3	Male Plug	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Brass	15	DB15	1.539 (39.1)	1.025 (26.04)	1.311 (33.3)	.359 (9.14)	.496 (12.6)	.422 (10.72)	1.083 (27.5)	.236 (6)
	41-2211-BU	4	Female Socket	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Phosphor Bronze	15	DB15	1.539 (39.1)	.969 (24.6)	1.311 (33.3)	.308 (7.82)	.496 (12.6)	.422 (10.72)	1.083 (27.5)	.244 (6.2)
	41-1311-BU	5	Male Plug	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Brass	25	DB25	2.087 (53)	1.583 (40.21)	1.850 (47)	.378 (9.6)	.496 (12.6)	.422 (10.72)	1.626 (41.3)	.236 (6)
	41-2311-BU	6	Female Socket	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Phosphor Bronze	25	DB25	2.087 (53)	1.508 (38.3)	1.850 (47)	.308 (7.82)	.496 (12.6)	.422 (10.72)	1.626 (41.3)	.244 (6.2)
	41-2411-BU	7	Female Socket	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Phosphor Bronze	37	DB37	2.728 (69.3)	2.156 (54.76)	2.500 (63.5)	.308 (7.82)	.496 (12.6)	.422 (10.72)	2.272 (57.7)	.244 (6.2)

Hi-density Type D-Subminiature Connectors

Retail Part No.	Bulk Part No.	Fig. No.	Descrip.	Contact Rating	Wire Size	Insulator Material	Shell/Finish Material	Contact Material	No. of Pins	Solder Cup Type	A In. (mm)	B In. (mm)	C In. (mm)	D In. (mm)	E In. (mm)	F In. (mm)	G In. (mm)	H In. (mm)
	41-2115-BU	8	Male Plug	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Brass	15	HD15	1.213 (30.8)	.697 (17.7)	.984 (25)	.359 (9.14)	.496 (12.6)	.422 (10.72)	1.083 (27.5)	.236 (6)
	41-2116-BU	9	Female Socket	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Phosphor Bronze	15	HD15	1.213 (30.8)	.640 (16.22)	.984 (25)	.308 (7.82)	.496 (12.6)	.422 (10.72)	.759 (19.3)	.244 (6.2)
	41-2124-BU	10	Male Plug	5 Amps	20 AWG	2-piece Nylon	Zinc plated Brass	Brass	26	HD26	1.539 (39.1)	1.025 (26.04)	1.311 (33.3)	.359 (9.14)	.496 (12.6)	.422 (10.72)	1.083 (27.5)	.236 (6)