

Description

Single pole high performance thermal circuit breaker, with push-to-reset tease free, trip-free snap action mechanism (R-type TO CBE to EN 60934). Designed for threadneck panel mounting and for applications with a high fault current switching requirement. Approved to CBE standard EN 60934 (IEC 60934).

Typical applications

Motors, transformers, solenoids, battery chargers, power supplies, appliances, machinery, extra low voltage systems.

Ordering information

Type No.

4130 single pole thermal circuit breaker

Mounting

G threadneck panel mounting

Threadneck design

- 2** M12x1, knurled nut (bulk shipped)
- 4** M12x1, hex nut and knurled nut (bulk shipped)

Number of poles

- 1** single pole, thermally protected

Actuator configuration

- 1** black push button

Terminal design

- K4** terminal M6x8
screw and washer bulk shipped

Characteristic curve

- M1** medium delay

Current ratings

- 20...70 A**

4130 - G 2 1 1 - K4 M1 - 20 A ordering example



4130...

Technical data

For further details please see chapter: Technical Information

Voltage rating AC 240 V; DC 50 V

Current rating range 20...70 A

Typical life

AC 240 V:	20...70 A	100 operations at $2 \times I_N$, inductive
DC 50 V:	20...80 A	500 operations at $2 \times I_N$, resistive
		500 operations at $2 \times I_N$, inductive

Ambient temperature -30...+60 °C (-22...+140 °F)

Insulation co-ordination (IEC 60664) rated impulse withstand voltage 2.5 kV pollution degree 2 (reinforced insulation in the mounting area)

Dielectric strength operating area

test voltage
AC 3,000 V

Insulation resistance > 100 MΩ (DC 500 V)

Interrupting capacity I_{cn} 800 A

Interrupting capacity (UL 1077)

I_N	U_N	
20...70 A	AC 240 V	1,000 A
20...60 A	AC 120 V	3,500 A
70 A	AC 120 V	2,000 A
20...50 A	DC 50 V	3,500 A
60...70 A	DC 50 V	2,000 A

Degree of protection (IEC 60529/DIN 40050) operating area IP40
terminal area IP00

Vibration 8 g (57-500 Hz) ±0.61 mm (10-57 Hz)
to IEC 60068-2-6, test Fc
10 frequency cycles/axis

Shock

25 g (11 ms)
to IEC 60068-27, test Ea

Corrosion 96 hours at 5 % salt mist,
to IEC 60068-2-11, test Ka

Humidity 240 hours at 95 % RH
to IEC 60068-2-3, test Ca

Mass approx. 55 g


Standard current ratings and typical internal resistance values

Current rating (A)	Internal resistance (Ω)	Current rating (A)	Internal resistance (Ω)
20	< 0.02	40	< 0.01
25	< 0.02	50	< 0.01
30	< 0.02	60	< 0.01
35	< 0.02	70	< 0.01


Approvals

Authority	Voltage ratings	Current ratings
VDE (EN 60934)	AC 240 V; DC 50 V	20...70 A
UL	AC 240 V; AC 120 V; DC 50 V	20...80 A


Dimensions




Installation drawing



Internal connection diagram



Typical time/current characteristics



The time/current characteristic curve depends on the ambient temperature prevailing. In order to eliminate nuisance tripping, please multiply the circuit breaker current ratings by the derating factor shown below. See also section 9 – Technical information.


Ambient temperature	°F	-22	-4	+14	+32	+73.4	+104	+122	+140
	°C	-30	-20	-10	0	+23	+40	+50	+60
Derating factor		0.68	0.76	0.84	0.92	1	1.08	1.16	1.24

Accessories


Hex nut with splash cover, black
X 201 296 01 without O ring (IP64)
X 200 801 03 with O ring (IP66)
**Hex nut with splash cover,
transparent**
X 200 801 08 with O ring (IP66)




**Water splash cover,
transparent with knurled
nut and O ring (IP64)
X 210 663 01**



**Separate hardware
Hex nut Y 300 116 02**



**Knurled nut
Y 302 065 01**



This is a metric design and millimeter dimensions take precedence ($\frac{\text{mm}}{\text{inch}}$)

All dimensions without tolerances are for reference only. In the interest of improved design, performance and cost effectiveness the right to make changes in these specifications without notice is reserved. Product markings may not be exactly as the ordering codes. Errors and omissions excepted.