Hubbell Raceway Systems More Innovation. More Capacity. More Flexibility.

HUBBEL



Nobody delivers like Hubbell Commercial Solutions

The Raceway Story

or well over a century, Hubbell Wiring
Systems, including Wiring Device-Kellems
and Hubbell Premise Wiring, has continued
its tradition of pioneering innovative products
and quality solutions for industrial, commercial and
institutional applications.

In 1986, Hubbell's commitment to this tradition led to the introduction of PolyTrak®, a line of ground-breaking non-metallic surface raceway that was designed and developed to exceed every customer's expectations.

Listening to and understanding the needs of our customers gave rise to several unique PolyTrak designs that meet virtually every raceway application.
With products like BaseTrak®,
Super BaseTrak®,

LANTrak®, WallTrak®, PremiseTrak® and PlugTrak®, customers can easily install the right raceway system to provide the proper capacity, bend radius and aesthetically pleasing design for any power, data and telecommunication cable distribution.

Hubbell's innovative tradition continues today with the introduction of a new line of metal raceway. Only Hubbell Wiring Systems could take a familiar, mature product like metal raceway and make it better. How did we do it? We listened to our customers.

Through extensive interviews, indepth focus groups and state-of-theart research and development, we have delivered an improved metal raceway product line with all the enhancements and flexibility customers asked



for. Technologies like the Hubbell Handi-Screw and

the Hubbell By-Pass divider along with rounded corners, single-seam box construction and enhanced

datacom capabilities are just some of the features we incorporated to benefit customers. With maximum functionality, vital capacity, unmatched quality and easy installation, never before has there been a metal raceway like this.




Listening to the customer and developing and implementing innovative products to meet their needs are the fundamental principles that make Hubbell Wiring Systems a respected leader in the electrical and data communications industry. These same

principles are the driving force behind the expansion and enhancement of our comprehensive surface raceway product line. That's our story.







Catalog Num	nber	Description	
1 PDB12TGD	N. II	Two-Gang Deep Divided Box for WallTrak, LANTrak and PremiseTrak (Latching)	
2 PP1BC7		7 ft. PremiseTrak (Latching) Single Channel	
3 PP1TCBC	21	Tee Fitting (Base and Cover) for PremiseTrak (Latching)	
4 PDB12LF	0	Round Lighting Fixture Box for WallTrak, LANTrak and PremiseTrak (Latching)	

Catalog Number	Description
5 PP1IEBC	Internal Elbow (Base and Cover) for PremiseTrak (Latching)
6 PS3BC10	10 ft. (Base and Cover) Super BaseTrak Three Channel Raceway
7 PS3FCIB3G	Three-Gang Full Capacity Raised Inline Box Super BaseTrak
8 PS3IEBC	Internal Elbow (Base and Cover) for Super BaseTrak



	Catalog Nun	nber	Description		Catalog Nur	nber	Description
9	PLP1CACF		Conduit Adapter/Ceiling Fitting for WallTrak, LANTrak and PremiseTrak (Latching)	13	PB3RED	F	Reducer BaseTrak to WallTrak
10	PDB12LPB	ME	Low Profile Box WallTrak, LANTrak and PremiseTrak (Latching)	14	PB3FCIB3G	1	Three-Gang Full Capacity Raised Inline Box BaseTrak
11	PL1FEBC	24	Flat Elbow (Base and Cover) LANTrak	15	PB2IND2G	F	Two-Gang Inline Flush Box PB2 BaseTrak
12	PT156112	** D	PlugTrak 6 ft. 15 Amp Single Circuit Six Duplex Receptacles 12" Spacing	16	PB2SPL10 PB2B10		10 ft. (Split Cover) 10 ft. (Base) PB2 BaseTrak Raceway


Non-Metallic Surface Raceway



Complete Line of Raceway

- PolyTrak Non-Metallic Surface Raceway is a complete system with raceway, fittings, boxes and devices.
- Sizes range from single channel PremiseTrak to three channel Super BaseTrak for all types of surface raceway requirements.
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements.
- UL Listed and CSA Certified to 600 volts.
- Office white color.





Non-Metallic PlugTrak

- Available as hard wired multi-outlet assembly or relocatable power tap.
- Hubbell designed and manufactured
 15 or 20 Amp receptacles.
- UL Listed and CSA Certified.
- Office white color.

Hard wired multi-outlet PlugTrak:

- Available in 5 ft. or 6 ft. lengths.
- Available in single, two circuit and is inherently an isolated ground product.
- Multiple spacing configurations.
- Hard wired PlugTrak mates with LANTrak fittings and boxes.

Portable PlugTrak:

- Available in 3 ft. or 5 ft. lengths.
- 6 ft. length 15 or 20 Amp molded cord set allows reliable access.
- Pre-punched holes makes mounting easy.



One Box, Three Systems

- Boxes have three cut-aways that can be utilized with WallTrak, LANTrak and PremiseTrak (Latching) systems.
- Reduces inventory requirements.
- Eliminates need to order three separate boxes.
- Boxes available in low, standard and deep profiles.
- Two-gang divided box available for power, data, voice, audio and video applications.
- Boxes utilize Hubbell KP plates or INFINeSTATION™ modules and bezels.





Flush or Full Capacity Boxes

- Super BaseTrak and BaseTrak raceway offer multiple solutions for box installation.
- Super BaseTrak inline three-gang box allows maximum capacity in a flush design.
- Super BaseTrak and BaseTrak available in single, two and three-gang full capacity boxes.
- Three and two channel BaseTrak (PB3 and PB2) available with one and two-gang inline boxes.
- Full capacity in-line boxes eliminate the need to de-rate the wire-fill capacity due to the intrusion of datacom devices into the raceway channel.





Raceway			Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	$\bigcap_{A \to B} \bigcap_{A}$		PT1BC5 PT1BC7 A: .68" (17.30) B: .75" (18.90)	5 ft. 7 ft.	Office White
Base and Cover (with adhesive) Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A B		PT1ABC5 PT1ABC7 A: .68" (17.30) B: .75" (18.90)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes			Catalog Number		Color
One-Gang Low Profile Box For shallow switches and receptacles.	B		PT12LPB A: 3.25" (82.55) B: 4.90" (124.46) C: 1.12" (28.50)		Office White
One-Gang Standard Box For standard switches and receptacles.	C A	100	PT12SBA A: 3.25" (82.55) B: 4.90" (124.46) C: 1.63" (41.40)		Office White
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	B		PT12DBA A: 3.25" (82.55) B: 4.90" (124.46) C: 1.91" (48.40)		Office White
Two-Gang Deep Box For deep devices or applications where additional room is beneficial. Uses two-gang KP or DP plates for data application. Uses two-gang KP plate for power application.	B		PT12TGB A: 5.06" (128.52) B: 4.90" (124.46) C: 1.91" (48.40)		Office White
Round Box			Catalog Number		Color
Round Lighting Fixture Box To hang fixtures.		0	PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)		Office White

Round Box		Catalog Number	Color
Round Lighting Fixture Box To hang fixtures.	\$ B	PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)	Office White

Fittings

Internal Elbow - Cover Only

For inside surfaces at right angles.





Catalog Number


PT1IE
A: 1.34" (33.9)
B: 0.89" (22.7)
C: 1.34" (33.9)

Office White

Color

External Elbow - Cover Only

For outside surfaces at right angles.




PT1EE

A: 1.24" (27.69) B: 0.88" (22.35) C: 1.24" (27.69) Office White

Flat Elbow - Cover Only

For right angle turns on same surface.





PT1FE

A: 1.33" (33.78) B: 1.33" (33.78) C: 0.74" (18.70) Office White

Tee - Cover Only

Full capacity 11/4 in. bend radius. Tee.





PT1TC

A: 1.77" (44.90) B: 1.33" (33.80) C: 0.74" (18.70) Office White

Splice Cover

For covering potential openings where two lengths of raceway come together.






PT1SC

A: 1.00" (25.40) B: 0.89" (22.61) C: 0.74" (18.70) Office White

End Cap

For closing end of raceway.






PT1EC

A: 0.88" (22.35) B: 0.74" (18.70) C: 0.89" (22.70) Office White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.





PT12CA

A: 1.64" (41.60) B: 1.62" (41.00) C: 2.50" (63.50)

Raceway			Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A A		PP1BC5 PP1BC7 A: 0.77" (19.60) B: 0.84" (21.30)	5 ft. 7 ft.	Office White
Base and Cover (with adhesive) Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A A		PP1ABC5 PP1ABC7 A: 0.77" (19.60) B: 0.84" (21.30)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes			Catalog Number		Color
One-Gang Low Profile Box For shallow switches and receptacles.	B		PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)		Office White
One-Gang Standard Box For standard switches and receptacles.	B	21.74	PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)		Office White
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	B	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Deep Divided Box For deep switches, receptacles and communication devices.	C A		PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Deep Undivided Box For low voltage applications only.	C		PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Round Box			Catalog Number		Color
Round Lighting Fixture Box		and the same of th	PDB12LF		Office

Round Box		Catalog Number	Color
Round Lighting Fixture Box To hang fixtures.	B	PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)	Office White


Base & Cover

Catalog Number

Fittings

Internal Elbow

Full capacity 1¼ in. bend radius internal elbow.



Cover Only

PP1IEA: 2.40" (60.96)
B: 1.03" (26.16)
C: 2.40" (60.96)

PP1IEBCA: 2.40" (60.96)
B: 1.03" (26.16)


C: 2.40" (60.96)

Office White

Color

External Elbow

Full capacity 1¼ in. bend radius external elbow.






PP1EE

A: 4.47" (113.54) B: 1.03" (26.16) C: 4.47" (113.54) **PP1EEBC**A: 4.47" (113.54)
B: 1.03" (26.16)
C: 4.47" (113.54)

Office White

Flat Elbow

Full capacity 11/4 in. bend radius flat elbow.






PP1FE

A: 2.62" (66.55) B: 2.62" (66.55) C: 0.85" (21.59) **PP1FEBC**A: 2.62" (66.55)
B: 2.62" (66.55)
C: 0.85" (21.59)

Office White

Tee

Full capacity 11/4 in. bend radius tee.





PP1TC

A: 4.22" (107.19) B: 2.62" (66.55) C: 0.85" (21.59) **PP1TCBC**A: 4.22" (107.19)
B: 2.62" (66.55)

C: 0.85" (21.59)

Office White

Splice Cover

For covering potential openings where two lengths of raceway come together.





PP1SC

A: 1.09" (27.69) B: 1.02" (25.91) C: 0.85" (21.59) Office White

Safety Strap

For preventing potential tampering with PP1 PremiseTrak cover. Can also be used as a splice cover.





PP1SS

A: 0.62" (15.75) B: 1.94" (49.28) C: 0.86" (21.84) Office White

End Cap

For closing end of raceway.






PP1EC

A: 1.00" (25.40) B: 0.84" (21.34) C: 0.77" (19.56) Office White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.





PLP1CACF

A: 2.29" (58.17) B: 3.31" (84.07) C: 3.90" (99.06)

PL1 LANTrak[®] (Latching) Non-Metallic Raceway

Raceway			Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A A		PL1BC5 PL1BC7 A: 1.04" (26.40) B: 1.38" (35.00)	5 ft. 7 ft.	Office White
Base and Cover (with adhesive) Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	B		PL1ABC5 PL1ABC7 A: 1.04" (26.40) B: 1.38" (35.00)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes			Catalog Number		Color
One-Gang Low Profile Box For shallow switches and receptacles.	B		PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)		Office White
One-Gang Standard Box For standard switches and receptacles.	B	2.00	PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)		Office White
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	B	100 mg	PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Deep Divided Box For deep switches, receptacles and communication devices.	B		PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Deep Undivided Box For low voltage applications only.	B		PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Round Box			Catalog Number		Color
Round Lighting Fixture Box	_	Contract of the Contract of th	PDB12LF		Office

Round Box		Catalog Number	Color
Round Lighting Fixture Box To hang fixtures.	\$B	PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)	Office White


UL Listed, CSA Certified Catalog Number

Base & Cover

Fittings

Internal Elbow

Full capacity 11/4 in. bend radius internal elbow.





Cover Only PL1IE


A: 2.51" (63.75) B: 1.57" (39.88) C: 2.51" (63.75)

PL1IEBC A: 2.51" (63.75) B: 1.57" (39.88) C: 2.51" (63.75) Office White

Color

External Elbow

Full capacity 11/4 in. bend radius external elbow.






PL1EE

A: 5.06" (128.52) B: 1.57" (39.88) C: 5.06" (128.52) **PL1EEBC** A: 5.06" (128.52) B: 1.57" (39.88) C: 5.06" (128.52) Office White

Flat Elbow

Full capacity 11/4 in. bend radius flat elbow.






PL1FE

A: 3.19" (81.03) B: 3.19" (81.03) C: 1.11" (28.19) PL1FEBC A: 3.19" (81.03) B: 3.19" (81.03) C: 1.11" (28.19) Office White

Tee

Full capacity 11/4 in. bend radius tee.





PL1TC

A: 4.75" (120.65) B: 3.15" (80.01) C: 1.11" (28.19)

PL1TCBC

A: 4.75" (120.65) B: 3.15" (80.01) C: 1.11" (28.19)

Office White

Splice Cover

For covering potential openings where two lengths of raceway come together.





PL1SC

A: 1.12" (28.45) B: 1.55" (39.37) C: 1.11" (28.19) Office White

Safety Strap

For preventing potential tampering with PL1 LANTrak cover. Can also be used as a splice cover.





PL1SS

A: 0.62" (15.75) B: 2.68" (68.07) C: 1.12" (28.45) Office White

End Cap

For closing end of raceway.






PL1EC

A: 1.00" (25.40) B: 1.39" (35.31) C: 1.04" (26.42) Office White

Conduit Adapter/Ceiling **Fitting**

For connecting conduit to raceway. Also use for ceiling feeds.





PLP1CACF

A: 2.29" (58.17) B: 3.31" (84.07) C: 3.90" (99.06)

PW2 WallTrak® (Latching) Non-Metallic Raceway

(3/				
Raceway			Catalog Number	Length	Color
Base and Cover Two channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A		PW2BC5 PW2BC7 A: 1.04" (26.40) B: 2.12" (53.85)	5 ft. 7 ft.	Office White
Base and Cover (with adhesive) Two channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	A		PW2ABC5 PW2ABC7 A: 1.04" (26.40) B: 2.12" (53.85)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes			Catalog Number		Color
One-Gang Low Profile Box For shallow switches and receptacles.	B		PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)		Office White
One-Gang Standard Box For standard switches and receptacles.	B	AND SECOND	PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)		Office White
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	B	24	PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
One-Gang Divider For use with PDB12S and PDB12D one-gang boxes. Required when two services are passing through box.	B C	M	PDB1DIV A: 2.79" (70.86) B: 1.40" (35.56) C: 0.94" (23.88)		Office White
Two-Gang Deep Divided Box For deep devices or applications where additional room is beneficial.	B		PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Divider For use with PDB12TGD two-gang box only. Required when two services are passing through box and mounting devices perpendicular to raceway.	B	H	PDB2DIV A: 4.62" (117.35) B: 2.76" (70.10) C: 0.94" (23.88)		Office White
Two-Gang Deep Undivided Box For low voltage applications only.	B		PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Round Box			Catalog Number		Color
Round Lighting Fixture Box To hang fixtures.	; B	9	PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)		Office White



68

Catalog Number

			Julu.J	9	
Fittings			Cover Only	Base & Cover	Color
Internal Elbow Full capacity 11/4 in. bend radius internal elbow.	B		PW2IE A: 2.83" (71.88) B: 2.32" (58.93) C: 2.83" (71.88)	PW2IEBC A: 2.83" (71.88) B: 2.32" (58.93) C: 2.83" (71.88)	Office White
External Elbow Full capacity 11/4 in. bend radius external elbow.	B		PW2EE A: 5.00" (127.00) B: 2.32" (58.93) C: 5.00" (127.00)	PW2EEBC A: 5.00" (127.00) B: 2.32" (58.93) C: 5.00" (127.00)	Office White
Flat Elbow Full capacity 11/4 in. bend radius flat elbow.	B		PW2FE A: 3.94" (100.08) B: 3.94" (100.08) C: 1.11" (28.19)	PW2FEBC A: 3.94" (100.08) B: 3.94" (100.08) C: 1.11" (28.19)	Office White
Tee Full capacity 11/4 in. bend radius tee.	B		PW2TC A: 5.42" (137.67) B: 3.91" (99.31) C: 1.90" (48.26)	PW2TCBC A: 5.42" (137.67) B: 3.91" (99.31) C: 1.90" (48.26)	Office White
Splice Cover For covering potential openings where two lengths of raceway come together.	B		PW2SC A: 1.11" (28.19) B: 2.30" (58.42) C: 1.11" (28.19)		Office White
Safety Strap For preventing potential tampering with PW2 WallTrak cover. Can also be used as a splice cover.	A TO B		PW2SS A: 0.62" (15.75) B: 3.43" (87.12) C: 1.12" (28.45)		Office White
End Cap For closing end of PW2 WallTrak to surface.	B		PW2EC A: 1.00" (25.40) B: 2.14" (54.36) C: 1.04" (26.42)		Office White
Reducer Reduces from PW2 WallTrak Raceway to one or two PP1 PremiseTrak Raceway.	B			PW2RED A: 1.62" (41.15) B: 2.40" (60.96) C: 1.15" (29.21)	Office White
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for	B	AM		PW2CACF A: 4.18" (106.17) B: 3.32" (84.33) C: 4.20" (106.68)	Office White

ceiling feeds.

PB2 BaseTrak® Non-Metallic Raceway **Raceway Catalog Number Length** Color **Base PB2B5** 5 ft. Office Two channel raceway. **PB2B10** 10 ft. White A: 1.42" (36.00) Available in 5 ft. (1.5m) and B: 4.50" (114.30) 10 ft. (3m) lengths. Cover PB2C5 5 ft. Office Cover allows access to multiple **PB2C10** 10 ft. White B: 4.50" (114.30) channels. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths. В **Split Cover** PB2SPL5 5 ft. Office Cover allows separation of channels PB2SPL10 10 ft. White B: 2.22" (56.30) and access to a single channel. Wire Clip PB2WC Office For holding conductors in place. White Box **Catalog Number** Color **Two-Gang InLine Box** PB2IND2G Office A: 7.66" (194.56) B: 4.74" (120.40) White For switches, receptacles and communication devices. Provides C: 1.84" (46.74) flush look. Accepts KP style plates.

Fittings			Catalog Number	Color
Internal Elbow - Base and Cover Full capacity 1¼ in. bend radius internal elbow.	C		PB3IEBCA A: 4.36" (110.74) B: 4.72" (119.89) C: 4.36" (110.74)	Office White
External Elbow - Base and Cover Full capacity 1¼ in. bend radius external elbow.	B		PB3EEBCA A: 6.48" (164.59) B: 4.72" (119.89) C: 6.48" (164.59)	Office White
Flat Elbow - Base and Cover Full capacity 1¼ in. bend radius flat elbow.	В	511	PB3FEBCA A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)	Office White



UL Listed, CSA Certified

Fittings

Tee - Base and Cover

Full capacity 11/4 in. bend radius tee.





Catalog Number

PB3TCBCAA: 7.37" (187.20)
B: 7.08" (179.83)
C: 2.72" (69.09)

Color Office White

Splice Cover

For covering potential openings where two lengths of raceway come together.






PB3SC

A: 1.56" (39.62) B: 4.74" (120.40) C: 1.69" (42.93) Office White

Safety Strap

For preventing potential tampering with PB2 BaseTrak cover. Can also be used as a splice cover.





PB3SS

A: 1.50" (38.10) B: 6.01" (152.65) C: 1.74" (44.20) Office White

End Cap

For closing end of PB2 BaseTrak Raceway.





PB3ECA

A: 2.02" (51.31) B: 4.68" (118.97) C: 1.72" (43.69) Office White

Reducer

Reduces from PB2 BaseTrak Raceway to PW2 WallTrak Raceway.





PB3REDA

A: 3.50" (88.90) B: 4.72" (119.89) C: 1.73" (43.94) Office White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.




PB2CACF

A: 4.72" (119.89) B: 5.22" (132.70) C: 6.30" (160.02) Office White

Surface Panel Connector

For connecting PB2 Raceway with surface type panel boxes.





PB3SPCA


A: 2.22" (56.39) B: 5.66" (143.76) C: 1.60" (40.64)

PB3 BaseTrak® Non-Metallic Raceway

Raceway

Base and Cover

Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.





Catalog Number	Length
PB3BC5	5 ft.
PB3BC10	10 ft.
A: 1.63" (41.40)	

Office White

Wire Clip

For holding conductors in place.



PB3WC

B: 4.50" (114.30)

Office White

Color

Color

Boxes

One-Gang Inline Box

For switches, receptacles and communication devices. Provides flush look. Accepts KP style plates.






Catalog Number **PB3IND**

A: 7.70" (195.58) B: 4.84" (122.94) C: 2.02" (51.30)

Office White

Two-Gang InLine Box

For switches, receptacles and communication devices. Barriers allow separation of power and datacom. Removal of barriers allows for expanded capacity. Accepts KP style plates.






PB3IND2G

A: 7.00" (177.80) B: 4.75" (120.65) C: 3.22" (81.78)

Office White

One-Gang Full Capacity Box

Single gang box that allows full capacity from PB3 raceway to box for either power or datacom applications. Accepts KP style plates and one-gang DP plates.






PB3FCIB

A: 4.38" (111.25) B: 4.80" (121.92) C: 3.17" (80.52)

Office White

Two-Gang Full Capacity Box

Two-Gang box that allows full capacity from PB3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.






PB3FCIB2G

A: 7.20" (182.88) B: 4.80" (121.92) C: 3.17" (80.52)

Office White

Three-Gang Full Capacity Box

Three gang box that allows full capacity from PB3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.





PB3FCIB3G


A: 9.96" (252.98) B: 4.80" (121.92) C: 3.17" (80.52)

Office White

Fittings

Internal Elbow

Full capacity 11/4 in. bend radius internal elbow.





Catalog Number

Base & Cover Color Cover Only

PB3IE	PB3IEBCA
A: 4.36" (110.74)	A: 4.36" (110.
3: 4.72" (119.89)	B: 4.72" (119.
1 00" (1 10 7 1)	0 4 00 11 (4 4 0

(110.74)(119.89)

Office White

External Elbow

Full capacity 11/4 in. bend radius external elbow.





PB3EE

A: 6.48" (164.59) B: 4.72" (119.89)

PB3EEBCA A: 6.48" (164.59)

B: 4.72" (119.89)





Catalog Number



Fittings

Flat Elbow

Full capacity 11/4 in. bend radius flat elbow.





Cover Only

PB3FE A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)

Base & Cover PB3FEBCA

C: 1.71" (43.43)

Office A: 7.64" (194.66) White B: 7.64" (194.66)

Tee

Full capacity 11/4 in. bend radius tee.





PB3TCBCA

A: 7.37" (187.20) B: 7.08" (179.83) C: 2.72" (69.09)

Office White

Color

Splice Cover

For covering potential openings where two lengths of raceway come together.






PB3SC

A: 1.56" (39.62) B: 4.74" (120.40) C: 1.69" (42.93)

Office White

Safety Strap

Prevents potential tampering with PB3 BaseTrak cover. Can also be used as a splice cover.





PB3SS

A: 1.50" (38.10) B: 6.01" (152.65) C: 1.74" (44.20)

Office White

End Cap

For closing end of PB3 BaseTrak Raceway.





PB3ECA

A: 2.02" (51.31) B: 4.68" (118.97) C: 1.72" (43.69)

Office White

Reducer

Reduces from PB3 BaseTrak Raceway to PW2 WallTrak Raceway.






PB3REDA

A: 3.50" (88.90) B: 4.72" (119.89) C: 1.73" (43.94)

Office White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.






PB3CACF

A: 4.72" (119.89) B: 5.22" (132.70) C: 6.30" (160.02) Office White

Surface Panel Connector

For connecting PB3 Raceway with surface type panel boxes.





PB3SPCA

A: 2.22" (56.39) B: 5.66" (143.76) C: 1.60" (40.64)

Office White

Transition Fitting

Transitions horizontal PB3 BaseTrak to vertical PW2 WallTrak, PL1 LANTrak or PP1 PremiseTrak.






PB3TRBC

A: 3.22" (81.79) B: 7.28" (184.91) C: 2.42" (61.47)

Office White

Transition Fitting

Transitions from BT3 (old style) BaseTrak Raceway to PB3 (new style) BaseTrak Raceway.





BTPB3TF


A: 2.22" (56.39) B: 5.66" (143.76) C: 1.35" (34.29)

PS3 Super BaseTrak® Non-Metallic Raceway

Raceway

Base and Cover

Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.





PS3BC5
PS3BC10
A: 1.97" (50.00)
B: 6.70" (170.20)

Catalog Number

5 ft. 10 ft.

Length

Office White

Color

Wire Clip

For holding conductors in place.




PS3WC

Office White

Boxes

Three-Gang Inline Box

For any combination of power and datacom applications. Provides flush look. Accepts KP style plates and bezels.





Catalog Number PS3IND


A: 7.00" (177.80) B: 6.95" (176.53) C: 2.28" (57.91)

Office White

Color

One-Gang Full Capacity Box

Single gang box that allows full capacity from PS3 raceway to box for either power or datacom applications. Accepts KP style plates and one-gang DP plates.






PS3FCIB

A: 4.38" (111.25) B: 6.95" (176.53) C: 3.46" (87.88)

Office White

Two-Gang Full Capacity Box

Two-Gang box that allows full capacity from PS3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.






PS3FCIB2G

A: 7.20" (182.88) B: 6.95" (176.53) C: 3.46" (87.88)

Office White

Three-Gang Full Capacity Box

Three gang box that allows full capacity from PS3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.





PS3FCIB3G


A: 9.96" (252.98) B: 6.95" (176.53) C: 3.46" (87.88)

Office White

Fittings

Internal Elbow

Full capacity 11/4 in. bend radius internal elbow.





Catalog Number

Base & Cover Color Cover Only


PS3IE

A: 4.36" (110.74) B: 6.93" (176.02) C: 4.36" (110.74)

PS3IEBC A: 4.36" (110.74) B: 6.93" (176.02) C: 4.36" (110.74) Office White

External Elbow

Full capacity 11/4 in. bend radius external elbow.





PS3EE

A: 6.81" (172.97) B: 6.93" (176.02) C: 6.81" (172.97)

PS3EEBC A: 6.81" (172.97)

B: 6.93" (176.02) C: 6.81" (172.97)

Office White


74

Catalog Number

Fittings

Flat Elbow

Full capacity 11/4 in. bend radius flat elbow.





Cover Only Base & Cover Color

PS3FE

A: 9.85" (250.19) B: 9.85" (250.19) C: 2.08" (52.83) PS3FEBC

A: 9.85" (250.19) B: 9.85" (250.19) C: 2.08" (52.83) Office White

Tee

Full capacity 11/4 in. bend radius





PS3TCBC

A: 10.00" (254.00) B: 9.68" (245.87) C: 3.30" (83.82) Office White

Splice Cover

For covering potential openings where two lengths of raceway come together.





PS3SCA: 1.56" (39.62) B: 6.95" (176.53) C: 2.03" (51.62)

Office White

Safety Strap

Prevents potential tampering with PS3 Super BaseTrak cover. Can also be used as a splice cover.





PS3SS

A: 1.50" (38.10) B: 8.24" (209.30) C: 2.08" (52.85) Office White

End Cap

For closing end of PS3 Super BaseTrak Raceway.





PS3EC

A: 1.50" (38.10) B: 6.88" (174.75) C: 2.06" (52.32) Office White

Reducer

Reduces from PS3 Super BaseTrak Raceway to PB3 BaseTrak Raceway.






PS3RED

A: 4.81" (122.17) B: 6.93" (176.02) C: 2.05" (52.07) Office White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.






PS3CACF

A; 6.93" (176.02) B: 4.32" (109.73) C: 6.29" (159.77) Office White

Surface Panel Connector

To connect PS3 Raceway with surface type panel boxes.





PS3SPC

A: 1.00" (25.40) B: 7.87" (199.90) C: 2.54" (64.52)

Non-Metallic PlugTrak®



Non-Metallic PlugTrak® - 5 Ft. Base and Cover

Catalog Numbers	Amps	Circuits	# Duplex Receptacles	Receptacle Spacing (in)
PT155112	15	Single	5	12"
PT155212	15	Two	5	12"
PT155115	15	Single	4	15"
PT155130	15	Single	2	30"
PT205112	20	Single	5	12"
PT205212	20	Two	5	12"
PT205115	20	Single	4	15"
PT205215	20	Two	4	15"
PT205130	20	Single	2	30"

Boxes Single-Gang **Low Profile**



Fittings External Elbow Cover Only





One-Gang	
Standard	



Flat Elbow Base and Cover



One-Gang Deep



Flat Elbow **Cover Only**



Two-Gang **Deep Divided**



Tee Base and Cover



Round Lighting **Fixture**



Tee **Cover Only**



Splice Cover PL1SC



Non-Metallic PlugTrak® - 6 Ft. Base and Cover

Catalog Numbers	Amps	Circuits	# Duplex Receptacles	Receptacle Spacing (in)
PT156112	15	Single	6	12"
PT156212	15	Two	6	12"
PT156118	15	Single	4	18"
PT156124	15	Single	3	24"
PT206106	20	Single	12	6"
PT206206	20	Two	12	6"
PT206112	20	Single	6	12"
PT206212	20	Two	6	12"
PT206118	20	Single	4	18"
PT206218	20	Two	4	18"
PT206124	20	Single	3	24"
PT206224	20	Two	3	24"
PT206136	20	Single	2	36"

Catalog **Fittings** Number Internal PL1IEBC **Elbow**

Base and Cover

Internal

External

Elbow Base and

Cover

Elbow Cover Only



				6	
8	9	ſ	I	f	í
4	q			P	j'a
q	ĝ			Ь	þ







PL1EEBC



End Cap

Security Cap



PL1SS

PL1EC



Conduit Adapter/ Ceiling Fitting



Non-Metallic Portable PlugTrak®



Catalog Numbers	Amp	Length	Cord Length	# Duplex Receptacles
PT153112P	15	3 Foot	6 Foot	3
PT155112P	15	5 Foot	6 Foot	5
PT203112P	20	3 Foot	6 Foot	3
PT205112P	20	5 Foot	6 Foot	5
PL1MC (Mounting Clip)				

Plates and Outlets for Non-Metallic Raceway



(UL) (IP UL Listed, CSA Certified

	$\overline{}$	h "KP" Pla	ates				rame Modules		Snap-In Conne	ector Fittings (flu	ısh outlets)
Toggle KP1	0 0	Receptaice (1.41" ID) KP7	$ $ $ $	Duplex KP8			e will accept any mod gled fixtures to be us 2-Gang	dules in three unit ed in bottom opening	Snap-in connecto	rs to be used with Di nunication inserts. No	
Blank KP14	0 0	Style Line KP26	°	KP212		Plate Frame DF10W	Plate Frai DF2OW	me III OII II OII	Blank (10 pack) SIBOWPK10	F Connector SIFOW	ST Fiber Connector SISTOW
(3) Jacks KP2163		Receptacle (1.60" ID) KP720	°	KFZ IOZ	0	Blank Module .5 Unit DFBM05OW	Blank Module 1 Unit DFBM10W	Blank Module 1.5 Unit DFBM15OW	BNC SIBNCOW	RCA Black SIRCAOW	Super S-Video SISVOW
Coax/Jack KP2140		KP Module Bezel Frame KPIMBZOW			0	Keystone, 1–Port	Keystone, 2–Port Flat, 1 Unit	Keystone, 1–Port Angled, 1.5 Unit	SC Duplex Adapter Use with plate and modules only. SIFSC		
One Gar	na Sm	ooth "DP"	Diatos			DF1KOW	DF2KOW	DFA1KOW	Communication	on Outlets (Jacks	s)
Style Line HPS1DOW		Duplex P8DOW	Plates	2-Port					Cat. 5e, Office White T568A, T568B, RJ45	Cat. 6, Office White T568A, T568B, RJ45	6 Position USOC, Office White, RJ25 HBLUOW
Keystone		Keystone		DP12OW E		Keystone, 2—Port Angled, 1.5 Unit DFA2KOW	SC 1 Duplex Angled, 1.5 Unit DFA1SCOW	SC 2 Duplex Angled, 2 Unit DFA2SCOW	HBL5EOW	HBL60W	
3-Port Flush DP130W		4-Port Flush DP14OW		6-Port					Jack Color Options	(replaces "OW" Suffix	x)
Commu	nicatio	n Outlets						→	OW = Office White		
Style Line Keystone 2–Port FCX2440V		Style Line Keystone 3–Port FCX344OW		Duplex Keystone 2–Port DJOOW		Keystone Openir Hole size for mou all Hubbell Jacks	unting A	A: .580 in. (14.73) B: .760 in. (19.30)	BK = Black OR = Orange B = Blue R = Red AL = Almond	W = White EI = Elec. Iv GN = Green Y = Yellow	

Technical Data - Non-Metallic Surface Raceway

100	recrimical Data - Non-Metallic Surface naceway													
	Non-Metallic Raceway Wire Fill Capacities													
			Power IN/T90 Nyl	on)	Vo	ice	Data (Copper Cables)				(Multimo	Data ode Fiber Opt	ic Cables)	
			14 AWG	12AWG	10AWG	4-Pair	25-Pair	Type RG59U	Category 5e	Category 6	Augmented Cat 6	(2) or (4) Fiber Round Cable	Fiber Optic Jumpers	Fiber Optic Zip Cord
		Wire O.D. (in.):				0.19	0.41	0.242	0.21	0.25	0.35	0.19	0.118	.12 X .24
		Wire Area (sq. in.):				0.0283	0.1320	0.0460	0.0346	0.0491	0.0962	0.0283	0.0109	0.0288
Series	Channel	Channel Area (sq. in.)	Tempe	UL erature Ris	e Test	40%	40%	40%	40%	40%	40%	40%	40%	40%
PT1	Α	0.29	5	8	5	4	1	3	3	2	1	4	11	4
PP1	Α	0.38	12	11	8	5	1	3	4	3	2	5	14	5
PL1	Α	1.03	42	34	22	15	3	9	12	8	4	15	38	14
PW2	A+B	1.6	41	36	22	23	5	14	18	13	7	23	59	22
AB	Α	0.81	12	22	12	11	2	7	9	7	3	11	30	11
	В	0.79	12	22	10	11	2	7	9	6	3	11	29	11
PB2	A+B	5.72	60	36	45	81	17	50	66	47	24	81	210	79
A B	A or B	2.86	42	30	28	40	9	25	33	23	12	40	105	40
PB3	A+B+C	5.57	60	36	45	79	17	48	64	45	23	79	204	77
ABC	A or C	1.8	42	30	28	25	5	16	21	15	7	25	66	25
	В	1.97	42	30	28	28	6	17	23	16	8	28	72	27
PS3	A+B+C	10.58	72	66	78	150	32	92	122	86	44	150	388	147
ABC	A or C	3.41	42	36	42	48	10	30	39	28	14	48	125	47
	В	3.76	42	36	42	53	11	33	43	31	16	53	138	52

Note: Pathway (Raceway) fill shall be 40% Maximum. Raceway fittings and outlets/receptacles reduce the cross section of the raceway system, thus reducing overall cable fill capacity.

Physical Properties

(When tested in accordance with UL 5A) Impact Resistance5 ft. lbs. Crush Resistance 300 lbs.

Temperature Range -25.6° to 158° F

Flame RatingUL94V-0 MaterialUV Stabilized PVC

Codes/Standards

NEC Article388 EIA/TIA 569A UL Standard . . . UL 5A

Listings E118895 / E119190 CSA Standard . .C22.2 no. 62

Certified. LR87514

PlugTrak Specifications

NEC Article(s) 380

Receptacle Rating .NEMA 5-15R & 5-20R

Wire.....#12 AWG Stranded

Copper

Receptacle Face . . . Thermoplastic

Nobody delivers like Hubbell Commercial Solutions



Hubbell SystemOne. The only Floor Box and FRPT system that uses common covers for a seamless look.




Hubbell provides a complete offering of Fire-Rated Poke-Throughs including flush, pedestal and Hubbell SystemOne options.




Hubbell provides a full offering of Floor Box products including large capacity and Hubbell SystemOne options.



Hubbell offers a line of raised access floor products for computer room environments.



Hubbell Premise Wiring's full line catalog provides complete information on a wide range of Connectivity Solutions and Fiber System products and services.



Hubbell's full line catalog provides the widest variety of industrial and commercial products available.



Hubbell Wiring Device-Kellems

Hubbell Incorporated (Delaware) 185 Plains Road • Milford, CT 06461-2420 (203) 882-4800 • Fax (800) 255-1031 Internet site: www.hubbell-wiring.com

Hubbell Premise Wiring

Hubbell Incorporated (Delaware)
14 Lord's Hill Road • Stonington, CT 06378-0901
(860) 535-8326 • (800) 626-0005 • Fax (860) 535-8328
Internet site: www.hubbell-premise.com

Hubbell Canada Inc.

870 Brock Road South • Pickering, Ontario L1W 1Z8 (800) 263-4622 • (905) 839-1138 • Fax (905) 839-9108 Internet site: www.hubbell-canada.com

Hubbell De Mexico, S.A. de C.V.

Ave. Coyoacan No. 1051 • Col. Del Valle C.P. 03100 Mexico D. F. (01 55) 91 51 99 99 • Fax (01 55) 91 51 99 88 Internet site: www.hubbell.com.mx