






Ground Fault Products

2 Pole 3 Wire Grounding

15 and 20 Ampere, 120 Volt AC

**Straight Blade Commercial Specification Grade
and Commercial Hospital Grade GFCI Duplex Receptacles**


Meets 2003
UL 943
Requirements

**GFR5252IA****GFR5350BK****GF8300HI****Circuit Guard®
Commercial Specification Grade
GFCI Duplex Receptacles**

Description	Color	Catalog Numbers	
Flush, nylon face, back & side wired, multiple drive screws. Matching nylon wallplate included.	Brown	GFR5252A	GFR5352A
	Ivory	GFR5252IA	GFR5352IA
	Gray	GFR5252GYA	GFR5352GYA
	White	GFR5252WA	GFR5352WA
	Black	GFR5252BKA	GFR5352BKA
	Office White	GFR5252OWA	GFR5352OWA
	Red	GFR5252RA	GFR5352RA
Bulk packed, 50 pieces.	Brown	GFR5252AM1	GFR5352AM1
	Ivory	GFR5252IAM1	GFR5352IAM1
	Gray	GFR5252GYAM1	GFR5352GYAM1
	White	GFR5252WAM1	GFR5352WAM1
	Black	GFR5252BKAM1	GFR5352BKAM1

Circuit Guard Faceless GFCI

Description	Color	Catalog Numbers	
Faceless, back and side wired, multiple drive screws. Matching nylon wallplate included.	Brown	-	GFR5350
	Ivory	-	GFR5350I
	White	-	GFR5350W
	Black	-	GFR5350BK

**Circuit Guard
Commercial Hospital Grade
GFCI Duplex Receptacles**

Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired, multiple drive screws. Matching nylon wallplate included.	Brown	GF8200H	GF8300H
	Ivory	GF8200HI	GF8300HI
	Gray	GF8200HGY	GF8300HGY
	Red	GF8200HR	GF8300HR
	White	GF8200HW	GF8300HW
	Office White	GF8200HOW	GF8300HOW

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption.

Specifications

Trip Level	4 to 6 mA.
Trip Time	.025 sec. nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15%.
Amperage	15A/20A, 20A Feed Thru.
Maximum Interrupting Capacity	2000A.
Operating Temperature	-35°C to +66°C or -30°F to +150°F.
Maximum Humidity	95%.
Listings & Standards	Meets UL498 for receptacles, UL943 2003 Class A for GFCIs UL File E41978. CSA Certified.
Codes	Meets all NEC & CEC requirements.