



# HBL5965VBLK -- Straight Blade Products, Valise Plug



2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black  
Nylon

## Product Specifications

<b>Product Type</b>	 <p>Plugs</p>
<b>Body Style</b>	Straight
<b>Standard</b>	NEMA
<b>Amperage</b>	15A
<b>Voltage</b>	125V
<b>Poles and Wires</b>	2 Pole, 3-Wire Grounding
<b>Hospital Grade ?</b>	No
<b>Plug/Connector Grade</b>	Valise
<b>Color</b>	 <p>Black</p>
<b>Other Available Colors</b>	Black, Gray, Yellow, Orange
<b>NEMA No.</b>	5-15P
<b>Horsepower</b>	0.5
<b>Cord Dia.</b>	.220"- .660" (5.6-16.8)
<b>Type</b>	2 Pole, 3 Wire, Grounding
<b>Rating</b>	15A,125V
<b>Certification</b>	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
<b>IP Suitability</b>	IP20
<b>Housing Material</b>	Nylon
<b>Cord Clamp Material</b>	Noryl (Polyphenylene Oxide)
<b>Contact Blades Material</b>	.060" (1.5) Brass
<b>Ground Contact Blade Material</b>	.040" (1.0) Brass
<b>Terminal Screw Material</b>	Steel (copper or nickel finish)
<b>Ground Screw Material</b>	Steel (green finish)
<b>Dielectric Voltage</b>	Withstands 2,000V minimum.
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
<b>Terminal Identification</b>	Terminals identified in accordance with UL498 (Brass, White, Green).
<b>Terminal Accommodation</b>	#18-#10 AWG copper stranded conductor
<b>Product Identification</b>	Ratings are a permanent part of the device.
<b>Flammability</b>	UL 94 V2.
<b>Operating Temperatures</b>	Maximum continuous 75°C, minimum -40°C (w/o impact).
<b>UPC Number</b>	783585013084
<b>Weight in LBS</b>	0.100
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>



NE MA 7-15P  
**15A 277V AC**  
UL CSA  
2HP

NEMA Configuration

