
Product Datasheet Catalog Home Page Search

HBL2326 -- Twist-Lock Flanged Receptacle



2P3W, 20A 250V, L6-20R, White Nylon

2.06* (52.3)	
HBL2316	
Product Specifications	
Product Type	Twist-Lock Devices
Product Item	Flanged Receptacle
Wiring Scheme	2-Pole, 3-Wire Grounding
Amperage	20A
Voltage	250V AC
NEMA Configuration	L6-20R
Item Style	Standard
Device Color	White
Horsepower	2
Terminal Retainer Material	Clear polycarbonate
Terminal Clamp Material	.08"(2) steel-nickel plated
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive
Ground Screw Material	#10-32 Brass (green finish) Multi-drive
Body Holding Screw Material	Steel, zinc plated Multi-drive
Body Contact Carrier Material	Natural White Nylon
Contact Spring Material	Brass
Spring Binding Plate Material	Brass
Flanged Casing Material	Natural White Nylon
Mounting Screw Material	Nickel-plated Brass Round head screws
Ground Contact Material	.031" (.8) Brass
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	20A #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Listings	FED SPEC UL/CSA
UPC Number	783585037875
Weight in LBs	0.25
Link to Drawing Library	Click here for Library
I'I' DDDC ''	



Click here for Catalog

Link to PDF Catalog

